

Note:

1. Material:

* Base:

High Temperature Polyamide

UL 94V-0 Color Nature



* Contact: Brass

△ 2. For Lead Free Wave flow Process


Ordering Code:

CI06 ** P 1 V 00 -LF
 ① ② ③ ④ ⑤ ⑥ ⑦

- ① Series No.
- ② No. of circuits
- ③ Contact type: P= Pin Header
- ④ Plating option:
 1= 3.05μm (120u") Tin over
 0.76μm(30u") Nickel (Matte Tin Finish)
- ⑤ Type: V= Straight Type
- ⑥ Option: 00= Standard
- ⑦ Other option:
 -LF= For Lead Free Wave flow Process



SEC.A-A



Recommended P.C. Board Layout

△ A = 2.0 x No. of Spaces

B = A + 3.96

C = A + 2.8

* Available in 2 through 16 circuits

Lead Free Process

RoHS Compliant

△4						DATE	UNIT: mm / inch	TITLE:	瀚荃股份有限公司 CviLux Corporation
△3	Enya	3/8-13'	ECN13056-0/ECR13007-1	DRAWN BY:	Enya	4/16-13'	TOLERANCE UNLESS OTHERWISE SPECIFIED	2.00mm PIN HEADER DIP TYPE	
△2	Tim	11/09-10'	ECR10145-0/ECN10364	ENGINEER:	Eisley	4/19-13'	.X ± 0.30/012 X: ± 1'	MATERIAL:	DRAWING NO. CI0606SD PART NO. CI06**P1V00-LF
△1	Sandy	9/27-07'	ECN07402	CHECKED BY:	Eisley	4/19-13'	.XX ± 0.20/008	FINISH:	SCALE 3 / 1 SHEET 1 OF 1
SYM	NAME	DATE	REVISIONS	APPROVED BY:	David	4/19-13'	.XXX ± 0.10/004 .XX ±		

