

Material & Finish :

* Insulation: Nylon 66

* Contact: Brass

△ Circuit Pattern Schedule:
See Drawing No: CP0111S*

Ordering Code:

CP-01 4 ** 1 * 0
① ② ③ ④ ⑤ ⑥

① Series No.

② Type of Connector:
4= Right angle PCB mount header







③ No of Circuits:

△ ④ Plating Code: 1= Tin plated over Nickel
2= Gold flash plated over
1.27μm(50μ") Nickel
3= 0.38μm(15μ") Gold plated
over 1.27μm(50μ") Nickel

⑤ Variation:

1= UL 94V-2, Without mounting ears
3= UL 94V-0, Without mounting ears

⑥ Option: 0= Color Nature (Standard)
1= Color Black




Recommended P.C. Board Layout

Halogen-Free

Tin-Lead Process

RoHS Compliant

| | | | | | | | | | | | |
|-----|-------|----------|-----------|------------|-------------------|-----------------|--|--|--|--|--|
| △ 4 | | | | | DATE | UNIT: mm / inch | TITLE: RIGHT ANGLE HEADER CP-01 POWER CONNECTOR |  瀚荃股份有限公司 CviLux Corporation | | | |
| △ 3 | Sandy | 5/9-08' | ECN08219 | 2008.03.13 | DRAWN BY: Sandy | 5/12-08' | TOLERANCE UNLESS OTHERWISE SPECIFIED | | | | |
| △ 2 | Sandy | 2/20/06' | ECN06054 | ISSUED | ENGINEER: Eisley | 5/13-08' | .X ± 0.38/.015 X' ± r' | SCALE 2 / 1 SHEET 1 OF 1 | | | |
| △ 1 | SUN | 1/15/04' | ECN04025 | | CHECKED BY: David | 5/13-08' | .XX ± 0.25/.010 .X' ± | | | | |
| SYM | NAME | DATE | REVISIONS | | APPROVED BY: Alex | 5/13-08' | .XXX ± 0.10/.004 .XX' ± | | | | |