

## Wire-wound Chip Inductors (LB series)

## LB2016T100K



## ■ Features

- Item Summary  
10uH±10%, 0.155A, 0806/2016 (EIA/JIS)
- Lifecycle Stage  
Mass Production
- Standard packaging quantity (minimum)  
Taping Embossed 2000pcs

## ■ Products characteristics table

Inductance	10 uH ± 10 %
Case Size (EIA/JIS)	0806/2016
Rated Current (max)	0.155 A
DC Resistance (max)	0.65 Ω
DC Resistance (typ)	0.5 Ω
LQ Measuring Frequency	2.52 MHz
Self Resonant Frequency (min)	32 MHz
Operating Temp. Range	-40 to +105 °C (Including-self-generated heat)
Temperature characteristic (Inductance change)	± 20 %
RoHS2 Compliance (10 subst.)	Yes
REACH Compliance (168 subst.)	Yes
Soldering	Reflow

## ■ External Dimensions

Dimension L	2.0 ±0.2 mm
Dimension W	1.6 ±0.2 mm
Dimension T	1.6 ±0.2 mm
Dimension e	0.5 ±0.2 mm

2016.12.30

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.  
 TAIYO YUDEN reserves the right to make change to the Date at any time without notice.  
 Before making final selection, please check product specification.

Wire-wound Chip Inductors (LB series)

LB2016T100K



Dimension	unit : mm	unit : inch
Length :	2.0 +/- 0.2	(0.079 +/- 0.008)
Width :	1.6 +/- 0.2	(0.063 +/- 0.008)
Height :	1.6 +/- 0.2	(0.063 +/- 0.008)

Inductance :	10	uH	( test freq at 2.52MHz )
DC Resistance :	0.5 / 0.65	ohm	( typ / max )
Rated Current :	155	mA	

Rated current typical : 10% reduction from initial L value.  
and Temperature will rise by 20 deg C

