

MB1SAT THRU MB10SAT

SURFACE MOUNT GLASS PASSIVATED BRIDGE RECTIFIERS

Forward Current-0.8A

Reverse Voltage-100V to 1000V

FEATURES


- ◆ For surface mount applications
- ◆ Glass passivated chip junction
- ◆ Reverse voltage: 100V to 1000V
- ◆ Forward current: 0.8A
- ◆ High surge current capability

MECHANICAL DATA

- ◆ Case: MBS molded plastic body
- ◆ Terminals: Solderable Per MIL-STD-750, Method 2026
- ◆ Weight: Approximated 0.1 grams

PINING

PIN	DESCRIPTION
1	Input Pin (~)
2	Input Pin (~)
3	Output Anode (+)
4	Output Cathode (-)



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase half-wave 60 Hz, resistive or inductive load, for capacitive load current derating by 20 %.

PARAMETER	SYMBOL	MB1SAT	MB2SAT	MB4SAT	MB6SAT	MB8SAT	MB10SAT	UNIT
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	100	200	400	600	800	1000	V
Maximum RMS Voltage	V_{RMS}	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	V_{DC}	100	200	400	600	800	1000	V
Maximum Average Forward Rectified Current at $T_c = 125^\circ\text{C}$	$I_{F(AV)}$	0.8						A
Peak Forward Surge Current (Note1)	I_{FSM}	30						A
Maximum Forward Voltage at 0.4A	V_F	1.0						V
at 0.8A		1.1						
Maximum DC Reverse Current $T_A=25^\circ\text{C}$	I_R	5						uA
at Rated DC Blocking Voltage $T_A=125^\circ\text{C}$		40						
Typical Junction Capacitance(Note2)	C_J	13						pF
Typical Thermal Resistance(Note3)	$R_{\theta JA}$	95						$^\circ\text{C}/\text{W}$
	$R_{\theta JC}$	32						
Operating and Storage Temperature Range	T_J, T_{STG}	-55 to +150						$^\circ\text{C}$

Notes: 1. Measured at 8.3 ms single half sine wave superimposed on rated load (JEDEC Method).

2. Measured at 1MHz and applied reverse voltage of 4 V D.C.

3. Mounted on glass epoxy PC board with 4×1.5" X 1.5" (3.81 X 3.81 cm) copper pad.

MB1SAT THRU MB10SAT

RATINGS AND CHARACTERISTIC CURVES

Fig.1 Average Rectified Output Current Derating Curve




Fig.2 Typical Reverse Characteristics




Fig.3 Typical Instantaneous Forward Characteristics




Fig.4 Typical Junction Capacitance






Fig.5 Maximum Non-Repetitive Peak Forward Surge Current



MB1SAT THRU MB10SAT

PACKAGE OUTLINE



MBS mechanical data

UNIT		A	C	D	E	HE	d	e	L	L1	a	∠
mm	max	2.6	0.22	5.0	4.1	7.0	2.7	0.7	1.7	1.1	0.2	7°
	min	2.2	0.15	4.5	3.6	6.4	2.3	0.5	1.3	0.5	—	
mil	max	102	8.7	197	161	276	106	28	67	43	8	
	min	94	5.9	177	142	252	91	20	51	20	—	

ORDERING INFORMATION

Device	Package	Shipping
MB1SAT thru MB10SAT	MBS	3,000/Tape & Reel (13 inches)