

**Ordering Information:**

C2521HF-XP - \*\*  
1 2

1.Part No.

2.Color:

(blank):Black

WH:White

**SPECIFICATIONS:**

Current Rating: 3A AC,DC

Voltage Rating: 250V AC,DC

Temperature Range: -40°C ~ +105°C

Contact Resistance: 10mΩ Max



Insulation Resistance: 500MΩ Min

Withstanding Voltage: 1500V AC/minute

Material: Nylon 66,UL94V-0 (Black)

**Ordering Information & Dimensions**

Circuits	Dimensions(mm)		Circuits	Dimensions(mm)	
	A	B		A	B
2P	2.50	5.65	8P	17.50	20.65
3P	5.00	8.15	9P	20.00	23.15
4P	7.50	10.65	10P	22.50	25.65
5P	10.00	13.15	11P	25.00	28.15
6P	12.50	15.65	12P	27.50	30.65
7P	15.00	18.15			



CHANGJIANG CONNECTORS CO.,LTD.

Unit	Scale	Sheet
mm	4:1	1 of 1

Title :

2.50mm PITCH

Draw By:	Approved :
Dlankul Wan	Jack Yin

SINNGLE ROW HOUSING

General Tolerance

A1	CHANGE THE SIZE	2018.11.23	x.xx±0.25	PROJECT
A0	NEW RELEASE	2013.12.11	x.xx±0.20	
REV	DESCRIPTION	DATE	x.xxx±0.15	

DRAW NO : C2521HF-XP

REV A1