




# 承认书

## SPECIFICATION FOR APPROVAL

CUSTOMER:			
CUSTOMER P/N:			
Cybermax P/N:	CMCW1608F1R0KTT		
DRAWN NO. :	CM191121001		
DATE:	19.11.21	REVISION NO.	A

Signature:

APPROVED BY	CHECKED BY	DRAWN BY
 <p>黄 19.11.21 大燕</p>	 <p>谢 19.11.21 焕飞</p>	 <p>申 19.11.21 双凤</p>

**cybermax**  
cybermaxtech.com





CUSTOMER:		PAGE:	1/7
CUSTOMER P/N:		REVISION:	
Cybermax P/N:	CMCW1608F1R0KTT	DATE:	19.11.21
DRAWN NO.:	CM191121001		

<b>SHAPE &amp; DIMENSION (UNIT:mm)</b>	
Marking Code:	Size: Color: typeface:
PAD LAYOUT(MM):	ELECREICAL SCHEMATIC:

ELECREICAL SPECIFICATION						
MEAS. ITEM	SPEC.				TEST FREQ.	CONDITIONS
<b>L</b>	1.0	$\mu\text{H}$	$\pm$	10%	2.5MHz/0.1V	Ta=25°C, Idc=0A
<b>DCR</b>	320	m $\Omega$	$\pm$	30%		Ta=25°C
<b>Isat</b>	0.7	A	Max.		2.5MHz/0.1V	$\Delta L/L \leq 30\%$
<b>Irms</b>	0.7	A	Max.		2.5MHz/0.1V	$\Delta \leq 40^\circ\text{C}$
<b>SRF</b>	103	MHz	TYP			
GENERAL SPECIFICATION						
Electrical specifications :		at 25°C				
Operation Temperature:		-40~+125°C				
Storage Temperature:		-40~+125°C				
(1)WIRE TYPE: $\varnothing$ 0.05mm						
(2)WINDING: 14.5Ts(Ref.)						

CUSTOMER:		PAGE:	2/7
CUSTOMER P/N:		REVISION:	
Cybermax P/N:	CMCW1608F1R0KTT	DATE:	19.11.21
DRAWN NO.:	CM191121001		


**产品试验项目列表**

测试项目	测试条件	标准
1. 过IR ReFlow试验	峰值温度: 260°C, 时间: 10秒 过热风炉2次	验证产品过IR炉后外观状况及特性变化; 试验前后感值变化率均在10%范围内, OK。
2. 恒温恒湿试验	温度: 40°C ± 2°C 湿度: 95% ± 2%RH 时间: 100小时, 取出后在常温下放置1小时至不超过2小时再检查外观及特性	1. 试验前后感值变化率均在10%范围内, OK; 2. 制品试验后外观均无发现破裂不良, 上锡面无氧化现象。
3. 冷热冲击试验	冷冲击-40°C ± 2°C、热冲击125°C ± 2°C 100个循环 (冷冲击30分钟, 热冲击30分钟为一个循环)	验证产品受冷热变化的能力; 试验前后感值变化率均在10%范围内, OK
4. 低温保存试验	温度: -40°C ± 2°C 时间: 100小时, 取出后在常温下放置1小时至不超过2小时再检查外观及特性	试验前后感值变化率均在10%范围内, OK
5. 高温保存试验	温度: 125°C ± 2°C 时间: 100小时, 取出后在常温下放置1小时至不超过2小时再检查外观及特性	试验前后感值变化率均在10%范围内, OK
6. 板弯试验	产品焊接在PCB上, 压力从PCB底部 (即产品底部的中点) 持续施加到2mm的弯曲深度, 保持到30s	测试后无外观缺陷
7. 推拉力强度测试	将产品焊在PCB板上, 用数显式推拉力计从侧面推	产品上基板后强度是否达到客户要求
8. 可焊性试验	端子涂布助焊剂, 然后浸入锡银铜245 ± 5°C锡炉中5 ± 0.5秒, 端子必须有95%以上着锡为良品	端子必须有95%以上着锡为良品
9. 跌落试验	样品离地1M自由落下, 连续10次跌落包装箱不同的点、线、面 (6个面3条边1个点)。	感值变化率在9%以内且无明显的外观缺陷为良品, 包材无明显破损
10. 振动试验	1、将制品包装放入振动试验机来回振动1个时/每个面 (3个面), 振动周波数10~55~10HZ全振幅1.5mm。	感值变化率在10%以内且无明显的外观缺陷为良品, 包材无明显破损
11. 加压强度试验	1. 将产品固定在铁板上, 用数显式推拉力计从产品边角上压, 以测试产品的强度	产品强度是否达到客户要求

CUSTOMER:		PAGE:	3/7
CUSTOMER P/N:		REVISION:	
Cybermax P/N:	CMCW1608F1R0KTT	DATE:	19.11.21
DRAWN NO.:	CM191121001		


**REFLOW -PROFILE**

Lead-free the recommended reflow condition(temperature chart)



The reflow condition recommended above is according to the machine used by our company. Big differences will arise as a result of the type of machine, reflow conditions, method, etc used. Hence, before setting up your reflow conditions, please confirm with the above.

Lead-free heat endurance test



The test should be made under the conditions according to the chart, after the test it is kept for 2 hours under the normal temperature and humidity. The reflow test can be done twice, but the interval should be more than one hour under the normal conditions. The reflow test conditions are based on the testing instruments available in Aritech.

CUSTOMER:		PAGE:	4/7
CUSTOMER P/N:		REVISION:	
Cybermax P/N:	CMCW1608F1R0KTT	DATE:	<b>19.11.21</b>
DRAWN NO.:	CM191121001		

**B.O.M**

项目名称 Project name	型号及规格	制造商	环保要求 EN. QU	备注 Memo
磁芯(DRUM CORE)	MF801SWI1608C050A-LS	佳叶	RoHS	主选
磁芯(DRUM CORE)	MF401 SWI1608C050A-LS	佳叶	RoHS	主选
线材(WIRE)	P180G1-0.05mm	益利素勒	RoHS	主选
胶水(GLUE)	AU-6402	诚海	RoHS	灌封

CUSTOMER:		PAGE:	5/7
CUSTOMER P/N:		REVISION:	
Cybermax P/N:	CMCW1608F1R0KTT	DATE:	19.11.21
DRAWN NO.:	CM191121001		

### TEST DATA FOR PREPRODUCTION SAMPLE

TEST RESOLUTION					DIMENSION (Unit: mm)		
MEAS.	L	D.C.R			长	宽	高
ITEM	μH	mΩ			mm	mm	mm
SPEC.	1	320			Max.1.8	Max.1.2	Max.1.0
	±	±					
	10%	30%					
TEST FREQ.	2.5MHz/0.1V		Isat 0.7A	ΔL/L ≤ 30%			
1	0.971	347	0.94	-3.2%	1.69	1.05	0.97
2	0.971	350	0.92	-5.3%	1.65	1.08	0.96
3	0.976	351	0.93	-4.7%	1.66	1.06	0.95
4	0.958	353	0.90	-6.1%	1.68	1.06	0.95
5	0.973	346	0.94	-3.4%	1.69	1.07	0.99
6	0.986	347	0.92	-6.7%			
7	0.982	349	0.94	-4.3%			
8	0.976	350	0.91	-6.8%			
9	0.979	350	0.94	-4.0%			
10	0.978	346	0.92	-5.9%			
AVG.	0.975	348.9	0.926	-5.03%			
R	0.028	7	1.60	-4.20%			



APPROVED BY	CHECKED BY	DRAWN BY
 <p>黄 19.11.21 大燕</p>	 <p>谢 19.11.21 焕飞</p>	 <p>申 19.11.21 双凤</p>

CUSTOMER:		PAGE:	6/7
CUSTOMER P/N:		REVISION:	
Cybermax P/N:	CMCW1608F1R0KTT	DATE:	19.11.21
DRAWN NO.:	CM191121001		


### PACKAGING

热封包装


Reel dimensions



UNIT:mm




Tape dimensions



UNIT:mm  
TOLERANCE:±0.1

Packaging


Quantity: **4000** pcs/reel






CUSTOMER:		PAGE:	7/7
CUSTOMER P/N:		REVISION:	
Cybermax P/N:	CMCW1608F1R0KTT	DATE:	19.11.21
DRAWN NO.:	CM191121001		

### PACKAGING



- 1.1 外箱: 39\*38\*18.5 cm 一箱裝 8 內箱
- 1.2 內箱: 18.7\*18.4\*8.3 cm 一箱裝 5 卷制品
- 1.3 外箱材質: A 三 A
- 1.4 內箱材質: A=A
- 1.5 每 5 卷制品用一只静电袋包裝
- 1.6 每一静电袋內放一只袋干燥剂
- 1.7 每一卷上面依标签样式的要求贴上标签明细
- 1.8 出货内外箱贴上该箱內实际内容明细
- 1.9 出货标签规格如下: 尺寸=长度:39mm 宽度:29mm

(如: 客戶有特殊要求時, 則依客戶要求實施.)



备注: 如果捆包数量小于内箱捆包数量时就用内箱包装