



### P-Channel Enhancement-Mode MOSFET (-30V, -14A)

#### PRODUCT SUMMARY

$V_{DSS}$	$I_D$	$R_{DS(on)}$ (m $\Omega$ )TYP
-30V	-14A	10@ $V_{GS} = -10V, I_D = -14A$
		18@ $V_{GS} = -4.5V, I_D = -8A$

#### Features

- Advanced Trench Process Technology
- High Density Cell Design for Ultra Low On-Resistance
- Fully Characterized Avalanche Voltage and Current
- -5V Logic Level Control
- Lead (Pb) -free and halogen-free

 <p>8 7 6 5 EY4409 XXXXXX 1 2 3 4 SOP-8</p>	 <p>D D D D S S S G</p>	<p>Pin1/2/3: Source Pin4: Gate Pin5/6/7/8: Drain</p>	TOP Marking
			<p>EY4409 part number XXXXXX ID CODE</p>

#### Absolute Maximum Ratings ( $T_A = 25^\circ\text{C}$ , unless otherwise noted)

Symbol	Parameter	Rated	Units
$V_{DS}$	Drain-Source Voltage	-30	V
$V_{GS}$	Gate-Source Voltage	$\pm 20$	V
$I_D$	Drain Current (Continuous)	-14	A
$I_{DM}$	Drain Current (Pulsed) <sup>a</sup>	-56	A
$P_D$	Total Power Dissipation @ $T_A = 25^\circ\text{C}$	3.0	W
$E_{AS}$ <sup>b</sup>	Avalanche Energy, Single pulse ( $L = 0.3\text{mH}$ )	81	mJ
$I_S$	Maximum Diode Forward Current	-3	A
$T_j, T_{stg}$	Operating Junction and Storage Temperature Range	-55 to +150	$^\circ\text{C}$
$R_{QJA}$	Maximum Junction-to-Ambient ( $t \leq 10\text{s}$ ) <sup>c</sup>	24	$^\circ\text{C/W}$
	Maximum Junction-to-Ambient (Steady State) <sup>c</sup>	40	$^\circ\text{C/W}$

a: Repetitive Rating: Pulse width limited by the maximum junction temperature.



b: Surface Mounted on 1in<sup>2</sup> pad area,  $t < 10\text{sec}$ .

c: 1-in<sup>2</sup> 2oz Cu PCB board

### Electrical Characteristics (T<sub>A</sub>=25°C, unless otherwise noted)

Symbol	Characteristic	Test Conditions	Min.	Typ.	Max.	Unit
<b>• Off Characteristics</b>						
BV <sub>DSS</sub>	Drain-Source Breakdown Voltage	V <sub>GS</sub> =0V, I <sub>D</sub> =-250uA	-30	-	-	V
I <sub>DSS</sub>	Zero Gate Voltage Drain Current	V <sub>DS</sub> =-30V, V <sub>GS</sub> =0V	-	-	-1	μA
I <sub>GSS</sub>	Gate-Body Leakage Current	V <sub>GS</sub> =±20V, V <sub>DS</sub> =0V	-	-	±100	nA
<b>• On Characteristics</b>						
V <sub>GS(th)</sub>	Gate Threshold Voltage	V <sub>DS</sub> =V <sub>GS</sub> , I <sub>D</sub> =-250uA	-1	-1.9	-2.5	V
R <sub>DS(on)</sub>	Drain-Source On-State Resistance	V <sub>GS</sub> =-10V, I <sub>D</sub> =-14A	-	10	13	mΩ
		V <sub>GS</sub> =-4.5V, I <sub>D</sub> =-8A	-	18	21	
<b>• Dynamic Characteristics</b>						
C <sub>iss</sub>	Input Capacitance	V <sub>DS</sub> =-15V, V <sub>GS</sub> =0V, f=1MHz	-	3320	-	PF
C <sub>oss</sub>	Output Capacitance		-	395	-	
C <sub>rss</sub>	Reverse Transfer Capacitance		-	245	-	
<b>• Switching Characteristics</b>						
Q <sub>g</sub>	Total Gate Charge	V <sub>DS</sub> =-15V, I <sub>D</sub> =-5.3A, V <sub>GS</sub> =-10V	-	39	-	nC
Q <sub>gs</sub>	Gate-Source Charge		-	7	-	
Q <sub>gd</sub>	Gate-Drain Charge		-	11	-	
t <sub>d(on)</sub>	Turn-on Delay Time	V <sub>DD</sub> =-15V, R <sub>L</sub> =5Ω, I <sub>D</sub> =-3A, V <sub>GEN</sub> =-10V, R <sub>G</sub> =6Ω	-	15	-	nS
t <sub>r</sub>	Turn-on Rise Time		-	33	-	
t <sub>d(off)</sub>	Turn-off Delay Time		-	67	-	
t <sub>f</sub>	Turn-off Fall Time		-	21	-	
<b>• Drain-Source Diode Characteristics</b>						
V <sub>SD</sub>	Drain-Source Diode Forward	V <sub>GS</sub> =0V, I <sub>S</sub> =-2.0A	-	-	-1.3	V

Note: Pulse Test: Pulse Width ≤ 300us, Duty Cycle ≤ 2%



Switching Test Circuit and Switching Waveforms

### Typical Characteristics Curves (Ta=25°C, unless otherwise note)




Fig1. Typical Output Characteristics




Fig2. -VGS(TH) Gate -Source Voltage Vs. Tj




Fig3. Typical Transfer Characteristics




Fig4. Normalized On-Resistance Vs. Tj




Fig5. Typical Source-Drain Diode Forward Voltage




Fig6. Maximum Safe Operating Area




Fig7. Typical Capacitance Vs. Drain-Source Voltage




Fig8. Typical Gate Charge Vs. Gate-Source Voltage





Fig9. Normalized Maximum Transient Thermal Impedance

### SOP-8 PACKAGE OUTLINE DIMENSIONS



Symbol	Dimensions In Millimeters (MM)		Dimensions In Inches (MIL)	
	Min	Max	Min	Max
A	1.350	1.750	0.053	0.069
A1	0.100	0.250	0.004	0.010
A2	1.350	1.550	0.053	0.061
b	0.330	0.510	0.013	0.020
c	0.170	0.250	0.007	0.010
D	4.700	5.100	0.185	0.201
E	3.800	4.000	0.150	0.157
E1	5.800	6.200	0.228	0.244
e	1.270 (BSC)		0.050 (BSC)	
L	0.400	1.270	0.016	0.050
θ	0°	8°	0°	8°