
# Kingbright

### T-1 (3mm) RIGHT ANGLE LED INDICATOR



- 1. All dimensions are in millimeters (inches). 2. Tolerance is  $\pm 0.25(0.01")$  unless otherwise noted.
- 3. Lead spacing is measured where the leads emerge from the package.

4. Specifications are subject to change without notice.

REV NO: V.3 CHECKED: Allen Liu DATE:MAR/19/2005 DRAWN:H.Q.YUAN

### Kingbright

Selection Guide								
Part No.	Dice	Lens Type	lv (mcd) @ 10mA		Viewing Angle			
			Min.	Тур.	<b>2</b> θ <b>1/2</b>			
L-710A8CB/1GD	GREEN (GaP)	GREEN DIFFUSED	8	20	40 <b>°</b>			

Note:

1.  $\theta$ 1/2 is the angle from optical centerline where the luminous intensity is 1/2 the optical centerline value.

#### Electrical / Optical Characteristics at T<sub>A</sub>=25°C

Symbol	Parameter	Device	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	Green	565		nm	IF=20mA
λD	Dominant Wavelength	Green	568		nm	IF=20mA
Δλ1/2	Spectral Line Half-width	Green	30		nm	IF=20mA
С	Capacitance	Green	15		pF	VF=0V;f=1MHz
VF	Forward Voltage	Green	2.2	2.5	V	IF=20mA
IR	Reverse Current	Green		10	uA	VR = 5V

#### Absolute Maximum Ratings at TA=25°C

Parameter	Green	Units		
Power dissipation	105	mW		
DC Forward Current	25	mA		
Peak Forward Current [1]	140	mA		
Reverse Voltage	5	V		
Operating/Storage Temperature	-40°C To +85°C			
Lead Solder Temperature [2]	260°C For 3 Seconds			
Lead Solder Temperature [3]	260°C For 5 Seconds			


Notes:

1. 1/10 Duty Cycle, 0.1ms Pulse Width.

2. 2mm below package base.

3. 5mm below package base.

# Kingbright



REV NO: V.3 CHECKED: Allen Liu DATE:MAR/19/2005 DRAWN:H.Q.YUAN