



APPROVE SHEET

TO: 直流支撑电容 40uF±10%600V

Main Materials		Mark & Outline	
ITEMS	NAME		
Film	Metalized Polypropylene film		
Electrode	Tinned copper wire		
Epoxy	Flame-retardant Epoxy-White		
Case	Flame-retardant plastic case-grey		

Part No.	TYPE	Dimensions (mm)							NOTE
		W	H	T	P	P1	L	ΦD	
FC6072	MKP-FC 40μF K 600V.DC	42	45	30	37.5	20.3	6	1.2	

CUSTOMER CONFIRM			CSD OFFER		
APPOVED BY	CHECKED BY	STAMP	APPOVED BY	STAMP	MADE BY
					闫佳佳
DATE			DATE	2020-08-26	

SHENZHEN CRC NEW ENERGY CO., LTD

6th and 7th Floor R&D Building, Yanchuan North Industrial Park,
Songgang Town, Baoan District, Shenzhen, China

TEL: +86 - 0755 - 29948883 / 29948998 FAX: +86 - 0755 - 29948906 <http://www.csdcap.com>

Technical data

Rated capacitance	C_N	$40\mu F \pm 10\%$
Rated voltage	U_N	600V.DC
Non-recurrent surge voltage	U_s	1000V.DC
Maximum current	I_{rms}	18A
Series resistance	R_s	$\leq 6.1m\Omega$
Tangent of the loss	$\tan \delta$	≤ 0.0015 (100Hz)
Insulation Resistance	$C \times R_{is}$	$\geq 5000S$
Self inductance	L_e	$\leq 30nH$
Lowest operating temperature	Θ_{min}	-40°C
Maximum operating temperature	Θ_{max}	105°C
Operating humidity	RH	0~95%
Storage temperature	$\Theta_{storage}$	-40°C~105°C
Service life		100000h
Failure quota		<100Fit


Test data

Voltage test between terminals	V _{tt}	900V.DC/10S
过电压	1.1 UN (30% of on-load-dur.) 1.15 UN (30min/day) 1.2 UN (5min/day) 1.3 UN (1min/day) 1.5 UN (30ms every time, 1 000times during the life of the capacitor)	


Operating altitude		2000m (max)
Terminal tightening torque		—
Bottom tightening torque		—
Weight		—

Electrical Characteristics of Film Capacitor

1. Lifetime Expectancy




Life time Expectancy of charge temperature




Life time Expectancy of charge voltage


2. Temperature Characteristics



Capacitance vs. Temperature



Operation voltage vs. Temperature




Operation current vs. Temperature




(CR value) IR vs. Temperature

3. Frequency Characteristics



Capacitance vs. Frequency



Dissipation Factor vs. Frequency