

**SPECIFICATIONS**


Rated Current: 3.0AMP  
 Contact Resistance: 30mΩ Max  
 Withstand Voltage: 1000V AC/DC  
 Insulation Resistance: 1000MΩ Min  
 Operation Temperature: -40°C to +105°C

Contact Material: Brass  
 Contact Plating: Au or Sn Over Ni  
 Insulator Material: Polyester (UL94V-0)  
 Standard: PBT  
 Max. Processing Temp: 180°C for 30-60 seconds  
 (200°C for 10 seconds)

**Ordering Information**

35113 XX C M R S0 B N A 1

No. of Pins: 30~96PIN  
 Contact Type: M=male  
 Contact Plating: S0:Gold 1.5U" Flash/Tin  
 Packing: O=PE Bag, A=Tray



Dimension antitheses list	
ITEM	A
Standard	3.00
Alternate	

OPERATION		DRAW		SCALE		FIT		PART NO.	
XX	±0.30	liujianjun	17.05.31	UNIT	mm	A4	1/1	SHENZHEN JINLING ELECTRONIC CO.,LTD	
B	±0.20	CHECK		SIZE	A4			35113XXCMRSC0BNA1	
A0	±0.10			SHEET	1/1			深圳市锦凌电子有限公司	
REV	DATE	MODIFICATION DESCRIPTION	CHANGE	DIM	TOL	APPROVE	PROJ.	客户:	
1								歌式插座 公座 90度 NP 成品图	

**JILN** 深圳市锦凌电子有限公司  
 SHENZHEN JINLING ELECTRONIC CO.,LTD  
 Tel: 86-755-2997-5806/5802 Fax: 86-755-2997-5892