Property of Lite-On Only

SMD LAMP LED

OFFICE : 90 Chien I Road, Chung Ho Taipei, Taiwan, R.O.C. TEL : +886-2-2222-6181 FAX : +886-2-2226-5872

LTW-206DCG-BTH


DATASHEET (preliminary)

DATE	:	2013/08/27
REV. NO.	:	Version : A
PAGE	:	0 of 11

Features

- * Package in 12mm tape on 7" diameter reels.
- * Compatible with automatic placement equipment.
- * Compatible with infrared and vapor phase reflow solder process.
- * EIA STD package.
- * I.C. compatible.
- * Meet green product and Pb-free(According to RoHS)

Package Dimensions



Part No. : LTW-206DCG-BTH


11

Property of Lite-On Only

Absolute Maximum Ratings at Ta=25°C

Parameter	LTW-206DCG-BTH	Unit	
Power Dissipation	120	mW	
Peak Forward Current			
(1/10 Duty Cycle, 0.1ms Pulse Width)	100	mA	
DC Forward Current	30	mA	
Reverse Voltage	5	V	
Operating Temperature Range	-30°C to $+85^{\circ}\text{C}$		
Storage Temperature Range	-40° C to $+100^{\circ}$ C		
Reflow Soldering Condition	260°C For 10 Seconds		

Suggest IR Reflow Condition :



R-Reflow Soldering Profile for lead free soldering (Acc. to J-STD-020D)

Property of Lite-On Only

Electrical Optical Characteristics At Ta=25°C								
Parameter	Symbol	Part No. LTW-	Min.	Тур.	Max.	Unit	Test Condition	
Luminous Flux	Φv	206DCG-BTH	8.40		9.90	lm	IF = 20mA Note 1, 2, 5	
Viewing Angle	2 0 1/2	206DCG-BTH		120		deg	Fig.6	
Chromaticity Coordinates	Х	206DCG-BTH		0.29			IF = 20mA	
Chromaticity Coordinates	у	2000CG-DIH		0.28			Note 3, 5 Fig.1	
Forward Voltage	VF	206DCG-BTH	2.8		3.4	V	IF = 20mA Note 4	

Note : 1. Luminous flux is measured with a light sensor and filter combination that approximates the CIE eye-response curve.

2. Lm classification code is marked on each packing bag.

3. The chromaticity coordinates (x, y) is derived from the 1931 CIE chromaticity diagram.

4. The forward voltage should be added +/- 0.1 tolerance

5. CAS140B is the test standard for the chromaticity coordinates (x, y) & lm.

6. The chromaticity coordinates (x, y) guarantee should be added ± -0.01 tolerance.



Bin Code List

VF Spec. Table						
IV Bin	Forward Voltage	e (V) at IF = 20mA				
	Min.	Max.				
V1	2.8	2.9				
V2	2.9	3.0				
V3	3.0	3.1				
V4	3.1	3.2				
V5	3.2	3.3				
V6	3.3	3.4				

Tolerance on each Forward Voltage are +/- 0.1V.

Luminous Spec. Table						
		Flux (Im) a	t IF = 20mA			
IV Bin	lı	Im		cd		
	Min.	Max.	Min.	Max.		
83	8.40	8.70	2800	2900		
84	8.70	9.00	2900	3000		
91	9.00	9.30	3000	3100		
92	9.30	9.60	3100	3200		
93	9.60	9.90	3200	3300		

Tolerance on each Luminous Flux are +/- 10%, and IV (mcd) is for reference.


Page: 4 of

Property of Lite-On Only


Bin Code List

Color Ranks Table											
Donka	Color bin limits at IF = 20mA					Ranks	Color bin limits at IF = 20mA				
Naliks	Ranks CIE 1931Chromaticity coordinates				Naliks	CIE	1931Ch	romaticit	y coordii	nates	
A33	x	0.2850	0.2786	0.2820	0.2880		x	0.2820	0.2753	0.2786	0.2850
A33	у	0.2670	0.2561	0.2515	0.2620	A44	у	0.2720	0.2608	0.2561	0.2670
D11	x	0.2888	0.2820	0.2850	0.2914	Baa	x	0.2914	0.2850	0.2880	0.2940
B11	У	0.2833	0.2720	0.2670	0.2779	B22	у	0.2779	0.2670	0.2620	0.2725
C11	x	0.2950	0.2888	0.2914	0.2975	C22	x	0.2975	0.2914	0.2940	0.3000
CIT	у	0.2940	0.2833	0.2779	0.2885	622	у	0.2885	0.2779	0.2725	0.2830
C33	x	0.3035	0.2975	0.3000	0.3060	C44	x	0.3010	0.2950	0.2975	0.3035
633	у	0.2990	0.2885	0.2830	0.2935	C44	у	0.3045	0.2940	0.2885	0.2990
						ļ					

Tolerance on each Hue (x, y) bin is +/- 0.01.



Property of Lite-On Only



User Guide


Cleaning

Do not use unspecified chemical liquid to clean LED they could harm the package. If cleaning is necessary, immerse the LED in ethyl alcohol or isopropyl alcohol at normal temperature for less one minute.


Recommend Printed Circuit Board Attachment Pad

Infrared / vapor phase


Reflow Soldering



Package Dimensions of Tape







Notes:

- 1. Empty component pockets sealed with top cover tape.
- 2. 7 inch reel-2000 pieces per reel.
- 3. Minimum packing quantity is 500 pieces for remainders.
- 4. The maximum number of consecutive missing lamps is two.
- 5. In accordance with EIA-481-1-B specifications.

Property of Lite-On Only

CAUTIONS

1. Application

The LEDs described here are intended to be used for ordinary electronic equipment (such as office equipment, communication equipment and household applications).Consult Liteon's Sales in advance for information on applications in which exceptional reliability is required, particularly when the failure or malfunction of the LEDs may directly jeopardize life or health (such as in aviation, transportation, traffic control equipment, medical and life support systems and safety devices).

2. Storage

This product is qualified as Moisture sensitive Level 3 per JEDEC J-STD-020 Precaution when handing this moisture sensitive product is important to ensure the reliability of the product.

The package is sealed:

The LEDs should be stored at 30°C or less and 90%RH or less. And the LEDs are limited to use within one year, while the LEDs is packed in moisture-proof package with the desiccants inside.

The package is opened:

The LEDs should be stored at 30°C or less and 60%RH or less. Moreover, the LEDs are limited to solder process within 168hrs. If the Humidity Indicator shows the pink color in 10% even higher or exceed the storage limiting time since opened, that we recommended to baking LEDs at 60°C at least 48hrs. To seal the remainder LEDs return to package, it's recommended to be with workable desiccants in original package.

3. Cleaning

Use alcohol-based cleaning solvents such as isopropyl alcohol to clean the LED if necessary.


4. Soldering

Recommended soldering conditions:


Reflow soldering		Soldering iron	Soldering iron		
Pre-heat Pre-heat time Soldering Temp. Soldering time	120~150°C 120 sec. Max. 260°C Max. 30 sec. Max.	Temperature Soldering time	300°C Max. 3 sec. Max. (one time only)		

5. Drive Method

An LED is a current-operated device. In order to ensure intensity uniformity on multiple LEDs connected in parallel in an application, it is recommended that a current limiting resistor be incorporated in the drive circuit, in series with each LED as shown in Circuit A below.



Circuit model B



- (A) Recommended circuit.
- (B) The brightness of each LED might appear different due to the differences in the I-V characteristics of those LEDs.

Part No. : LTW-206DCG-BTH

Page: 9 of 11

Property of Lite-On Only

6. ESD (Electrostatic Discharge)

Static Electricity or power surge will damage the LED. Suggestions to prevent ESD damage:

- Use of a conductive wrist band or anti-Slectrostatic glove when handling these LEDs.
- All devices, equipment, and machinery must be properly grounded.
- Work tables, storage racks, etc. should be properly grounded.
- Use ion blower to neutralize the static charge which might have built up on surface of the LED's plastic lens as a result of friction between LEDs during storage and handling.

ESD-damaged LEDs will exhibit abnormal characteristics such as high reverse leakage current, low forward voltage, or "no lightup" at low currents.

To verify for ESD damage, check for "lightup" and Vf of the suspect LEDs at low currents.

The Vf of "good" LEDs should be >2.0V@0.1mA for InGaN product

7.1 Reliability Test

Test Condition	Reference Standard	Note	Number of Damaged
Tsld=245±5°C, 3sec. (Lead Free Solder)	JEITA ED-4701 300 303	1 time Over 95%	0/30
-30°C ~ 85°C 30min. 30min.	JEITA ED-4701 300 307	100 cycles	0/30
Ta=85℃	JEITA ED-4701 200 201	1000 hrs.	0/30
Ta=60°C, RH=90%	JEITA ED-4701 100 103	1000 hrs.	0/30
Ta=25°C, IF=20mA		1000 hrs.	0/30
Ta=85°C, IF=5mA		500 hrs.	0/30
60°C, RH=90%, IF=20mA		500 hrs.	0/30
Ta=-30°C, IF=20mA		1000 hrs.	0/30
	Tsld=245±5°C, 3sec. (Lead Free Solder) -30°C ~ 85°C 30min. 30min. Ta=85°C Ta=60°C, RH=90% Ta=25°C, IF=20mA Ta=85°C, IF=5mA 60°C, RH=90%, IF=20mA	Tsld=245 \pm 5°C, 3sec. JEITA ED-4701 300 303 -30°C ~ 85°C 30min. 30min. JEITA ED-4701 300 307 Ta=85°C JEITA ED-4701 200 201 Ta=60°C, RH=90% JEITA ED-4701 100 103 Ta=25°C, IF=20mA Image: Comparison of the second seco	Tsld=245 \pm 5°C, 3sec. (Lead Free Solder)JEITA ED-4701 300 3031 time Over 95%-30°C ~ 85°C 30min. 30min.JEITA ED-4701 300 307100 cyclesTa=85°CJEITA ED-4701 200 2011000 hrs.Ta=60°C, RH=90%JEITA ED-4701 100 1031000 hrs.Ta=25°C, IF=20mAI000 hrs.1000 hrs.Ta=85°C, IF=5mA500 hrs.500 hrs.

Property of Lite-On Only

7.2 Criteria for Judging the Damage

Itaan	Course had	Test Conditions	Criteria for Judgment				
Item	Symbol Test Conditions		Min.	Max.			
Forward Voltage	VF	IF=20mA	-	U.S.L.*) $ imes$ 1.1			
Luminous Intensity	IV	IF=20mA	U.S.L.**) $ imes$ 0.7	-			

8. Others

The appearance and specifications of the product may be modified for improvement without prior notice.

9. Suggested Checking List

Training and Certification

- 1. Everyone working in a static-safe area is ESD-certified?
- 2. Training records kept and re-certification dates monitored?

Static-Safe Workstation & Work Areas

- 1. Static-safe workstation or work-Sreas have ESD signs?
- 2. All surfaces and objects at all static-safe workstation and within 1 ft measure less than 100V?
- 3. All ionizer activated, positioned towards the units?
- 4. Each work surface mats grounding is good?

Personnel Grounding

1. Every person (including visitors) handling ESD sensitive (ESDS) items wear wrist strap, heel strap or conductive shoes with conductive flooring?

- 2. If conductive footwear used, conductive flooring also present where operator stand or walk?
- 3. Garments, hairs or anything closer than 1 ft to ESD items measure less than 100V*?
- 4. Every wrist strap or heel strap/conductive shoes checked daily and result recorded for all DLs?
- 5. All wrist strap or heel strap checkers calibration up to date?
 - Note: *50V for Blue LED.

Device Handling

- 1. Every ESDS items identified by EIA-471 labels on item or packaging?
- 2. All ESDS items completely inside properly closed static-shielding containers when not at static-safe workstation?
- 3. No static charge generators (e.g. plastics) inside shielding containers with ESDS items?

4. All flexible conductive and dissipative package materials inspected before reuse or recycle?

Others

- 1. Audit result reported to entity ESD control coordinator?
- 2. Corrective action from previous audits completed?
- 3. Are audit records complete and on file?

11