




MBR1020CT THRU MBR10200CT

10.0 AMP SCHOTTKY BARRIER RECTIFIERS



FEATURES

- * Low forward voltage drop
- * High current capability
- * High reliability
- * High surge current capability
- * Good for switching mode application



MECHANICAL DATA


- * Case: Molded plastic
- * Epoxy: UL 94V-0 rate flame retardant
- * Lead: Lead solderable per MIL-STD-202, method 208 guaranteed
- * Polarity: As Marked
- * Mounting position: Any

VOLTAGE RANGE

20 to 200 Volts

CURRENT

10.0 Amperes



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Rating 25°C ambient temperature unless otherwise specified.
Single phase half wave, 60Hz, resistive or inductive load.
For capacitive load, derate current by 20%.

TYPE NUMBER	MBR1020CT	MBR1045CT	MBR1060CT	MBR1080CT	MBR10100CT	MBR10150CT	MBR10200CT	UNITS	
Maximum Recurrent Peak Reverse Voltage	20	45	60	80	100	150	200	V	
Maximum RMS Voltage	14	32	42	56	70	105	140	V	
Maximum DC Blocking Voltage	20	45	60	80	100	150	200	V	
Maximum Average Forward Rectified Current									
at Tc=125°C								10	A
Peak Forward Surge Current, 8.3 ms single half sine-wave superimposed on rated load (JEDEC method)								150	A
Maximum Instantaneous Forward Voltage at 10A	0.55	0.7	0.85	0.92				V	
Maximum DC Reverse Current Ta=25°C								0.2	mA
at Rated DC Blocking Voltage Ta=100°C								50	mA
Typical Junction Capacitance (Note1)								420	pF
Typical Thermal Resistance RθJC (Note 2)								2.5	°C/W
Operating Temperature Range Tj								-65 — +150	°C
Storage Temperature Range Tstg								-65 — +150	°C

NOTES:

1. Measured at 1MHz and applied reverse voltage of 4.0V D.C.
2. Thermal Resistance Junction to Case.

RATING AND CHARACTERISTIC CURVES (MBR1020CT THRU MBR10200CT)

FIG.1-TYPICAL FORWARD CURRENT DERATING CURVE




FIG.2-TYPICAL FORWARD CHARACTERISTICS




FIG.3-MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT




FIG.5 - TYPICAL REVERSE CHARACTERISTICS




FIG.4-TYPICAL JUNCTION CAPACITANCE

