

PSBDC40V3

Schottky Barrier diode

Feature

- Ultra Small mold type. SMC
- Low IR
- High reliability.

Applications

Low current rectification

Construction

Silicon epitaxial planar

Mechanical Characteristics

- Lead finish:100% matte Sn(Tin)
- Mounting position: Any
- > Qualified max reflow temperature:260°C
- Device meets MSL 1 requirements
- Pure tin plating: 7 ~ 17 um
- ➢ Pin flatness∶≤3mil

Electrical characteristics per line@25°C

Parameter	Symbol	Min.	Тур.	Max.	Unit	Conditions
Forward voltage	VF	-	-	0.55	V	I⊧=3A
Reverse current	IR	-	-	0.5	mA	V _R =40V

Absolute maximum rating@25°C

Parameter	Symbol	limits	Unit
Reverse voltage (DC)	Vrm	40	V
Average rectified forward current	lo	3	A
Peak Forward Surge Current 8.3ms Single Half Sine Wave Superimposed on Rated Load	IFSM	80	А
Operating Junction temperature Range	Tj	-55 to 125	ĉ
Storage temperature	T _{stg}	-40 to +125	°C

Schottky Barrier diode

PSBDC40V3

Typical Characteristics




Fig 3.Total Capacitance


Schottky Barrier diode


PSBDC40V3

Solder Reflow Recommendation





Peak Temp=257°C, Ramp Rate=0.802deg. °C/sec





Bottom View





Suggested PCB Layout

Unit:mm

Schottky Barrier diode


PSBDC40V3


Dim	Millim	neters	Inches		
Dim	Min	Max	Min	Мах	
А	2.00	2.62	0.079	0.103	
E	6.50	7.00	0.256	0.276	
D	5.60	6.20	0.220	0.244	
E1	7.50	8.00	0.299	0.315	
A ₁	0.05	0.21	0.002	0.008	
С	0.15	0.31	0.006	0.012	
L	0.90	1.60	0.035	0.063	
b	2.75	3.25	0.108	0.128	

Ordering information

Device	Package	Reel	Shipping
PSBDC40V3	SMC (Pb-Free)	13"	3000 / Tape & Reel

Load with information





IMPORTANT NOTICE

and **Prisemi** are registered trademarks of **Prisemi Electronics Co., Ltd** (Prisemi), Prisemi reserves the right to make changes without further notice to any products herein. Prisemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Prisemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in Prisemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. Prisemi does not convey any license under its patent rights nor the rights of others. The products listed in this document are designed to be used with ordinary electronic equipment or devices, Should you intend to use these products with equipment or devices which require an extremely high level of reliability and the malfunction of with would directly endanger human life (such as medical instruments, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), please be sure to consult with our sales representative in advance.

Website: http://www.prisemi.com For additional information, please contact your local Sales Representative. ©Copyright 2009, Prisemi Electronics Prisemi[®] is a registered trademark of Prisemi Electronics. All rights are reserved.