

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS


Rating 25°C ambient temperature uniess otherwies specified. Single phase half wave, 60Hz, resistive or inductive load. For capacitive load, derate current by 20%.

TYPE NUMBER	S2AA	S2BA	S2DA	S2GA	S2JA	S2KA	S2MA	UNITS
Maximum Recurrent Peak Reverse Voltage	50	100	200	400	600	800	1000	V
Maximum RMS Voltage	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	50	100	200	400	600	800	1000	V
Maximum Average Forward Rectified Current		•					•	
at Ta=75°C	2.0							А
Peak Forward Surge Current, 8.3 ms single half sine-wave								
superimposed on rated load (JEDEC method)	50						А	
Maximum Instantaneous Forward Voltage at 2.0A	1.1					V		
Maximum DC Reverse Current Ta=25°C	5.0						μΑ	
at Rated DC Blocking Voltage Ta=100 °C	100							μA
Typical Junction Capacitance (Note 1)	60							рF
Typical Thermal Resistance R JA (Note 2)	47						°C/W	
Operating and Storage Temperature Range TJ, Tstc	-55-+150							°C

NOTES:

1. Measured at 1MHz and applied reverse voltage of 4.0V D.C.

2. Thermal Resistance from Junction to Ambient.



www.gk-goodwork.com.

KEV 1.0 2015 JAN PAGE:2/2