

DATASHEET

Top View LEDs 67-11/T1C-FV2W2F/2T



Features

- P-LCC-2 package.
- Fluorescence Type
- High Luminous Intensity
- High Efficiency
- Pb-free.
- The product itself will remain within RoHS compliant version.
- Compliance with EU REACH.
- Compliance Halogen Free .(Br<900ppm,Cl<900ppm,Br+Cl<1500ppm).
- Precondition: Bases on JEDEC J-STD 020D Level 3

Descriptions

• The The white LED which was fabricated using a blue LED and a phosphor, and the phosphor is excited by blue light and emits yellow fluorescence.

The mixture of blue light and yellow light results in a white emission.

Applications

- OA Equipment
- . Backlighting of Full Color LCD
- Automotive Equipment
- Replacement of Conventional Light Bulbs and Fluorescent Lamps



Device Selection Guide

Chip Materials	Emitted Color	Resin Color
InGaN	White	Yellowish

Absolute Maximum Ratings (Ta=25°C)

Parameter	Symbol	Rating	Unit
Reverse Voltage	V_R	5	V
Forward Current	l _F	25	mA
Peak Forward Current (Duty 1/10 @1KHz)	lfp	100	mA
Power Dissipation	Pd	110	mW
Junction Temperature	Tj	115	$^{\circ}\!\mathrm{C}$
Operating Temperature	Topr	-40 ~ +85	$^{\circ}\mathrm{C}$
Storage Temperature	Tstg	-40 ~ +90	$^{\circ}\mathbb{C}$
Electrostatic Discharge (HBM)	ESD	2000	V
Soldering Temperature	T_{sol}		: 260 ℃ for 10 sec. : 350 ℃ for 3 sec.

Electro-Optical Characteristics (Ta=25°C)

Parameter	Symbol	Min.	Тур.	Max.	Unit	Condition
Luminous Intensity	lv	900		2240	mcd	
Viewing Angle	20 _{1/2}		120		deg	I _F =20mA
Forward Voltage	VF	2.70		3.50	V	
Reverse Current	I_{R}			10	μΑ	V _R =5V

Note:

- 1. Tolerance of Luminous Intensity: ±11%
- 2. Tolerance of Dominant Wavelength: ±1nm
- 3. Tolerance of Forward Voltage: ±0.1V



Bin Range of Luminous Intensity

Bin Code	Min.	Max.	Unit	Condition
V2	900	1120		
W1	1120	1420	mcd	I- 20m A
W2	1420	1800		I _F =20mA
ВВ	1800	2240	-	


Tolerance of Luminous Intensity: ±11%

Bin Range of Forward Voltage

Group	Bin Code	Min.	Max.	Unit	Condition		
	10	2.70	2.90				
F	11	2.90	3.10		L 20m A		
F .	12	3.10	3.30	V	I _F =20mA		
	13	3.30	3.50				
Note: Tolerance of Forward Voltage: ±0.1V.							



The C.I.E. 1931 Chromaticity Diagram



Bin Range of Chromaticity Coordinates Specifications


Group	Bin Code	CIE_x	CIE_x	Bin Code	CIE_y	CIE_y	Condition
		0.287	0.295	— B5	0.296	0.276	IF=20mA
	В3	0.283	0.305		0.287	0.295	
	Б3	0.304	0.330		0.307	0.315	
F		0.307	0.315		0.311	0.294	
-	B4 -	0.307	0.315	— — В6	0.311	0.294	
		0.304	0.33		0.307	0.315	
		0.33	0.36		0.330	0.339	
		0.33	0.339		0.330	0.318	-


Note:


Tolerance of Chromaticity Coordinates: ±0.01.





Typical Electro-Optical Characteristics Curves


















Package Dimension



Note: Tolerances unless mentioned ±0.1mm. Unit = mm


Moisture Resistant Packing Materials

Label Explanation




- CPN: Customer's Product Number
- P/N: Product Number
- · QTY: Packing Quantity
- CAT: Luminous Intensity Rank
- HUE: Dom. Wavelength Rank
- · REF: Forward Voltage Rank
- · LOT No: Lot Number

Reel Dimensions



Note: Tolerance unless mentioned is ±0.1mm; Unit = mm


Carrier Tape Dimensions: Loaded Quantity 2000 pcs Per Reel



Notes:

- 1.Tolerances unless mentioned ±0.1mm. Unit = mm
- 2.Minimum packing amount is 250/500/1000/2000 pcs per reel

Moisture Resistant Packing Process




Note: Tolerances unless mentioned ±0.1mm. Unit = mm



Precautions for Use

1. Over-current-proof

1.1 Customer must apply resistors for protection, otherwise slight voltage shift will cause big current change (Burn out will happen).



2. Storage

- 2.1 Moisture proof bag should only be opened immediately prior to usage.
- 2.2 Environment should be less than 30°C and 60% RH when moisture proof bag is opened.
- 2.3 After opening the package MSL Conditions stated on page 1 of this spec should not be exceeded.
- 2.4 If the moisture sensitivity card indicates higher than acceptable moisture, the component should be baked at min. 60deg +/-5deg for 24 hours.

3. Soldering Condition


- 3.1 Pb-free solder temperature profile
- 3.2 Reflow soldering should not be done more than two times.
- 3.3 When soldering, do not put stress on the LEDs during heating.
- 3.4 After soldering, do not warp the circuit board.

4. Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than 350° C for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

5. Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.





Application Restrictions

High reliability applications such as military/aerospace, automotive safety/security systems, and medical equipment may require different product. If you have any concerns, please contact Everlight before using this product in your application. This specification guarantees the quality and performance of the product as an individual component. Do not use this product beyond the specification described in this document.

DISCLAIMER

- 1. EVERLIGHT reserves the right(s) on the adjustment of product material mix for the specification.
- 2. The product meets EVERLIGHT published specification for a period of twelve (12) months from date of shipment.
- 3. The graphs shown in this datasheet are representing typical data only and do not show guaranteed values.
- 4. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from the use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- 5. These specification sheets include materials protected under copyright of EVERLIGHT. Reproduction in any form is prohibited without obtaining EVERLIGHT's prior consent.
- This product is not intended to be used for military, aircraft, automotive, medical, life sustaining or life saving
 applications or any other application which can result in human injury or death. Please contact authorized
 Everlight sales agent for special application request.