



TOLERANCE:

Abbr.	TOLERANCE				
	P=0.5	P=0.8	P=1.0	P=1.25	P=2.54
P	±0.05	±0.08	±0.08	±0.10	±0.15
Pt	±0.08	±0.10	±0.10	±0.15	±0.20
W	±0.08	±0.10	±0.10	±0.20	±0.20
M	±0.08	±0.12	±0.12	±0.15	±0.20
Cw	±0.02	±0.03	±0.03	±0.03	±0.04
L	(30~100)±3, (101~300)±5, (301~600)±10, (Length more than 601mm)±15mm				

	Dimension
Ft±0.01	0.043
St±0.01	0.225

Tolerance of Cutting Tilt

RoHS Compliant

UL Style : 20706

Customer P/N	CviLux P/N	No. of Conductor	Dimension											Support Tape Color
			P	Pt	L	W	M	Cw	Ct±0.01	S1±1.0	S2±1.0	d1±2.0	d2±2.0	
	FFCE2009T2050CB-300	20	0.5	9.5	50	10.5	0.5	0.3	0.035	3.0	3.0	5.0	5.0	BLUE

Cvi Lux
2013.12.20
ISSUED

SYM	NAME	DATE	REVISIONS	APPROVED BY:	DATE	UNIT: mm	TITLE:				
4											
3				DRAWN BY: Fang	10/12-13'	TOLERANCE UNLESS OTHERWISE SPECIFIED	FLAT FLEXIBLE CABLE (TERMINAL TYPE : T2)	MATERIAL: SEE PRODUCT SPECIFICATION			
2			ENGINEER: Lan	10/12-13'							
1			CHECKED BY: Lian	10/12-13'				DRAWING NO. FFC002SF	FILE NO.	T213137-4A	
			APPROVED BY: Kenny	10/12-13'				CUST. CODE:	SCALE 1 / 1	SHEET 1 OF 1	

瀚荃股份有限公司
CviLux Corporation