


**TOLERANCE:**

Abbr.	TOLERANCE				
	P=0.5	P=0.8	P=1.0	P=1.25	P=2.54
P	±0.05	±0.08	±0.08	±0.10	±0.15
Pt	±0.08	±0.10	±0.10	±0.15	±0.20
W	±0.08	±0.10	±0.10	±0.20	±0.20
M	±0.08	±0.12	±0.12	±0.15	±0.20
Cw	±0.02	±0.03	±0.03	±0.03	±0.04
L	(30~100)±3, (101~300)±5, (301~600)±10, (Length more than 601mm)±15mm				



	Dimension
<b>Ft±0.01</b>	0.043
<b>St±0.01</b>	0.225

**RoHS Compliant**

**UL Style : 20706 105C 60V**

Customer P/N	CviLux P/N	No. of Conductor	Dimension										Support Tape Color	
			P	Pt	L	W	M	Cw	Ct±0.01	S1±1	S2±1	d1±2		d2±2
	FFCE3308T103000-300	33	0.5	16	30	17	0.5	0.3	0.05	4	4	8	8	BLUE
	FFCE3308T108000-300	33	0.5	16	80	17	0.5	0.3	0.05	4	4	8	8	BLU

4				DATE	UNIT: mm	TITLE:	瀚荃股份有限公司 CviLux Corporation
3			DRAWN BY: long	4/20-20*	TOLERANCE UNLESS OTHERWISE SPECIFIED	<b>FLAT FLEXIBLE CABLE (TERMINAL TYPE : T1)</b>	
2			ENGINEER: long	4/20-20*	.X ±	MATERIAL: SEE PRODUCT SPECIFICATION	DRAWING NO. FFC001SF FILE NO. T120096-4A
1			CHECKED BY: Kenny	4/20-20*	.XX ±	CUST. CODE:	
SYM	NAME	DATE	REVISIONS	APPROVED BY: Kenny	4/20-20*	.XXX ±	SCALE 1 / 1 SHEET 1 OF 1