# **CAN/CAN-FD Bus Protector**

# Low Capacitance ESD Protection Diode for CAN/CAN–FD Bus

The S/ESDONCAN1 has been designed to protect the CAN transceiver from ESD and other harmful transient voltage events. This device provides bidirectional protection for each data line with a single compact SOT-23 package, giving the system designer a low cost option for improving system reliability and meeting stringent EMI requirements.

#### Features

- 200 W Peak Power Dissipation per Line (8 x 20 µsec Waveform)
- Diode Capacitance Matching
- Low Reverse Leakage Current (< 100 nA)
- Low Capacitance High-Speed FlexRay Data Rates
- IEC Compatibility: IEC 61000-4-2 (ESD): Level 4
  - IEC 61000–4–4 (EFT): 50 A 5/50 ns
  - IEC 61000-4-5 (Lighting) 3.0 A (8/20 μs)
- ISO 7637-1, Nonrepetitive EMI Surge Pulse 2, 8.0 A (1 x 50 µs)
- ISO 7637–3, Repetitive Electrical Fast Transient (EFT) EMI Surge Pulses, 50 A (5 x 50 ns)
- Flammability Rating UL 94 V–0
- S Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC–Q101 Qualified and PPAP Capable
- These are Pb–Free Devices

#### **Typical Applications**

- Industrial
  - Smart Distribution Systems (SDS)
  - DeviceNet
- Automotive
  - Controlled Area Network CAN 2.1 / CAN FD
  - Low and High Speed CAN




## **ON Semiconductor®**

www.onsemi.com


### SOT-23 DUAL BIDIRECTIONAL VOLTAGE SUPPRESSOR 200 W PEAK POWER







#### MARKING DIAGRAM



(Note: Microdot may be in either location)

#### **ORDERING INFORMATION**

See detailed ordering and shipping information in the package dimensions section on page 2 of this data sheet.

#### MAXIMUM RATINGS (T<sub>J</sub> = 25°C, unless otherwise specified)

| Symbol | Rating  | Value            | Unit          |
|--------|---|------------------|---------------|
| PPK    | Peak Power Dissipation, 8 x 20 $\mu s$ Double Exponential Waveform (Note 1)           | 200              | W             |
| TJ     | Operating Junction Temperature Range  | –55 to 150       | °C            |
| TJ     | Storage Temperature Range   | –55 to 150       | °C            |
| TL     | Lead Solder Temperature (10 s)  | 260              | °C            |
| ESD    | Human Body Model (HBM)<br>Machine Model (MM)<br>IEC 61000-4-2 Specification (Contact) | 8.0<br>400<br>23 | kV<br>V<br>kV |

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Non-repetitive current pulse per Figure 1.

#### **ELECTRICAL CHARACTERISTICS** (T<sub>J</sub> = $25^{\circ}$ C, unless otherwise specified)

| Symbol           | Parameter                  | Test Conditions  | Min  | Тур  | Max  | Unit |
|------------------|----------------------------|--|------|------|------|------|
| V <sub>RWM</sub> | Reverse Working Voltage    | (Note 2)   | 24   | -    | -    | V    |
| $V_{BR}$         | Breakdown Voltage          | I <sub>T</sub> = 1 mA (Note 3)                         | 26.2 | -    | 32   | V    |
| I <sub>R</sub>   | Reverse Leakage Current    | V <sub>RWM</sub> = 24 V                                | -    | 15   | 100  | nA   |
| V <sub>C</sub>   | Clamping Voltage           | I <sub>PP</sub> = 1 A (8 x 20 μs Waveform)<br>(Note 4) | -    | 33.4 | 36.6 | V    |
| V <sub>C</sub>   | Clamping Voltage           | I <sub>PP</sub> = 3 A (8 x 20 μs Waveform)<br>(Note 4) | -    | 44   | 50   | V    |
| I <sub>PP</sub>  | Maximum Peak Pulse Current | 8 x 20 μs Waveform (Note 4)                            | -    | -    | 3.0  | А    |
| CJ               | Capacitance                | V <sub>R</sub> = 0 V, f = 1 MHz (Line to GND)          | -    | -    | 10   | pF   |
| ΔC               | Diode Capacitance Matching | V <sub>R</sub> = 0 V, 5 MHz (Note 5)                   | -    | 0.26 | 2    | %    |

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

 Surge protection devices are normally selected according to the working peak reverse voltage (V<sub>RWM</sub>), which should be equal or greater than the DC or continuous peak operating voltage level.

3.  $V_{BR}$  is measured at pulse test current I<sub>T</sub>.

4. Pulse waveform per Figure 1.

5. ∆C is the percentage difference between C<sub>J</sub> of lines 1 and 2 measured according to the test conditions given in the electrical characteristics table.

#### **ORDERING INFORMATION**


| Device          | Package             | Shipping <sup>†</sup> |
|-----------------|---------------------|-----------------------|
| ESDONCAN1LT1G   | SOT-23<br>(Pb-Free) | 3,000 / Tape & Reel   |
| SESDONCAN1LT1G* | SOT-23<br>(Pb-Free) | 3,000 / Tape & Reel   |
| ESDONCAN1LT3G   | SOT-23<br>(Pb-Free) | 10,000 / Tape & Reel  |
| SESDONCAN1LT3G* | SOT-23<br>(Pb-Free) | 10,000 / Tape & Reel  |

+For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

\*S Prefix for Automotive and Other Applications Requiring Unique Site and Control Change Requirements; AEC-Q101 Qualified and PPAP Capable.

#### **TYPICAL PERFORMANCE CURVES**

(T<sub>J</sub> = 25°C unless otherwise noted)



#### **APPLICATIONS**

#### Background

The Controller Area Network (CAN) is a serial communication protocol designed for providing reliable high speed data transmission in harsh environments. Surge protection diodes provide a low cost solution to conducted and radiated Electromagnetic Interference (EMI) and Electrostatic Discharge (ESD) noise problems. The noise immunity level and reliability of CAN transceivers can be easily increased by adding external surge protection diodes to prevent transient voltage failures. The ESDONCAN1 provides a surge protection solution for CAN data communication lines. The ESDONCAN1 is a low capacitance dual bidirectional surge protection device in a compact SOT-23 package especially suitable for CAN2.1 (CAN-FD). This device is based on Zener technology that optimizes the active area of a PN junction to provide robust protection against transient EMI surge voltage and ESD. The ESDONCAN1 has been tested to EMI and ESD levels that exceed the specifications of popular high speed CAN networks.

Honeywell and SDS are registered trademarks of Honeywell International Inc. DeviceNet is a trademark of Rockwell Automation.





© Semiconductor Components Industries, LLC, 2019

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor date sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use a a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor houteds for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries

#### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT:

#### TECHNICAL SUPPORT

ON Semiconductor Website: www.onsemi.com

Email Requests to: orderlit@onsemi.com

North American Technical Support: Voice Mail: 1 800–282–9855 Toll Free USA/Canada Phone: 011 421 33 790 2910 Europe, Middle East and Africa Technical Support: Phone: 00421 33 790 2910 For additional information, please contact your local Sales Representative