



P.C.B LAYOUT

Specifications :

- Voltage rating: 250VAC / DC
- Current rating: 1 A AC / DC
- Withstanding voltage: 300V AC/minute
- Temperature range: -40 to +105
- Insulation resistance: ≥ 500M Min
- Contact resistance: ≤ 20M Max
- Material: PA6T 94V-0
- Planting Category: 1U"Gold
- Reflow soldering temperature: 260 ± 5°C, 10s

X1322 W V S-2*XX J- C30 D55 E50
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- ① Series No.
- ② Category: W-wafer
- ③ Welding Board Angle: V-Stright 90 °
- ④ Welding Way: S-SMT
- ⑤ Row No -Pin No : XX- 2*01P-40P
- ⑥ Plastic height: J=1.0mm
- ⑦ Pin length:C=3.0mm
- ⑧ Pin length:D=5.5mm
- ⑨ Pin length:E=5.0mm

X1322WVS-2*XXJ-C30D55E50	PA6T 94V-0	Brass	1U"Gold	X1322F
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal

For and on behalf of
XKB INDUSTRIAL PRECISION CO., LIMITED
 香港星坤工業精密有限公司

△ X
 △ X
 △ X
 MARK

REVISIONS	DESCRIPTION	DATE	REVISED	APPROVED

Authorized Signature(s)

DSND		DATE		SCALE: N/A	MODEL TYPE: X1322WVS-2*XXJ-C30D55E50
DWN		DATE		VIEW:	PART NO.:
CHKD		DATE		UNIT: mm	1.27mm Crimp Style Connectors
APPD		DATE		SIZE: A4	DWG NO.:

XKB INDUSTRIAL PRECISION CO., LIMITED

WEIGHT	SHEET	REVISION
1.0g	1/1	A0