



TOLERANCE:

Abbr.	TOLERANCE				
	P=0.5	P=0.8	P=1.0	P=1.25	P=2.54
P	±0.05	±0.08	±0.08	±0.10	±0.15
Pt	±0.08	±0.10	±0.10	±0.15	±0.20
W	±0.08	±0.10	±0.10	±0.20	±0.20
M	±0.08	±0.12	±0.12	±0.15	±0.20
Cw	±0.02	±0.03	±0.03	±0.03	±0.04
L	(30~100)±3, (101~300)±5, (301~600)±10, (Length more than 601mm)±15mm				

	Dimension
Ft±0.01	0.043
St±0.01	0.165

Tolerance of Cutting Tilt

RoHS Compliant

UL Style : 20706

Customer P/N	CviLux P/N	No. of Conductor	Dimension										Support Tape Color	
			P	Pt	L	W	M	Cw	Ct±0.01	S1±1.0	S2±1.0	d1±2.0		d2±2.0
	FFCC2404T108000-300	24	1.0	23.0	80	25.0	1.0	0.7	0.1	5.0	5.0	10.0	10.0	Blue
	FFCC2404T115000-300	24	1.0	23.0	150	25.0	1.0	0.7	0.1	5.0	5.0	10.0	10.0	Blue

4					DATE	UNIT: mm	TITLE:	瀚荃股份有限公司 CviLux Corporation
3				DRAWN BY: Marry	3/15-10	TOLERANCE UNLESS OTHERWISE SPECIFIED	FLAT FLEXIBLE CABLE (TERMINAL TYPE : T1)	
2				ENGINEER: Feng	3/15-10	.X ±	MATERIAL: SEE PRODUCT SPECIFICATION	DRAWING NO. FFC001SF FILE NO. T110111-2A
1				CHECKED BY: Feng	3/15-10	.XX ±	CUST. CODE: ACL1058	
SYM	NAME	DATE	REVISIONS	APPROVED BY: Justin	3/15-10	.XXX ±		SCALE 1 / 1 SHEET 1 OF 1

ENGINEERING
2010.03.16
ISSUED