


TOLERANCE:

Abbr.	TOLERANCE				
	P=0.5	P=0.8	P=1.0	P=1.25	P=2.54
P	±0.05	±0.08	±0.08	±0.10	±0.20
Pt	±0.08	±0.10	±0.10	±0.15	+0.2 -0.4
W	±0.08	±0.10	±0.10	±0.20	+0.2 -0.4
M	±0.08	±0.12	±0.12	±0.20	±0.30
Cw	±0.02	±0.03	±0.03	±0.03	±0.04
L	(30~100)±3, (101~300)±5, (301~600)±10, (Length more than 601mm)±15mm				



	Dimension
<b>Ft±0.01</b>	0.043
<b>St±0.01</b>	0.225

RoHS Compliant

UL Style : 20706

Customer P/N	CviLux P/N	No. of Conductor	Dimension										Support Tape Color	
			P	Pt	L	W	M	Cw	Ct±0.01	S1±1.0	S2±1.0	d1±2.0		d2±2.0
	FFCE1008T1035CC-300	10	0.5	4.5	35.0	5.5	0.5	0.3	0.05	3.0	3.0	6.0	6.0	BLUE

4						DATE	UNIT: mm	TITLE:	瀚荃股份有限公司 CviLux Corporation
3					DRAWN BY: Jack	9/2-08'	TOLERANCE UNLESS OTHERWISE SPECIFIED	<b>FLAT FLEXIBLE CABLE (TERMINAL TYPE : T1)</b>	
2					ENGINEER: Lara	9/2-08'	.X ±	X' ± 2'	MATERIAL: SEE PRODUCT SPECIFICATION
1					CHECKED BY: Leno	9/2-08'	.XX ±	.X' ±	DRAWING NO. FFC001SF
SYM	NAME	DATE	REVISIONS	APPROVED BY: William	9/2-08	.XXX ±	.XX' ±	CUST. CODE: HL0014	FILE NO. T108142-2A
									SCALE 1 / 1
									SHEET 1 OF 1

