

Description

The ESD5B5CL is designed to protect voltage sensitive components from ESD and transient voltage events. Excellent clamping capability, low leakage, and fast response time, make these parts ideal for ESD protection on designs where board space is at a premium. Because of its small size, it is suited for use in cellular phones, portable devices, digital cameras, power supplies and many other portable applications where board space comes at a premium. Also because of its low capacitance, it is suited for use in high frequency designs such as USB 2.0 high speed, VGA, DVI, SDI and other high speed line applications.


Features

- Protects one data line
- Ultra low leakage: nA level
- Low operating voltage: 5V
- Low clamping voltage
- Complies with following standards:
 - IEC 61000-4-2 (ESD) immunity test Air discharge: ±25kV

Contact discharge: ±22kV

- IEC61000-4-5 (Lightning) 2.5A (8/20µs)
- RoHS Compliant

Dimensions and Pin Configuration



Circuit and Pin Schematic

Mechanical Characteristics

- Package: SOD-523
- Lead Finish: Matte Tin
- Case Material: "Green" Molding Compound.
- UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 3 per J-STD-020
- Terminal Connections: See Diagram Below
- Marking Information: See Below

Applications

- Cellular Handsets and Accessories
- Personal Digital Assistants
- Notebooks and Handhelds
- Portable Instrumentation
- Digital Cameras
- Peripherals
- Audio Players
- Keypads, Side Keys, LCD Displays

Marking information



Details marking code reference customer approval list

Ordering Information


Part Number	Packaging	Reel Size
ESD5B5CL	3000/Tape & Reel	7 inch


Absolute Maximum Ratings (T_A=25°C unless otherwise specified)

Parameter	Symbol	Value	Unit
Peak Pulse Power (8/20µs)	Ppk	30	W
Peak Pulse Current (8/20µs)	Ірр	2.5	A
ESD per IEC 61000-4-2 (Air)		±25	
ESD per IEC 61000-4-2 (Contact)	VESD	±22	kV
Operating Temperature Range	TJ	-55 to +125	°C
Storage Temperature Range	Tstg	−55 to +150	°C

Electrical Characteristics (T_A=25°C unless otherwise specified)

Parameter	Symbol	Min	Тур	Мах	Unit	Test Condition
Reverse Working Voltage	VRWM			5	V	
Breakdown Voltage	Vbr	6		8	V	IT = 1mA
Reverse Leakage Current	I _R			0.2	μA	VRWM = 5V
Clamping Voltage	Vc		8.5	9	V	IPP = 1A (8 x 20µs pulse)
Clamping Voltage	Vc		10	12	V	IPP = 2.5A (8 x 20µs pulse)
Junction Capacitance	Сл		5		pF	VR = 0V, f = 1MHz






Integrated in OVP&OCP products


provider

orated


Junction Capacitance vs. Reverse Voltage




Clamping Voltage vs. Peak Pulse Current




8 X 20µs Pulse Waveform



Peak Pulse Power vs. Pulse Time



Power Derating Curve




8 kV Contact per IEC61000-4-2




Soldering parameters

Reflow Conditi	on	Pb-Free assembly (see FIG.2)		
Pre Heat	-Temperature Min (T _{s(min)})	+150℃		
	-Temperature Max(T _{s(max)})	+200 ℃		
	-Time (Min to Max) (ts)	60-180 secs.		
Average ramp	up rate (Liquid us Temp (T_L) to peak)	3℃/sec. Max		
$T_{s(max)}$ to T_L - R	amp-up Rate	3℃/sec. Max		
Reflow	-Temperature(T _L) (Liquid us)	+217℃		
	-Temperature(t _∟)	60-150 secs.		
Peak Temp (Tp)	+260(+0/-5) ℃		
Time within 5°C	C of actual Peak Temp (tp)	30 secs. Max		
Ramp-down Ra	ate	6℃/sec. Max		
Time 25℃ to P	eak Temp (T _P)	8 min. Max		
Do not exceed		+260°C		






Package mechanical data



	[DIMEN	SIONS		
DIM∾	INC	HES	M	NOTE	
	MIN	MAX	MIN	MAX	NOTE
А	.043	.051	1.10	1.30	_
В	.028	.035	0.70	0,90	-
С	.059	.067	1.50	1.70	1000
D	.020	.028	0.50	0.70	-
Е	.010	.014	0.25	0.35	0.000
F	.004	.008	0.10	0.20	_
G	.020	.028	0.50	0.70	-

1 CONTROLLING DIMENSION: MILLIMETERS

Suggested Land Pattern



DIMENSIONS						
DIMℕ	INCHES		N	NOTE		
	MIN	MAX	MIN	MAX	NUIE	
С	—	.067		1.70	REF	
G	-	.043	_	1.10	-	
Х	_	.031	_	0.80	REF	
Y	-	.024	_	0.60		
Ζ	—	.091	_	2.30		

1 CONTROLLING DIMENSION: MILLIMETERS

Contact information

WPMTEK Incorporated Limited

Floor 1 Building 4#, Binxianghua Industry Park, No.7,

Huada Road, Hualian Community, Longhua New District, Shenzhen

TEL: 86755-29308003 FAX: 86755-23739900

wpmtek Incorporated Limited (WPM) reserves the right to make changes to the product specification and data in this document without notice. WPM makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does WPM assume any liability arising from the application or use of any products or circuits, and specifically dis- claims any and all liability, including without limitation special, consequential or incidental damages.