

#### **Description**

The WPE0521PZ is designed to protect voltage sensitive components from ESD. Excellent clamping capability, low leakage, and fast response time provide best in class protection on designs that are exposed to ESD. Because of its small size, it is suited for use in cellular phones, MP3 players, digital cameras and many other portable applications where board space comes at a premium. It has been specifically designed to protect sensitive components which are connected to data and transmission lines from overvoltage caused by ESD(electrostatic discharge), and EFT (electrical fast transients).

### **Features**

■ Ultra small package: 1.0x0.6x0.5mm

■ Protects one data or power line

Ultra low leakage: nA level

Working voltage: 5V

Low clamping voltage

■ 2-pin leadless package

Complies with following standards:

- IEC 61000-4-2 (ESD) immunity test


Air discharge: ±30kV


Contact discharge: ±30kV

- IEC61000-4-5(Surge) 8A (8/20us)

RoHS Compliant

### **<u>Dimensions & Symbol</u>** (Unit: mm Max)





#### **Mechanical Characteristics**

■ Package: DFN1006-2 (1.0×0.6×0.5mm)

■ Lead Finish: NiPdAu

■ Case Material: "Green" Molding Compound.

■ Moisture Sensitivity: Level 3 per J-STD-020

Terminal Connections: See Diagram Below

Marking Information: See Below

### **Applications**

■ Data Line: USB1.0 &VGA

Serial and Parallel Ports

Notebooks and Handhelds

Cellular handsets and accesssories

Protable instrumentation

Peripherals

### **Marking information**



Details marking code reference specification of approval list

# Ordering Information

Part Number	Packaging	Reel Size
WPE0521PZ	10000/Tape & Reel	7 inch



### Absolute maximum ratings (T<sub>A</sub>=25°C, RH=45%-75%, unless otherwise noted)

Parameter	Symbol	Value	Unit	
Peak Pulse Power(tp=8/20uS waveform)	P <sub>PP</sub>	100	W	
Peak Pulse Current(tp=8/20uS waveform)	I <sub>PP</sub>	8	А	
ESD per IEC 61000-4-2 (Air)		±30		
ESD per IEC 61000-4-2 (Contact)	VESD	±30	kV	
Operating Temperature Range	TJ	-55 to +125	°C	
Storage Temperature Range	Tstg	-55 to +150	°C	


### **Electrical characteristics** (T<sub>A</sub>=25°C)


Parameter	Symbol	Min	Тур	Max	Unit	Test Condition
Reverse Working Voltage	VRWM			5.0	V	
Breakdown Voltage	VBR	6			V	IT = 1mA
Reverse Leakage Current	I <sub>R</sub>			0.2	μA	VRWM = 5.0V
Clamping Voltage	Vc		7	8	V	IPP = 1A (8 x 20µs pulse)
Clamping Voltage	Vc		10	12	V	IPP = 8A (8 x 20µs pulse)
Junction Capacitance	Сл		15	18	pF	VR = 0V, f = 1MHz

Rev.N\_Aug,2016 - 2 - www.wpmtek.com




### Typical Performance Characteristics (T<sub>A</sub>=25°C unless otherwise Specified)







Junction Capacitance vs. Reverse Voltage




Peak Pulse Power vs. Pulse Time



Clamping Voltage vs. Peak Pulse Current (tp =  $8/20\mu$ s)



**Power Derating Curve** 




8 X 20µs Pulse Waveform

ESD Clamping Voltage 8 kV Contact per IEC61000-4-2



## **Soldering parameters**

Reflow Conditi	on	Pb-Free assembly (see FIG.2)	
	-Temperature Min (T <sub>s(min)</sub> )	+150℃	
Pre Heat	-Temperature Max(T <sub>s(max)</sub> )	+200℃	
	-Time (Min to Max) (ts)	60-180 secs.	
Average ramp	up rate (Liquid us Temp (T <sub>L</sub> ) to peak)	3℃/sec. Max	
T <sub>s(max)</sub> to T <sub>L</sub> - R	amp-up Rate	3℃/sec. Max	
Reflow	-Temperature(T <sub>L</sub> ) (Liquid us)	<b>+217</b> ℃	
	-Temperature(t∟)	60-150 secs.	
Peak Temp (Tp	b)	+260(+0/-5)°C	
Time within 5°	C of actual Peak Temp (t <sub>p</sub> )	30 secs. Max	
Ramp-down R	ate	6℃/sec. Max	
Time 25°C to P	Peak Temp (T <sub>P</sub> )	8 min. Max	
Do not exceed		+260℃	




### Package mechanical data

	DIMENSIONS				
SYM	MILLIMETERS	INCHES			


Rev.N\_Aug,2016 - 4 - www.wpmtek.com





	MIN	NOM	MAX	MIN	NOM	MAX
Α	0.45	0.50	0.55	0.018	0.020	0.022
A1	0.00	0.02	0.05	0.000	0.001	0.002
b	0.45	0.50	0.55	0.018	0.020	0.022
С	0.12	0.15	0.18	0.005	0.006	0.007
D	0.95	1.00	1.05	0.037	0.039	0.041
е	0.65 BSC				0.026	BSC
Е	0.55	0.60	0.65	0.022	0.024	0.026
L	0.20	0.25	0.30	0.008	0.010	0.012
h	0.07	0.12	0.17	0.003	0.005	0.007

#### **Suggested Land Pattern**



	DIMENSIONS			
SYM	MILLIMETERS	INCHES		
Χ	0.60	0.024		
Y1	0.50	0.020		
Y2	0.30	0.012		
Y3	0.80	0.032		
Z	1.30	0.052		

### **Contact information**

WPMTEK Incorporated Limited

Room 207,2nd Floor, Block 3,Minxing Industry Park, Minzhi,

Longhua New District, Shenzhen, PRC.

TEL: 86755-29308003 FAX: 86755-23739900

wpmtek Incorporated Limited (WPM) reserves the right to make changes to the product specification and data in this document without notice. WPM makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does WPM assume any liability arising from the application or use of any products or circuits, and specifically dis- claims any and all liability, including without limitation special, consequential or incidental damages.