

SPECIFICATIONS

RK14K1220D22


ELECTRICAL

1. Total resistance : 100 kΩ ± 20%
2. Rated power : 0.05 W
3. Rated voltage :
 The rated voltage shall be the voltage of D.C. or A.C. (commercial frequency, effective value) corresponding to the rated power (dissipation), and be obtained from the following formula. When the obtained rated voltage exceeds the maximum working voltage given in the following, however, the maximum working voltage of the following shall be the rated voltage.

$$E = \sqrt{P \cdot R} \text{ (V)}$$
 Where E : Rated voltage (V)
 P : Rated power (dissipation) (W)
 R : Nominal total resistance (Ω)
 Maximum working voltage : 50 V A.C.
 This potentiometer is designed for A.C. voltage only.
4. Resistance taper : "SPECIAL W" (K142-W04)
5. Tap resistance between terminals : 1 & 4 : 50kΩ ± 30 %
6. Tap residual resistance between terminals : 2 & 4 : 1 kΩ max.
7. Residual resistance between terminals : 1 & 2 : 100 Ω max.
 2 & 3 : 100 Ω max.
8. Tap position : 150° ± 5°
9. Sliding noise : Less than 250 mV. (Measured by JIS C 6443)
 (Except click point)
10. Insulation resistance : More than 100 MΩ at 250V D.C.
11. Withstand voltage: 300V A.C. for one minute.
12. Gang error : Not specified.

MECHANICAL

1. Total rotational angle : 300° ± 5°
2. Rotational torque : 3~20 mN·m (Rotational speed 60°/sec.)
3. Resistance to soldering heat :
 After soldering (Less than 350°C and within 3 seconds) there shall be no evidence of poor contact between resistance element and terminals, or any physical damages as a result of the test.
4. Stopper strength : No damage with an application of 0.6N·m.
5. Robustness after soldering resistor shaft against end thrust and pull force :
 With the potentiometer mounted, no damage with 80N of push and pull force.
6. Robustness at shaft against side thrust :
 With the potentiometer mounted, no damage with 30N of thrust force to the shaft top.
7. Shaft play :
 After installing the potentiometer, the resistor shall be mounted by soldering the mounting legs on the panel. When a side thrust of 50mN·m shall be applied at the end of the shaft, the total shaft play shall not exceed 0.7XL/30 mm p-p.
 (L: Shaft length)
8. Bushing nut tightening strength : Tightening torque to be no greater than 1N·m.
 Pay attention otherwise the strength may not be assured.
9. Click position : 150° ± 5°
10. Click torque : Rotational torque + (3~30mN·m)



ENDURANCE

1. Rotational life : 15,000 cycles min.


NOTE

1. The items except above mentioned items shall meet or exceed JIS C 6443.
2. Operating temperature : -10°C~+70°C.
3. Storage temperature : -30°C~+70°C.

ALPS ELECTRIC CO., LTD.				
				TITLE
		APPD.	CHKD.	DSGD.
				DOCUMENT NO.
				5K142CD01BC
SYMB	DATE	APPD	CHKD	DSGD




ALPS ELECTRIC CO., LTD
1-7 YUKIGAYA OTSUKA-CHO OTA-KU TOKYO JAPAN




TAP POSITION; 150° (TAP RESISTANCE BETWEEN TERMS: 1-4; 50kΩ ±30%)
 TAP RESISTANCE; 50%
 AT 90°±5° C.W. SHAFT ROTATION FROM FULL C.C.W. POSITION VOLTAGE PERCENT SHALL FALL WITHIN THE LIMITS OF 1 ~ 7 PERCENT.
 AT 210°±5°-----93~99%.

					DSGD EL ㄱ		
					T. SHIOYA 87-06-29		
					CHKD. k. Magami 87-06-29		TITLE RESISTANCE TAPER
					APPD. M. Inoue 87-6-29	UNIT m m	DOCUMENT NO. K142 - W04
SYMB	DATE	APPD	CHKD	DSGD			


OR



フラット部はφ6^{-0.05}
φ6^{-0.05} WITHIN
THIS LENGTH.



シャ-シ止め
使用不可
NOT FOR
PLACING



軸はセンタークリック位置を示す


SHAFT SHOWN IN
CENTER CLICK POSITION.

取付穴寸法図 (公差±0.1)


*挿入側からみた図

P.W.B. MOUNTING DETAIL
(TOLERANCE±0.1)

VIEWED FROM MOUNTING SIDE



軸は反時計方向に
回しまった状態を示す
SHAFT SHOWN
IN FULL C.C.W.
POSITION.



回路図
CIRCUIT

外側 OUTER R1 ①②③④
内側 INNER R2 1 2 3 4

P.W.B. 板厚 T=1.6

指定なき部分の許容差 TOLERANCES UNLESS OTHERWISE SPEC	
$L \leq 10$	±0.3
$10 < L < 100$	±0.5
$100 \leq L$	±0.8
角度 ANGULAR DIMENSION	±5°

								1T独立、4T共通									
PART NO.		NAME		MATERIAL NAME / CODE				FINISH									
ALPS ELECTRIC CO., LTD.																	
DSGD.				Y. OHYA 2008-03-13				SCALE				NO.					
CHKD.								TITLE				FIGURE					
Origin. 1990-10-13				S.A		M.F.R.O		UNIT				DOCUMENT NO.					
SYMB		DATE		APPD		CHKD		DSGD		m m				K142COG34			
				U. Shimizu 2008-03-14													

OR