# EVERLIGHT

# DATASHEET

# SMD • B 11-22/R6G6C-A31/2T



### **Features**

- Package in 8mm tape on 7" diameter reel.
- Compatible with automatic placement equipment.
- · Compatible with infrared and vapor phase reflow solder process.
- Multi-color type.
- Pb-free.
- The product itself will remain within RoHS compliant version.
- Compliance with EU REACH.
- Compliance Halogen Free .(Br <900 ppm ,Cl <900 ppm , Br+Cl < 1500 ppm).

### Description

- The 11-22 SMD LED is much smaller than lead frame type components, thus enable smaller board size, higher packing density, reduced storage space and finally smaller equipment to be obtained.
- Besides, lightweight makes them ideal for miniature applications. etc.

## Applications

- Backlighting in dashboard and switch.
- Telecommunication: indicator and backlighting in telephone and fax.
- Flat backlight for LCD, switch and symbol.
- General use.

## **Device Selection Guide**

Code	Chip Materials	Emitted Color	Resin Color	
R6	AlGaInP	Brilliant Red	Weter Clear	
G6	AlGaInP	Brilliant Yellow Green	<ul> <li>Water Clear</li> </ul>	

# Absolute Maximum Ratings (Ta=25℃)

Parameter	Symbol	Code	Rating	Unit	
Reverse Voltage	V <sub>R</sub>		5	V	
E	l <sub>F</sub>	R6	25		
Forward Current		G6	25	— mA	
Peak Forward Current	I <sub>FP</sub>	R6	60		
(Duty 1/10 @1KHz)		G6	60	— mA	
E	Pd	R6	60		
Power Dissipation		G6	60	— mW	
Electrostatic Discharge	ESD <sub>HBM</sub>		2000	V	
Operating Temperature	T <sub>opr</sub>		-40 ~ +85	°C	
Storage Temperature	Tstg		-40 ~ +90	°C	
Soldering Temperature	Tsol		Reflow Soldering : 260 $^\circ\!\mathrm{C}$ for 10 sec. Hand Soldering : 350 $^\circ\!\mathrm{C}$ for 3 sec.		

# Electro-Optical Characteristics (Ta=25°C)

Parameter	Symbol	Code	Min.	Тур.	Max.	Unit	Condition
Luminous Intensity	lv	R6	285		565	– mcd	
		G6	112		225		
Viewing Angle	20 <sub>1/2</sub>			60		deg	
Peak Wavelength	λр	R6		632		– nm	 I <sub>F</sub> =20mA 
		G6		575			
Dominant Wavelength	λd	R6		624		– nm	
		G6		573			
Spectrum Radiation Bandwidth	Δλ -	R6		20		- nm	
		G6		20			
Forward Voltage	V <sub>F</sub> —	R6	1.7	2.0	2.4	- V	
		G6	1.7	2.0	2.4		
Reverse Current	I <sub>R</sub>	R6			10	– μΑ	V <sub>R</sub> =5V
		G6			10		

Note:


1. Tolerance of Luminous Intensity: ±11%

# Bin Range of Luminous Intensity


Rb				
Bin Code	Min.	Max.	Unit	Condition
T1	285	360		
T2	360	450	mcd	I <sub>F</sub> =20mA
U1	450	565		
G6				
Bin Code	Min.	Max.	Unit	Condition
R1	112	140		
R2	140	180	mcd	I <sub>F</sub> =20mA
S1	180	225		




# Typical Electro-Optical Characteristics Curves R6




# Typical Electro-Optical Characteristics Curves G6






EVERLIGHT

# **Package Dimension**




Note: Tolerances unless mentioned ±0.1mm. Unit = mm

# Moisture Resistant Packing Materials Label Explanation




- CPN: Customer's Product Number
- P/N: Product Number
- QTY: Packing Quantity
- CAT: Luminous Intensity Rank
- HUE: Chromaticity Coordinates & Dom. Wavelength Rank
- REF: Forward Voltage Rank
- · LOT No: Lot Number

### **Reel Dimensions**



Note: The tolerances unless mentioned is  $\pm 0.1$  mm ,Unit = mm

## Carrier Tape Dimensions: Loaded quantity 2000 PCS per reel




Note: The tolerances unless mentioned is  $\pm 0.1$ mm ,Unit = mm

## **Moisture Resistant Packaging**





5



Label

Aluminum moisture-proof bag



#### **Precautions For Use**

1. Over-current-proof

Customer must apply resistors for protection, otherwise slight voltage shift will cause big

current change ( Burn out will happen ).

2. Storage

2.1 Do not open moisture proof bag before the products are ready to use.

2.2 After opening the package: The LEDs should be kept at  $30^{\circ}$ C or less and 60%RH or less.


2.3 The LEDs should be used within 168 hours (7days) after opening the package .

If unused LEDs remain, it should be stored in moisture proof packages.

2.4 If the moisture absorbent material (silica gel) has faded away or the LEDs have exceeded the storage time, baking treatment should be performed using the following conditions. Baking treatment :  $60\pm5^{\circ}$ C for 24 hours.

3. Soldering Condition

3.1 Pb-free solder temperature profile




3.4 After soldering, do not warp the circuit board.

#### 4.Soldering Iron

Each terminal is to go to the tip of soldering iron temperature less than  $350^{\circ}$ C for 3 seconds within once in less than the soldering iron capacity 25W. Leave two seconds and more intervals, and do soldering of each terminal. Be careful because the damage of the product is often started at the time of the hand solder.

#### 5.Repairing

Repair should not be done after the LEDs have been soldered. When repairing is unavoidable, a double-head soldering iron should be used (as below figure). It should be confirmed beforehand whether the characteristics of the LEDs will or will not be damaged by repairing.



# EVERLIGHT

## **Application Restrictions**

High reliability applications such as military/aerospace, automotive safety/security systems, and medical equipment may require different product. If you have any concerns, please contact Everlight before using this product in your application. This specification guarantees the quality and performance of the product as an individual component. Do not use this product beyond the specification described in this document.



## DISCLAIMER

- 1. EVERLIGHT reserves the right(s) on the adjustment of product material mix for the specification.
- 2. The product meets EVERLIGHT published specification for a period of twelve (12) months from date of shipment.
- 3. The graphs shown in this datasheet are representing typical data only and do not show guaranteed values.
- 4. When using this product, please observe the absolute maximum ratings and the instructions for using outlined in these specification sheets. EVERLIGHT assumes no responsibility for any damage resulting from the use of the product which does not comply with the absolute maximum ratings and the instructions included in these specification sheets.
- 5. These specification sheets include materials protected under copyright of EVERLIGHT. Reproduction in any form is prohibited without obtaining EVERLIGHT's prior consent.
- 6. This product is not intended to be used for military, aircraft, automotive, medical, life sustaining or life saving applications or any other application which can result in human injury or death. Please contact authorized Everlight sales agent for special application request.

