50 kPa on-chip temperature compensated and calibrated silicon pressure sensors

The MPX2053 series devices are silicon piezoresistive pressure sensors that provide a highly accurate and linear voltage output directly proportional to the applied pressure. A single, monolithic silicon diaphragm with the strain gauge and an integrated thin-film resistor network. Precise span and offset calibration with temperature compensation are achieved by laser trimming.

Features

- Temperature compensated Over 0°C to +85°C
- Easy-to-Use chip carrier package options
- · Ratiometric to supply voltage
- · Gauge ported and non-ported options
- Available in easy-to-use tape and reel
- · Differential and gauge pressure options

MPX2053 Series

0 to 50 kPa (0 to 7.25 psi) 40 mV Full Scale (Typical)

Application Examples

- Pump/Motor control
- Robotics
- Level detectors
- · Medical diagnostics
- Pressure switching
- Blood pressure measurement

ORDERING INFORMATION								
Device Name	Case No.		# of Ports			Pressure Type		Device Marking
		None	Single	Dual	Gauge	Differential	Absolute	Device Marking
Small Outline Pac	kage (MPXV2	2053G Sei	ries)					
MPXV2053DP	1351			•		•		MPXV2053DP
Unibody Package	Unibody Package (MPX2053 Series)							
MPX2053D	344	•				•		MPX2053D
MPAK Package (N	/IPXM2053 Se	eries)	•	•	•	•		
MPXM2053D	1320	•				•		MPXM2053D
MPXM2053DT1	1320	•				•		MPXM2053D
MPXM2053GS	1320A		•		•			MPXM2053GS
MPXM2053GST1	1320A		•		•			MPXM2053GS

Pressure

UNIBODY PACKAGE



MPX2053D CASE 344-15

SMALL OUTLINE PACKAGE



MPXV2053DP CASE 1351-01

MPAK PACKAGES



MPXM2053D/DT1 CASE 1320-02



MPXM2053GS/GST1 CASE 1320A-02

Operating Characteristics

Table 1. Operating Characteristics (V_S = 10 V_{DC}, T_A = 25°C unless otherwise noted, P1 > P2)

Characteristic	Symbol	Min	Тур	Max	Units
Pressure Range ⁽¹⁾	P _{OP}	0	_	50	kPa
Supply Voltage ⁽²⁾	V _S	_	10	16	V _{DC}
Supply Current	Ι _Ο	_	6.0	_	mAdc
Full Scale Span ⁽³⁾	V _{FS}	38.5	40	41.5	mV
Offset ⁽⁴⁾	_	-1.0	_	1.0	mV
Sensitivity	—	$\Delta V / \Delta P$	_	0.8	—
Linearity ⁽⁵⁾	_	-0.6	_	0.4	%V _{FS}
Pressure Hysteresis ⁽⁵⁾ (0 kPa to 50 kPa)	_	_	±0.1	_	%V _{FS}
Temperature Hysteresis ⁽⁵⁾ (-40 °C to 125 °C)	_	_	±0.5	_	%V _{FS}
Temperature Coefficient of Full Scale ⁽⁵⁾	TCV _{FS}	-2.0	_	2.0	%V _{FS}
Temperature Coefficient of Offset ⁽⁵⁾	TCV _{OFF}	-1.0	_	1.0	mV
Input Impedance	Z _{IN}	1000	_	2500	Ω
Output Impedance	Z _{OUT}	1400	_	3000	Ω
Response Time ⁽⁶⁾ (10% to 90%)	t _R	_	1.0	—	ms
Warm-Up Time	—	_	20	_	ms
Offset Stability ⁽⁷⁾			±0.5	—	%V _{FS}

1. 1.0 kPa (kiloPascal) equals 0.145 psi.

2. Device is ratiometric within this specified excitation range. Operating the device above the specified excitation range may induce additional error due to device self-heating.

3. Full Scale Span (V_{FSS}) is defined as the algebraic difference between the output voltage at full rated pressure and the output voltage at the minimum rated pressure.

4. Offset (V_{off}) is defined as the output voltage at the minimum rated pressure.

5. Accuracy (error budget) consists of the following:

Linearity: Output deviation from a straight line relationship with pressure, using end point method, over the specified pressure range.
Temperature Hysteresis: Output deviation at any temperature within the operating temperature range, after the temperature is cycled to

and from the minimum or maximum operating temperature within the operating temperature applied.

• Pressure Hysteresis: Output deviation at any pressure within the specified range, when this pressure is cycled to and from the minimum or maximum rated pressure, at 25 °C.

• TcSpan: Output deviation at full rated pressure over the temperature range of 0°C to 85 °C, relative to 25 °C.

• TcOffset: Output deviation with minimum rated pressure applied, over the temperature range of 0 °C to 85 °C, relative to 25 °C.

6. Response Time is defined as the time for the incremental change in the output to go from 10% to 90% of its final value when subjected to a specified step change in pressure.

7. Offset stability is the product's output deviation when subjected to 1000 hours of Pulsed Pressure, Temperature Cycling with Bias Test.

Maximum Ratings

Table 2. Maximum Ratings⁽¹⁾

Rating	Max Value	Unit
Supply Voltage	16	V
Pressure (P1 > P2)	200	kPa
Storage Temperature	-40 to +125	°C
Operating Temperature Range	-40 to +125	°C

1. Exposure beyond the specified limits may cause permanent damage or degradation to the device.

Figure 1 shows a block diagram of the internal circuitry integrated on a pressure sensor chip.




Figure 1. Temperature Compensated Pressure Sensor Schematic

Voltage Output versus Applied Differential Pressure

The differential voltage output of the sensor is directly proportional to the differential pressure applied.

The output voltage of the differential or gauge sensor increases with increasing pressure applied to the pressure

side relative to the vacuum side. Similarly, output voltage increases as increasing vacuum is applied to the vacuum side relative to the pressure side.

On-Chip Temperature Compensation and Calibration

Figure 2 shows the minimum, maximum and typical output characteristics of the MPX2053 series at 25°C. The output is directly proportional to the differential pressure and is essentially a straight line.

A silicone gel isolates the die surface and wire bonds from the environment, while allowing the pressure signal to be transmitted to the silicon diaphragm.




Figure 2. Output vs. Pressure Differential

Pressure

LINEARITY

Linearity refers to how well a transducer's output follows the equation: $V_{out} = V_{off}$ + sensitivity x P over the operating pressure range. There are two basic methods for calculating nonlinearity: (1) end point straight line fit (see Figure 3) or (2) a least squares best line fit. While a least squares fit gives the "best case" linearity error (lower numerical value), the calculations required are burdensome. Conversely, an end point fit will give the "worst case" error (often more desirable in error budget calculations) and the calculations are more straightforward for the user. The specified pressure sensor linearities are based on the end point straight line method measured at the midrange pressure.




Figure 3. Linearity Specification Comparison

Figure 4 illustrates the differential or gauge configuration in the basic chip carrier (Case 344). A silicone gel isolates the die surface and wire bonds from the environment, while allowing the pressure signal to be transmitted to the silicon diaphragm.

The MPX2053 series pressure sensor operating characteristics and internal reliability and qualification tests

are based on use of dry air as the pressure media. Media other than dry air may have adverse effects on sensor performance and long term reliability. Contact the factory for information regarding media compatibility in your application. Refer to application note AN3728, for more information regarding media compatibility.







Figure 4. Unibody Package — Cross-Sectional Diagram (Not to Scale)







ES:
DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
CONTROLLING DIMENSION: INCH.
DIMENSION -A- IS INCLUSIVE OF THE MOLD STOP RING. MOLD STOP RING NOT TO EXCEED 16.00 (0.630).

	INCHES		MILLIM	ETERS	
DIM	MIN	MAX	MIN	MAX	
Α	0.595	0.630	15.11	16.00	
В	0.514	0.534	13.06	13.56	
С	0.200	0.220	5.08	5.59	
D	0.016	0.020	0.41	0.51	
F	0.048	0.064	1.22	1.63	
G	0.100) BSC	2.54 BSC		
J	0.014	0.016	0.36	0.40	
L	0.695	0.725	17.65	18.42	
М	30°	NOM	30° NOM		
Ν	0.475	0.495	12.07	12.57	
R	0.430	0.450	10.92	11.43	
Y	0.048	0.052	1.22	1.32	
Z	0.106	0.118	2.68	3.00	


STYLE 1: PIN 1. GROUND 2. + OUTPUT 3. + SUPPLY 4. - OUTPUT

STYLE	3:	
PIN	1.	GND
	2.	-VOUT
	3.	VS
	4.	+VOUT

CASE 344-15 **ISSUE AA** UNIBODY PACKAGE

STYLE 2: PIN 1. V∞ 2. - SUPPLY 3. + SUPPLY 4. GROUND

MPX2053



NXP SEMICONDUCTORS N. V. ALL RIGHTS RESERVED	MECHANICAL OU	TLINE	PRINT VERSION N	NOT TO SCALE
TITLE:		DOCUMEN	NT NO: 98ASA992551	D REV: B
8 LD SNSR, DUAL	PORT	STANDAF	RD: NON-JEDEC	
		S0T1693	3–1	14 MAR 2016

CASE 1351-01 ISSUE A SMALL OUTLINE PACKAGE



NOTES:

1. CONTROLLING DIMENSION: INCH

2. INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M-1994.

A DIMENSIONS DO NOT INCLUDE MOLD FLASH OR PPROTRUSIONS. MOLD FLASH AND PROTRUSIONS SHALL NOT EXCEED .006 PER SIDE.


A DIMENSION DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE DAMBAR PROTRUSION SHALL BE .008 MAXIMUM.


STYLE 1:		STYLE 2:		
PIN 1:	GND	PIN	1:	N/C
PIN 2:	+Vout	PIN	2:	Vs
PIN 3:	Vs	PIN	3:	GND
PIN 4:	-Vout	PIN	4:	Vout
PIN 5:	N/C	PIN	5:	N/C
PIN 6:	N/C	PIN	6:	N/C
PIN 7:	N/C	PIN	7:	N/C
PIN 8:	N/C	PIN	8:	N/C

© NXP SEMICONDUCTORS N. V. ALL RIGHTS RESERVED			MECHANICAL OUTLINE		PRINT VERSION	NOT TO SCALE		
TITLE:						DOCUMEN	NT NO: 98ASA99255	D REV: B
	8	LD	SNSR,	DUAL	DUAL PORT		RD: NON-JEDEC	
						SOT1693	3-1	14 MAR 2016

CASE 1351-01 ISSUE A SMALL OUTLINE PACKAGE







NXP SEMICENDUCTERS N.V. ALL RIGHTS RESERVED	MECHANICAL OU	TLINE	PRINT VERSION N	IT TO SCALE
TITLE:			NT ND: 98ARH99088A	REV: D
5 LD M-PAC		STANDAR	RD NON-JEDEC	
		SDT1674	-1	29 FEB 2016

CASE 1320-02 ISSUE B MPAK PACKAGE



NOTES:

- 1. DIMENSIONS ARE IN INCHES.
- 2. INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M-1994.

A DIMENSION DOES NOT INCLUDE MOLD FLASH OR PROTRUSION. MOLD FLASH OR PROTRUSION SHALL NOT EXCEED .006" PER SIDE.

4. ALL VERTICAL SURFACES TO BE 5' MAXIMUM.

A DIMENSION DOES NOT INCLUDE DAMBAR PROTRUSION.


PIN 1: GND PIN 2: +Vout PIN 3: Vs PIN 4: -Vout

© NXP SEMICONDUCTORS N. V. ALL RIGHTS RESERVED	MECHANICAL OUTLINE		PRINT VERSION	NOT TO SCALE
TITLE:		DOCUMEN	NT NO: 98ARH99088	A REV: D
5 LD M-PAC		STANDAR	RD: NON-JEDEC	
		SOT1674	4—1	29 FEB 2016

CASE 1320-02 ISSUE B MPAK PACKAGE

MPX2053





NXP SEMICONDUCTORS N. V. ALL RIGHTS RESERVED	MECHANICAL OUTLINE		PRINT VERSI	ON NOT TO SCALE
TITLE:		DOCUMEN	NT NO: 98ARH99	087A REV: B
5 LD M-PAC, POR	STANDAF	RD: NON-JEDEC		
		SOT1673	3-1	29 FEB 2016

CASE 1320-02 ISSUE A MPAK PACKAGE



NOTES:

1. DIMENSIONS ARE IN INCHES.

2. INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M-1994.

A DIMENSIONS DOES NOT INCLUDE MOLD FLASH OR PROTRUSION. MOLD FLASH OR PROTRUSION SHALL NOT EXCEED .006" PER SIDE.

4. ALL VERTICAL SURFACES TO BE 5" MAXIMUM.

DIMENSION DOES NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE DAMBAR PROTRUSION SHALL BE .008 MAXIMUM.

NXP SEMICONDUCTORS N. V. ALL RIGHTS RESERVED	MECHANICAL OUTLINE		PRINT VERSION	NOT TO SCALE
TITLE: 5 LD M-PAC, PORTED		DOCUMEN	NT NO: 98ARH99087	A REV: B
		STANDARD: NON-JEDEC		
		SOT1673	3-1	29 FEB 2016

CASE 1320-02 ISSUE A MPAK PACKAGE

MPX2053

Table 3. Revision History

Revision number	Revision date	Description of changes
10	06/2020	 This data sheet has been formatted to comply with the identity guidelines of NXP Semiconductors. Ordering Information: Removed MPX2053DP, MPX2053GP and MPXV2053GP from the table. Package images: Removed the package images for MPX2053DP, MPX2053GP and MPXV2053GP. Updated all other package images. Operating Characteristics: Revised "Non-Linearity" to "Linearity" and added new footnote after Linearity, Pressure Hysteresis, Temperature Hysteresis, Temperature Coefficient of Full Scale, and Temperature Coefficient of Offset. Package Dimensions: Removed package dimensions for Case 344B-01 Issue B, Unibody package, Case 344C-01 Issue B, Unibody package, and Case 1369-01, Issue D Small Outline package. Updated all other package dimension images.
9	10/2012	Deleted references to device number MPXV2053GVP throughout the document

How to Reach Us:

Home Page: nxp.com

Web Support: nxp.com/support Information in this document is provided solely to enable system and software implementers to use NXP products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits based on the information in this document.

NXP reserves the right to make changes without further notice to any products herein. NXP makes no warranty, representation, or guarantee regarding the suitability of its products for any particular purpose, nor does NXP assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in NXP data sheets and/or specifications can and do vary in different applications, and actual performance may vary over time. All operating parameters, including "typicals," must be validated for each customer application by customer's technical experts. NXP does not convey any license under its patent rights nor the rights of others. NXP sells products pursuant to standard terms and conditions of sale, which can be found at the following address: nxp.com/salestermsandconditions.

NXP, the NXP logo, Energy Efficient Solutions logo, are trademarks of NXP Semiconductors, B.V., Reg. U.S. Pat. & Tm. Off. Xtrinsic is a trademark of NXP Semiconductors, B.V. All other product or service names are the property of their respective owners.

© 2012, 2020 NXP Semiconductors, B.V.

