

N and P-Channel Enhancement Mode Power MOSFET

Description

The NCE4606A uses advanced trench technology to provide excellent $R_{\mathrm{DS}(\mathrm{ON})}$ and low gate charge . The complementary MOSFETs may be used to form a level shifted high side switch, and for a host of other applications.

General Features

N-Channel

 $V_{DS} = 30V, I_{D} = 6.5A$

 $R_{DS(ON)}$ < 24m Ω @ V_{GS} =10V

 $R_{DS(ON)}$ < 37m Ω @ V_{GS} =4.5V


P-Channel

 $V_{DS} = -30V, I_{D} = -7A$

 $R_{DS(ON)}$ < 30m Ω @ V_{GS} =-10V

 $R_{DS(ON)}$ < 50m Ω @ V_{GS} =-4.5V

- High power and current handing capability
- Lead free product is acquired
- Surface mount package



Package Marking and Ordering Information

Device Marking Dev		Device	Device Package	Reel Size	Tape width	Quantity
	NCE4606A	NCE4606A	SOP-8	Ø330mm	12mm	4000 units

Absolute Maximum Ratings (T_A=25 ℃unless otherwise noted)

Paran	Symbol	N-Channel	P-Channel	Unit	
Drain-Source Voltage	V _{DS}	30	-30	V	
Gate-Source Voltage	V _{GS}	±20	±20	V	
Continuous Drain Current	T _A =25℃		6.5	-7	А
Continuous Drain Current	T _A =70°C	I _D	5.4	-5.8	
Pulsed Drain Current (Note 1)		I _{DM}	30	-30	Α
Maximum Power Dissipation T _A =25℃		P _D	2.0	2.0	W
Operating Junction and Storage	T_J, T_STG	-55 To 150	-55 To 150	$^{\circ}$	

Thermal Characteristic

Thermal Resistance,Junction-to-Ambient (Note2)	R _{0JA}	N-Ch	62.5	°C/W
Thermal Resistance, Junction-to-Ambient (Note2)	$R_{\theta JA}$	P-Ch	62.5	°C/W



N-CH Electrical Characteristics (T_A=25 °C unless otherwise noted)

Parameter	Symbol	Condition	Min	Тур	Max	Unit	
Off Characteristics	<u> </u>						
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} =0V I _D =250μA	30	33	-	V	
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} =30V,V _{GS} =0V	-	-	1	μA	
Gate-Body Leakage Current	I _{GSS}	V _{GS} =±20V,V _{DS} =0V	-	-	±100	nA	
On Characteristics (Note 3)			•	•			
Gate Threshold Voltage	V _{GS(th)}	$V_{DS}=V_{GS}$, $I_{D}=250\mu A$	1	1.6	3	V	
Drain Course On State Besistance		V _{GS} =10V, I _D =6A	-	19	24	mΩ	
ain-Source On-State Resistance	R _{DS(ON)}	V _{GS} =4.5V, I _D =6A	-	26	37		
Forward Transconductance	g FS	V _{DS} =5V,I _D =6A	15	-	-	S	
Dynamic Characteristics (Note4)	<u> </u>						
Input Capacitance	C _{lss}	\/ -45\/\/ -0\/	-	530.3	-	PF	
Output Capacitance	Coss	V _{DS} =15V,V _{GS} =0V, F=1.0MHz	-	67.1	-	PF	
Reverse Transfer Capacitance	C _{rss}	r=1.0lvinz	-	61.2	-	PF	
Switching Characteristics (Note 4)							
Turn-on Delay Time	t _{d(on)}		-	4.5	-	nS	
Turn-on Rise Time	t _r	V_{DD} =15V, R_L =2.5 Ω	-	2.5	-	nS	
Turn-Off Delay Time	$t_{d(off)}$	V_{GS} =10 V , R_{GEN} =3 Ω	-	14.5	-	nS	
Turn-Off Fall Time	t _f		-	3.5	-	nS	
Total Gate Charge	Qg	\/ -45\/ -64	-	14.2	-	nC	
Gate-Source Charge	Q _{gs}	V_{DS} =15V, I_{D} =6A, V_{GS} =10V	-	1.8	-	nC	
Gate-Drain Charge	n Charge Q _{gd}		-	3.3	-	nC	
Drain-Source Diode Characteristics	<u>.</u>		•				
Diode Forward Voltage (Note 3)	V _{SD}	V _{GS} =0V,I _S =6A	-	0.8	1.2	V	
	•						



http://www.ncepower.com

P-CH Electrical Characteristics (T_A=25 [°]C unless otherwise noted)

Parameter	Symbol	Condition	Min	Тур	Max	Unit
Off Characteristics				•		
Drain-Source Breakdown Voltage	BV _{DSS}	V _{GS} =0V I _D =-250μA	-30	-33	-	V
Zero Gate Voltage Drain Current	Gate Voltage Drain Current I _{DSS} V _{DS} =-30V,V _{GS} =0V		-	-	-1	μA
Gate-Body Leakage Current	I _{GSS}	V _{GS} =±20V,V _{DS} =0V	-	-	±100	nA
On Characteristics (Note 3)	<u> </u>			•		
Gate Threshold Voltage	V _{GS(th)}	$V_{DS}=V_{GS}$, $I_{D}=-250\mu A$	-1.0	-1.3	-2.0	V
Drain Source On State Registance	Б	V _{GS} =-10V, I _D =-6.5A	-	24	30	mΩ
Drain-Source On-State Resistance	R _{DS(ON)}	V _{GS} =-4.5V, I _D =-5A	-	34	50	
Forward Transconductance	g fs	V _{DS} =-5V,I _D =-6.5A	10	-	-	S
Dynamic Characteristics (Note4)	<u> </u>			•		
Input Capacitance	C _{lss}	\/ 45\/\/ 0\/	-	956.1	-	PF
Output Capacitance	C _{oss}	V_{DS} =-15V, V_{GS} =0V, F=1.0MHz	-	122	-	PF
Reverse Transfer Capacitance	C _{rss}	r=1.0Wnz	-	116.2	-	PF
Switching Characteristics (Note 4)	<u> </u>			•		
Turn-on Delay Time	t _{d(on)}		-	8	-	nS
Turn-on Rise Time	t _r	V_{DD} =-15V, R_L =2.3 Ω	-	6	-	nS
Turn-Off Delay Time	t _{d(off)}	V_{GS} =-10 V , R_{GEN} =6 Ω	-	20	-	nS
Turn-Off Fall Time	t _f		-	7.5	-	nS
Total Gate Charge	Qg	\/ - 45\/	-	21.3	-	nC
Gate-Source Charge	Q _{gs}	V _{DS} =-15V,I _D =-6.5A	-	2.2	-	nC
Gate-Drain Charge	Q _{gd}	V _{GS} =-10V	-	4.5	-	nC
Drain-Source Diode Characteristics			•	•		
Diode Forward Voltage (Note 3)	V _{SD}	V _{GS} =0V,I _S =-6.5A	-	-	-1.2	V
	1					

Notes:

- 1. Repetitive Rating: Pulse width limited by maximum junction temperature.
- **2.** Surface Mounted on FR4 Board, $t \le 10$ sec.
- 3. Pulse Test: Pulse Width \leq 300 μ s, Duty Cycle \leq 2%.
- 4. Guaranteed by design, not subject to production



N- Channel Typical Electrical and Thermal Characteristics (Curves)




Figure 1:Switching Test Circuit




Figure 3 Output Characteristics




Figure 5 Drain-Source On-Resistance




Figure 2:Switching Waveforms




Figure 4 Transfer Characteristics




Figure 6 Drain-Source On-Resistance








Figure7 Rdson vs Vgs




Qg Gate Charge (nC) Figure 9 Gate Charge



Vds Drain-Source Voltage (V)

Figure 11 Capacitance vs Vds



 T_J -Junction Temperature($^{\circ}$ C) Figure 8 Power Dissipation





Figure 10 Source- Drain Diode Forward



Vds Drain-Source Voltage (V)
Figure 12 Safe Operation Area






Figure 13 Normalized Maximum Transient Thermal Impedance



P- Channel Typical Electrical and Thermal Characteristics (Curves)




Figure 1 Output Characteristics




Figure 2 Transfer Characteristics




Figure 3 Rdson- Drain Current




Figure 4 Rdson-Junction Temperature




Figure 5 Gate Charge






Figure 6 Source- Drain Diode Forward





Vds Drain-Source Voltage (V)

Figure 7 Capacitance vs Vds



 T_J -Junction Temperature (°C) Figure 9 BV_{DSS} vs Junction Temperature




Figure 8 Safe Operation Area




Figure 10 V_{GS(th)} vs Junction Temperature





Figure 11 Normalized Maximum Transient Thermal Impedance

Square Wave Pluse Duration(sec)



SOP-8 Package Information



Symbol	Dimensions	In Millimeters	Dimensions In Inches		
Symbol	Min.	Max.	Min.	Max.	
А	1.350	1.750	0.053	0.069	
A1	0.100	0.250	0.004	0.010	
A2	1.350	1.550	0.053	0.061	
b	0.330	0.510	0.013	0.020	
С	0.170	0.250	0.006	0.010	
D	4.700	5.100	0.185	0.200	
E	3.800	4.000	0.150	0.157	
E1	5.800	6.200	0.228	0.244	
е	1.270	(BSC)	0.050	(BSC)	
L	0.400	1.270	0.016	0.050	
θ	0°	8°	0°	8°	



Attention

- Any and all NCE power products described or contained herein do not have specifications that can handle applications that require extremely high levels of reliability, such as life-support systems, aircraft's control systems, or other applications whose failure can be reasonably expected to result in serious physical and/or material damage. Consult with your NCE power representative nearest you before using any NCE power products described or contained herein in such applications.
- NCE power assumes no responsibility for equipment failures that result from using products at values that exceed, even momentarily, rated values (such as maximum ratings, operating condition ranges, or other parameters) listed in products specifications of any and all NCE power products described or contained herein.
- Specifications of any and all NCE power products described or contained herein stipulate the performance, characteristics, and functions of the described products in the independent state, and are not guarantees of the performance, characteristics, and functions of the described products as mounted in the customer's products or equipment. To verify symptoms and states that cannot be evaluated in an independent device, the customer should always evaluate and test devices mounted in the customer's products or equipment.
- NCE power Semiconductor CO.,LTD. strives to supply high-quality high-reliability products. However, any and all semiconductor products fail with some probability. It is possible that these probabilistic failures could give rise to accidents or events that could endanger human lives, that could give rise to smoke or fire, or that could cause damage to other property. When designing equipment, adopt safety measures so that these kinds of accidents or events cannot occur. Such measures include but are not limited to protective circuits and error prevention circuits for safe design, redundant design, and structural design.
- In the event that any or all NCE power products(including technical data, services) described or contained herein are controlled under any of applicable local export control laws and regulations, such products must not be exported without obtaining the export license from the authorities concerned in accordance with the above law.
- No part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, including photocopying and recording, or any information storage or retrieval system, or otherwise, without the prior written permission of NCE power Semiconductor CO.,LTD.
- Information (including circuit diagrams and circuit parameters) herein is for example only; it is not guaranteed for volume production. NCE power believes information herein is accurate and reliable, but no guarantees are made or implied regarding its use or any infringements of intellectual property rights or other rights of third parties.
- Any and all information described or contained herein are subject to change without notice due to product/technology improvement, etc. When designing equipment, refer to the "Delivery Specification" for the NCE power product that you intend to use.
- This catalog provides information as of Sep.2010. Specifications and information herein are subject to change without notice.