


Features

- Ease of Paralleling
- Zero reverse recovery current
- Zero forward recovery voltage
- Temperature independent switching behavior
- High temperature operation
- High frequency operation

Key Characteristics		
V_{RRM}	650	V
$I_F, T_c=141^{\circ}\text{C}$	4	A
Q_c	9	nC

Benefits

- Unipolar rectifier
- Substantially reduced switching losses
- No thermal run-away with parallel devices
- Reduced heat sink requirements



Applications

- Switch Mode Power Supplies (SMPS)
- Boost diodes in PFC or DC/DC stages
- Motor drives
- Solar application, UPS
- Power Switching Circuits

Part No.	Package Type	Marking
ASD465F	TO-220-2F	ASD465F

Maximum Ratings

Parameter	Symbol	Test Condition	Value	Unit
Repetitive Peak Reverse Voltage	V_{RRM}		650	V
Surge Peak Reverse Voltage	V_{RSM}		650	V
DC Blocking Voltage	V_{DC}		650	V
Continuous Forward Current	I_F	$T_C=25^{\circ}\text{C}$	11	A
		$T_C=135^{\circ}\text{C}$	4.9	
		$T_C=141^{\circ}\text{C}$	4	
Repetitive Peak Forward Surge Current	I_{FRM}	$T_C=25^{\circ}\text{C}$, $t_p=10\text{ms}$, Half Sine Wave, $D=0.3$	21	A
Non-repetitive Peak Forward Surge Current	I_{FSM}	$T_C=25^{\circ}\text{C}$, $t_p=10\text{ms}$, Half Sine Wave	33	A
Power Dissipation	P_{TOT}	$T_C=25^{\circ}\text{C}$	50	W
		$T_C=110^{\circ}\text{C}$	22	W
Operating Junction	T_j		-55°C to 175°C	$^{\circ}\text{C}$
Storage Temperature	T_{stg}		-55°C to 175°C	$^{\circ}\text{C}$
Mounting Torque		M3 Screw	1	Nm lbf-in
		6-32 Screw	8.8	

Thermal Characteristics

Parameter	Symbol	Test Condition	Value	Unit
			Typ.	
Thermal resistance from junction to case	R_{thJC}		4.7	$^{\circ}\text{C}/\text{W}$

Electrical Characteristics

Parameter	Symbol	Test Conditions	Numerical		Unit
			Typ.	Max.	
Forward Voltage	V_F	$I_F=4A, T_j=25^{\circ}C$	1.4	1.65	V
		$I_F=4A, T_j=175^{\circ}C$	1.7	2.3	
Reverse Current	I_R	$V_R=650V, T_j=25^{\circ}C$	1	10	μA
		$V_R=650V, T_j=175^{\circ}C$	2	50	
Total Capacitive Charge	Q_C	$V_R=400V, T_j=25^{\circ}C$ $Q_C = \int_0^{V_R} C(V) dV$	9	-	nC
Total Capacitance	C	$V_R=0V, T_j=25^{\circ}C, f=1MHz$	230	260	pF
		$V_R=200V, T_j=25^{\circ}C, f=1MHz$	24	26	
		$V_R=400V, T_j=25^{\circ}C, f=1MHz$	20	21	


Performance Graphs1) Forward IV characteristics as a function of T_j :2) Reverse IV characteristics as a function of T_j :

Figure 1. Forward Characteristics




Figure 2. Reverse Characteristics

3)Current Derating




Figure 3. Current Derating

4)Capacitance vs. reverse voltage :





Figure 4. Capacitance vs. Reverse Voltage

Package TO-220-2F

SYMBOL	DIMENSIONS		
	Min.	Nom.	Max.
A	4,60	4,70	4,80
b	0,70	0,80	0,91
b1	1,20	1,30	1,47
b2	1,10	1,20	1,30
C	0,45	0,50	0,63
D	15,80	15,87	15,97
e	2,54		
E	10,00	10,10	10,30
F	2,44	2,54	2,64
G	6,50	6,70	6,90
L	12,90	13,10	13,30
L1	3,13	3,23	3,33
Q	2,65	2,75	2,85
Q1	3,20	3,30	3,40
ϕR	3,08	3,18	3,28

DISCLAIMER

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Copyright ©2019 Anbon Semiconductor Company Ltd.
All rights reserved.

