


Power MOSFET

PRODUCT SUMMARY						
V _{DS} (V)	250					
$R_{DS(on)}(\Omega)$	V _{GS} = 10 V 2.0					
Q _g (Max.) (nC)	8.2					
Q _{gs} (nC)	1.8					
Q _{gd} (nC)	4.5					
Configuration	Single					



FEATURES

- Dynamic dV/dt Rating
- Repetitive Avalanche Rated
- · Fast Switching
- Ease of Paralleling
- Simple Drive Requirements
- Compliant to RoHS Directive 2002/95/EC



DESCRIPTION

Third generation Power MOSFETs from Vishay provide the designer with the best combination of fast switching, ruggedized device design, low on-resistance and cost-effectiveness.

The TO-220AB package is universally preferred for all commercial-industrial applications at power dissipation levels to approximately 50 W. The low thermal resistance and low package cost of the TO-220AB contribute to its wide acceptance throughout the industry.

ORDERING INFORMATION			
Package	TO-220AB		
Lead (Pb)-free	IRF614PbF		
Lead (FD)-free	SiHF614-E3		
SnPb	IRF614		
OHF D	SiHF614		

PARAMETER			SYMBOL	LIMIT	UNIT	
Drain-Source Voltage			V _{DS}	250	.,	
Gate-Source Voltage			V _{GS}	± 20	V	
Continuous Drain Current	V_{GS} at 10 V $T_{C} = 25 ^{\circ}\text{C}$ $T_{C} = 100 ^{\circ}\text{C}$	T _C = 25 °C	,	2.7	А	
Continuous Drain Current		T _C = 100 °C	I _D	1.7		
Pulsed Drain Current ^a			I _{DM}	8.0		
Linear Derating Factor				0.29	W/°C	
Single Pulse Avalanche Energy ^b			E _{AS}	61	mJ	
Repetitive Avalanche Current ^a			I _{AR}	2.7	Α	
Repetitive Avalanche Energy ^a		E _{AR}	3.6	mJ		
Maximum Power Dissipation $T_C = 25 ^{\circ}C$			P _D	36	W	
Peak Diode Recovery dV/dtc		dV/dt	4.8	V/ns		
Operating Junction and Storage Temperature Range			T _J , T _{stg}	- 55 to + 150	00	
Soldering Recommendations (Peak Temperature)	nmendations (Peak Temperature) for 10 s			300 ^d	°C	
Manualina Tanana	6-32 or M3 screw			10	lbf ⋅ in	
Mounting Torque				1.1	N⋅m	

Notes

- a. Repetitive rating; pulse width limited by maximum junction temperature (see fig. 11).
- b. V_{DD} = 50 V, starting T_J = 25 °C, L = 13 mH, R_g = 25 Ω , I_{AS} = 2.7 A (see fig. 12).
- c. $I_{SD} \le 2.7$ A, $dI/dt \le 65$ A/ μ s, $V_{DD} \le V_{DS}$, $T_J \le 150$ °C.
- d. 1.6 mm from case.

^{*} Pb containing terminations are not RoHS compliant, exemptions may apply



THERMAL RESISTANCE RATINGS						
PARAMETER	SYMBOL	TYP.	MAX.	UNIT		
Maximum Junction-to-Ambient	R _{thJA}	-	62			
Case-to-Sink, Flat, Greased Surface	R _{thCS}	0.50	-	°C/W		
Maximum Junction-to-Case (Drain)	R _{thJC}	-	3.5			

PARAMETER	SYMBOL	TEST (MIN.	TYP.	MAX.	UNIT	
Static						•	
Drain-Source Breakdown Voltage	V _{DS}	$V_{GS} = 0$) V, I _D = 250 μA	250	-	-	V
V _{DS} Temperature Coefficient	$\Delta V_{DS}/T_{J}$	Reference	to 25 °C, I _D = 1 mA	-	0.39	-	V/°C
Gate-Source Threshold Voltage	V _{GS(th)}	$V_{DS} = V$	$V_{DS} = V_{GS}, I_{D} = 250 \mu\text{A}$		-	4.0	V
Gate-Source Leakage	I _{GSS}	VG	_{SS} = ± 20 V	-	-	± 100	nA
Zoro Coto Voltago Drain Comment	,	V _{DS} = 250 V, V _{GS} = 0 V		-	-	25	
Zero Gate Voltage Drain Current	I _{DSS}	V _{DS} = 200 V, V	V _{GS} = 0 V, T _J = 125 °C	-	-	250	μA
Drain-Source On-State Resistance	R _{DS(on)}	V _{GS} = 10 V	I _D = 1.6 A ^b	-	-	2.0	Ω
Forward Transconductance	9 _{fs}	$V_{DS} = 5$	60 V, I _D = 1.6 A ^b	0.90	-	-	S
Dynamic							
Input Capacitance	C _{iss}	V	_{'GS} = 0 V,	-	140	-	pF
Output Capacitance	C _{oss}	V	_{DS} = 25 V,	1	42	-	
Reverse Transfer Capacitance	C_{rss}	f = 1.0	MHz, see fig. 5	1	9.6	-	
Total Gate Charge	Qg			ı	-	8.2	
Gate-Source Charge	Q_{gs}	$V_{GS} = 10 \text{ V}$	$I_D = 2.7 \text{ A}, V_{DS} = 200 \text{ V}$	-	-	1.8	nC
Gate-Drain Charge	Q _{gd}		see fig. 6 and 13 ^b	-	-	4.5	
Turn-On Delay Time	t _{d(on)}	V_{DD} = 125 V, I_D = 2.7 A , R_g = 24 Ω, R_D = 45 Ω, see fig. 10 ^b		-	7.0	-	ns
Rise Time	t _r			-	7.6	-	
Turn-Off Delay Time	t _{d(off)}			-	16	-	
Fall Time	t _f			-	7.0	-	
Internal Drain Inductance	L _D	Between lead, 6 mm (0.25") from package and center of die contact		-	4.5	-	
Internal Source Inductance	L _S			-	7.5	-	- nH
Drain-Source Body Diode Characteristic	s					,	
Continuous Source-Drain Diode Current	Is	MOSFET symbol showing the integral reverse p - n junction diode		-	-	2.7	
Pulsed Diode Forward Current ^a	I _{SM}			-	-	8.0	А
Body Diode Voltage	V _{SD}	T _J = 25 °C, I _S = 2.7 A, V _{GS} = 0 V ^b		-	-	2.0	V
Body Diode Reverse Recovery Time	t _{rr}	$T_J = 25 \text{ °C}, I_F = 2.7 \text{ A, dI/dt} = 100 \text{ A/µs}^b$		-	190	390	ns
Body Diode Reverse Recovery Charge	Q _{rr}			-	0.64	1.3	μC
Forward Turn-On Time	t _{on}	Intrinsic turn-	on time is nealiaible (turn	on is dominated by L _S and L _D)			Ln)

Notes

- a. Repetitive rating; pulse width limited by maximum junction temperature (see fig. 11).
- b. Pulse width \leq 300 μ s; duty cycle \leq 2 %.



TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Fig. 1 - Typical Output Characteristics, T_C = 25 °C




Fig. 2 - Typical Output Characteristics, T_C = 150 °C




Fig. 3 - Typical Transfer Characteristics




Fig. 4 - Normalized On-Resistance vs. Temperature






Fig. 5 - Typical Capacitance vs. Drain-to-Source Voltage




Fig. 7 - Typical Source-Drain Diode Forward Voltage




Fig. 6 - Typical Gate Charge vs. Gate-to-Source Voltage




Fig. 8 - Maximum Safe Operating Area








Fig. 9 - Maximum Drain Current vs. Case Temperature




Fig. 10a - Switching Time Test Circuit



Fig. 10b - Switching Time Waveforms




Fig. 11 - Maximum Effective Transient Thermal Impedance, Junction-to-Case






Fig. 12a - Unclamped Inductive Test Circuit




Fig. 12b - Unclamped Inductive Waveforms




Fig. 12c - Maximum Avalanche Energy vs. Drain Current




Fig. 13a - Basic Gate Charge Waveform





Fig. 13b - Gate Charge Test Circuit





Peak Diode Recovery dV/dt Test Circuit






Fig.14 - For N-Channel

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package/tape drawings, part marking, and reliability data, see www.vishay.com/ppg?91025.





TO-220-1



DIM	MILLIN	IETERS	INCHES			
DIM.	MIN.	MAX.	MIN.	MAX.		
Α	4.24	4.65	0.167	0.183		
b	0.69	1.02	0.027	0.040		
b(1)	1.14	1.78	0.045	0.070		
С	0.36	0.61	0.014	0.024		
D	14.33	15.85	0.564	0.624		
E	9.96	10.52	0.392	0.414		
е	2.41	2.67	0.095	0.105		
e(1)	4.88	5.28	0.192	0.208		
F	1.14	1.40	0.045	0.055		
H(1)	6.10	6.71	0.240	0.264		
J(1)	2.41	2.92	0.095	0.115		
L	13.36	14.40	0.526	0.567		
L(1)	3.33	4.04	0.131	0.159		
ØР	3.53	3.94	0.139	0.155		
Q	2.54	3.00	0.100	0.118		
ECN: X15-0364-Rev. C, 14-Dec-15 DWG: 6031						

Note

 \bullet $M^{\star}=0.052$ inches to 0.064 inches (dimension including protrusion), heatsink hole for HVM



Revison: 14-Dec-15 1 Document Number: 66542



Legal Disclaimer Notice

Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.