ELECTRICAL	Single shaft(R1,R2)
1. Total resistance:	10 kQ± 20%
2. Rated power:	0. 05W
3. Rated voltage:	Please refer to the attached.
4. Resistance taper:	Please refer to the attached.
5. Tap position:	Trouse refer to the attached.
6. Tap resistance between terminals:	400 200 to 200 may
7. Residual resistance between terminals:	1&2, 2&3 : 20Q max.
8. Sliding noise : (Measured by JIS C 6443)	Less than 100mV
9. Insulation resistance :	More than 100 MΩ at 250V D.C.
10. Withstand voltage:	300V A.C. for 1 minute.
11. Gang error :	3 dB max. between PANEL SECTION REAR SECTION -40dB less than odb
12. switch rating:(Resistor load)	0.5A12VD.C.(min:10mA)
13. Switch contact resistance:	Initial value :100mQ max.
(Measured by the O. 5A 5V D. C. voltage drop method.)	After 10,000 cycles:200mΩ max.
14. Circuit:	——————————————————————————————————————
MECHANI CAL	
1. Total rotational angle :	300*10"
2. Rotational torque: (Rotational speed 60°/sec.)	2~25mN·m.
3. Stopper strength :	No damage with an application of 0.5N.m.min
4. Resistance to soldering heat :	Please refer to the attached.
5. Bushing nut tightening strength :	Tightening torque to be no greater than 1N·m. *Pay attention otherwise the strength may not be assured.
6. Push / pull strength :	
	710 14
7. Shaft wobble :(Apply the moment of 50mN·m at the point of 30mm from monting surface)	0.6 XL/30mm p-p max. (L:Shaft length) (If the shaft length is less than 30mm, the value shall be calculated proportionally.)
8. Operation force of shaft:	
9.Click position :	
10. Click torque:	
11. Rotation play at the click position:	
12.Contact arrangement :	S. P. S. T. (PUSH ON)
13. Switching stroke :	0. 5 <sup>+0.7</sup> <sub>-0.3</sub> mm
14. Switch operation force :	4 <sup>+4</sup> <sub>-2</sub> N
ENDURANCE	
1. Rotational life :	More than 15,000 cycles.
2. Switching life :	More than 10,000 cycles.
NOTES	
1. The items except above mentioned items 2. This type is protected against sulfides 3. Operating temperature renge: -20°C to 4. Storage temperature renge: -40°C to	shall meet or exceed JIS C 6443. ; +70°C +85°C
AIDEAIDIRIE <i>C</i> O ITO	TITLE APPD. CHKD. DSGD. NO.  SPECIFICATIONS SYMB. DATE APPD CHYD DSGD. R. A[858W8] M. FDdo I. Yamaguti VROOO0012
	SIMO DATE AFFOCINO DOGO ITTURO DE TITURO DE TI
	Confidentia
	- KK

Rated voltage: The rated voltage shall be the voltage of D.C. or A.C. (commercial frequency, effective value) corresponding to the rated power (dissipation), and be obtained from the following formula. When the obtained rated voltage exceeds the maximum working voltage given in the following, however, the maximum working voltage of the following shall be the rated voltage.  $E = \sqrt{P \cdot R} \; (V)$ 

Where E : Rated voltage (V)  $P : \text{Rated power (dissipation) (W)} \\ R : \text{Nominal total resistance } (\Omega) \\ \text{Maximum working voltage : 50 V A.C.} , 10 V D.C.$ 

Resistance to soldering heat

There shall be no evidence of poor contact between resistance element and terminals, or any physical damages as a result of soldering.

● Dip soldering Condition of soldering: Soldering shall be certified with following condition. Substrate to be soldered : Copper clad laminated phenol board in one surface of 1.6 mm thickness. Solder flux : Flux of 0.82 specific weight in bubbling type solder fluxcoating apparatus shall be used and bubbling surface height shall be defined substantially as halt thickness of substrate. Flux shall not flow up on substrate surface. Preheating: Surface temperature of substrate shall be settled within 100°C in 2 minutes. Dip soldering:

Please use the above process only 1 or 2 times.


 Manual soldering To be performed in 3 seconds within 350°C.

To be performed in 260±5°C, 5±1 sec.

					APPD.	CHKD.	DSGD.	NAM	E					
					]									
					May. 23, 194	May. 23, '9	4 May. 23, 194							
						H Fodo	T. Yamaguti	DOC	UMENT	NO.				
SYMB	DATE	APPD	CHKD	DSGD	R. Arasawa	M, Elluv	i, iamayati							
		·			•		<u> </u>	•				40	_	 _

## Confidential

## ALPSALPINE CO.,LTD.



AT 150° C.W. SHAFT ROTATION FROM FULL C.C.W. POSITION VOLTAGE PERCENT SHALL FALL WITHIN THE LIMITS OF 10-25 PERCENT.

Way, 23, '94 Way, 23, '94 RESISTANCE TAPER  SYMB DATE APPD CHKD DSGD  I. Wagani S. Sasaki I. SUZUKi  VROOOOO12						APPD.	CHKD.	DSGD.	NAME K 0 9 - A 0 1	1
$\mathbf{L} = \mathbf{L} \mathbf{L} \mathbf{L} \mathbf{L} \mathbf{L} \mathbf{L} \mathbf{L} \mathbf{L}$						Way. 23. '94	Way, 23, '94	Way, 23, '94		-
SYMB DATE APPD CHKD DSGD A. Magami S. Jasali A. Juzuki VROOOOO12						V Wanami	C Cacabi	V C1171161	DOCUMENT NO.	
	SYMB	DATE	APPD	CHKD	DSGD	n, mayalli	J. J. 3. 8. 8. 7	1, 302011	VR0000012	

Confidential

