





MAPX	MODIFICATION	DATE
------	--------------	------





- NOTES:
- MATERIAL:
    - MOLDING: LCP UL94 V-0
    - CONTACT: COPPER ALLOY.
    - GOLD PLATED Min ON CONTACT AREA, 100u" Min TIN (LEAD FREE) ON SOLDER AREA,
    - SHELL: SUS304-H, T=0.30±0.03mm
    - 50u" NICKEL PLATING OVER ALL.
    - SHILD: SUS304-H, T=0.12±0.03mm
  - MECHANICAL:
    - INSERTION: 5~20N.
    - EXTRACTION: 8~20N AFTER TEST.
    - DURABILITY: 10000 CYCLES
  - ELECTRICAL:
    - CURRENT: 5A FOR VBUS; 1.25A FOR GND PIN. 0.25A FOR OTHER.
    - VOLTAGE: 20 V MAX
    - WITHSTANDING VOLTAGE: 100V AC R.M.S.
    - CONTACT RESISTANCE: 40mΩ MAX.
    - INSULATION RESISTANCE: 100MΩ MIN.
  - ENVIRONMENTAL:
    - TEMPERATURE RANGE -25°C ~ +85°C



SECTION B-B



SECTION A-A



USCX-24FX-XXRX-06

- 1-G.P
- 2-RoHS
- 3-REACH
- 4-HF/无卤
- 1-卷带包装
- 2-PVC盒
- N-可焊接
- S-锡锡
- T-亮锡
- A-金
- B-半金劈锡 1u"
- D-半金劈锡 5u"
- F-半金劈锡 15u"
- H-半金劈锡 30u"
- K-黑色
- N-本色

Detail 产品图  
PRODUCT CHART DWG


深圳市精拓金电子有限公司

公差一览表  
TOLERANCE UNLESS OTHERWISE

X.	±0.25	X.	±5.°
.X	±0.20	.X	±2.°
.XX	±0.15	.XX	±1.°
.XXX	±0.05	.XXX	±0.5°


单位 UNITS	MM	制图 DRAWING	邱建辉	制图料号 PRODUCT PART NO.	918-318K2023C40005
比例 SCALE	1:1	审核 CHKD	郭治富	产品名称 PRODUCT NO.	TYPE-C3. 1板上型母座四脚插板有柱SMT+DIP 8.65不带弹片前插后贴
日期 DATE	2011.09.02	核准 APPD	黄国荣	角法 VIEW	版本 VER
					A0

MAPX	MODIFICATION	DATE



USB TYPE-C FULL-FEATURED RECEPTACLE INTERFACE PIN ASSIGNMENTS

PIN	Signal Name	Description	PIN	Signal Name	Description
A1	GND	Ground return	B12	GND	Ground return
A2	SSTXp1	Positive half of first SuperSpeed TX differential pair	B11	SSRXp1	Positive half of first SuperSpeed RX differential pair
A3	SSTXn1	Negative half of first SuperSpeed TX differential pair	B10	SSRXn1	Negative half of first SuperSpeed RX differential pair
A4	Vbus	Bus Power	B9	Vbus	Bus Power
A5	CC1	Configuration Channel	B8	SBU2	Sideband Use (SBU)
A6	Dp1	Positive half of the USB 2.0 differential pair-Position 1	B7	Dn2	Negative half of the USB 2.0 differential pair-Position 2
A7	Dn1	Negative half of the USB 2.0 differential pair-Position 1	B6	Dp2	Positive half of the USB 2.0 differential pair-Position 2
A8	SBU1	Sideband Use (SBU)	B5	CC2	Configuration Channel
A9	Vbus	Bus Power	B4	Vbus	Bus Power
A10	SSRXn2	Negative half of second SuperSpeed RX differential pair	B3	SSTXn2	Negative half of second SuperSpeed TX differential pair
A11	SSRXp2	Positive half of second SuperSpeed RX differential pair	B2	SSTXp2	Positive half of second SuperSpeed TX differential pair
A12	GND	Ground return	B1	GND	Ground return




RECOMMEND P.C.B LAYOUT (COMPONENT SIDE)  
TOLERANCE FOR PCB LAYOUT IS ± 0.05  
KEEP OUT AREA

<b>产品图</b> PRODUCT CHART DWG		<b>深圳市精拓金电子有限公司</b>							
公差一览表 TOLERANCE UNLESS OTHERWISE		单位	MM	制图	邱建辉	制图料号	918-318K2023C40005		
X.	±0.25	X.	±5.°	比例	1:1	审核	郭治富	产品名称	TYPE-C3.1板上型母座四脚插板有柱SMT+DIP
.XX	±0.15	.XX	±2.°	日期	2011.09.02	核准	黄国荣	角法	8.65不带弹片前插后贴
.XXX	±0.05	.XXX	±1.°	日期	2011.09.02	核淮	APPD	版本	A0
								角法	VIEW
								版本	VER


由 Autodesk 教育版产品制作

由 Autodesk 教育版产品制作


7	8	9	10
MAPX	MODIFICATION		DATE




① 产品入载带示意图




② 卷盘贴标签示意图




③ 8盘产品叠层示意图



⑥ 外箱封箱示意图



⑤ 产品入外箱示意图



④ 10盘产品入防水袋示意图

图四

图三

包装说明:

1. 将检验好的成品;SMT朝下放入载带底部;每卷装700PCS产品;具体如图一所示
2. 将包装好的产品;每盘必需贴上内标签;具体如图二所示
3. 将贴好内标签的产品每8盘叠一层装入防水袋中并加一包干燥剂;装好后将防水袋封好;具体如图三图四所示
4. 先将1pcs平卡放入纸箱底部;然后将装好产品的防水袋装入纸箱中;防水袋热熔封口,封口面需朝上;并将4PCS三角套分别装入4个角;如图五所示
5. 装好后将1pcs平卡放入纸箱最上面并封好纸箱及贴好相关标签;具体如图六所示;(产品包装的标签,如客户有要求,请按客户要求包装出货)
6. 载带前面留30PCS空格,后面留20PCS空格
7. COVER与CARRY剥离力:50-125g,速度:300mm/分钟左右,剥离角度:165°-180°

产品图			
PRODUCT CHART DWG			
公差一览表			
TOLERANCE UNLESS OTHERWISE			
X.	±0.25	X.	±5.°
.X	±0.20	.X	±2.°
.XX	±0.15	.XX	±1.°
.XXX	±0.05	.XXX	±0.5°

深圳市精拓金电子有限公司

单位	MM	制图	邱建辉	制图料号	918-318K2023C40005
比例	1:1	审核	郭治富	产品名称	TYPE-C3.1板上型母座四脚插板有柱SMT+DIP
日期	2011.09.02	核准	黄国荣	角法	8.65不带弹片前插后贴
版本		APPD		版本	AO

由 Autodesk 教育版产品制作

由 Autodesk 教育版产品制作