



### General Features




- $R_{DS(ON)} < 20m\Omega @ V_{GS} = -10V$   
 $R_{DS(ON)} < 33m\Omega @ V_{GS} = -4.5V$
- High Power and Current Handling Capability
- Lead Free Product is Acquired
- Surface Mount Package

### Applications

- PWM Applications
- Load Switch
- Power Management

### Product Summary

VDS	-30	V
RDS(on),max.@ VGS=-10 V	20	mΩ
ID	-9	A



### Absolute Maximum Ratings ( $T_C=25^\circ C$ unless otherwise specified)

Symbol	Parameter	Max.	Units	
$V_{DSS}$	Drain-Source Voltage	-30	V	
$V_{GSS}$	Gate-Source Voltage	$\pm 12$	V	
$I_D$	Continuous Drain Current	$T_C = 25^\circ C$	-9	A
		$T_C = 100^\circ C$	-5	
$I_{DM}$	Pulsed Drain Current <small>note1</small>	-15	A	
$P_D$	Power Dissipation	$T_C = 25^\circ C$	1.8	W
$R_{\theta JC}$	Thermal Resistance, Junction to Ambient	6.9	$^\circ C/W$	
$T_J, T_{STG}$	Operating and Storage Temperature Range	-55 to +150	$^\circ C$	

**Electrical Characteristics** ( $T_C=25^\circ\text{C}$  unless otherwise specified)

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Units
<b>Off Characteristic</b>						
$BV_{DSS}$	Drain-Source Breakdown Voltage	$V_{GS}=0V, I_D = -250\mu A$	-30	-	-	V
$I_{DSS}$	Zero Gate Voltage Drain Current	$V_{DS} = -30V, V_{GS} = 0V,$	-	-	-1	$\mu A$
$I_{GSS}$	Gate to Body Leakage Current	$V_{DS} = 0V, V_{GS} = \pm 12V$	-	-	$\pm 100$	nA
<b>On Characteristics</b>						
$V_{GS(th)}$	Gate Threshold Voltage	$V_{DS} = V_{GS}, I_D = -250\mu A$	-1.0	-1.6	-2.5	V
$R_{DS(on)}$	Static Drain-Source on-Resistance <small>note2</small>	$V_{GS} = -10V, I_D = -5A$	-	16	20	m $\Omega$
		$V_{GS} = -4.5V, I_D = -3.0A$	-	23	33	
$g_{FS}$	Forward Transconductance	$V_{DS} = -5V, I_D = -5.0A$	20	-	-	S
<b>Dynamic Characteristics</b>						
$C_{iss}$	Input Capacitance	$V_{DS} = -15V, V_{GS} = 0V,$ $f = 1.0MHz$	-	1300	-	pF
$C_{oss}$	Output Capacitance		-	240	-	pF
$C_{rss}$	Reverse Transfer Capacitance		-	95	-	pF
$Q_g$	Total Gate Charge	$V_{DS} = -15V, I_D = -5A,$ $V_{GS} = -1.0V$	-	20	50	nC
$Q_{gs}$	Gate-Source Charge		-	4	-	nC
$Q_{gd}$	Gate-Drain("Miller") Charge		-	6	-	nC
<b>Switching Characteristics</b>						
$t_{d(on)}$	Turn-on Delay Time	$V_{DS} = -15V, I_D = -4A,$ $R_{GEN}=2.5\Omega, V_{GS}=-1.0V$	-	11	-	ns
$t_r$	Turn-on Rise Time		-	18	-	ns
$t_{d(off)}$	Turn-off Delay Time		-	30	-	ns
$t_f$	Turn-off Fall Time		-	10	-	ns
<b>Drain-Source Diode Characteristics and Maximum Ratings</b>						
$I_S$	Maximum Continuous Drain to Source Diode Forward Current		-	-	-7	A
$I_{SM}$	Maximum Pulsed Drain to Source Diode Forward Current		-	-	-10	A
$V_{SD}$	Drain to Source Diode Forward Voltage	$V_{GS} = 0V, I_S = -5A$	-	-	-1.2	V

Notes:1. Repetitive Rating: Pulse Width Limited by Maximum Junction Temperature

2. Pulse Test: Pulse Width $\leq 300\mu s$ , Duty Cycles $\leq 2\%$



### Typical Performance Characteristics




Figure1. Output Characteristics




Figure2. Transfer Characteristics




Figure3. Capacitance Characteristics




Figure4. Gate Charge




Figure5. Drain-Source on Resistance




Figure6. Drain-Source on Resistance




Figure7. Safe Operation Area







Figure8. Switching wave

### Ordering and Marking Information

Ordering Device No.	Marking	Package	Packing	Quantity
ASDM30P09ZB-R	30P09	SOT23-3	Tape&Reel	3000/Reel
ASDM30P09ZB-R	3007	SOT23-3	Tape&Reel	3000/Reel

PACKAGE	MARKING
SOT23-3	
SOT23-3	

## SOT-23-3L PACKAGE INFORMATION



Symbol	Dimensions In Millimeters		Dimensions In Inches	
	Min	Max	Min	Max
A	1.050	1.250	0.041	0.049
A1	0.000	0.100	0.000	0.004
A2	1.050	1.150	0.041	0.045
b	0.300	0.500	0.012	0.020
c	0.100	0.200	0.004	0.008
D	2.820	3.020	0.111	0.119
E	1.500	1.700	0.059	0.067
E1	2.650	2.950	0.104	0.116
e	0.950(BSC)		0.037(BSC)	
e1	1.800	2.000	0.071	0.079
L	0.300	0.600	0.012	0.024
$\theta$	0°	8°	0°	8°

**IMPORTANT NOTICE**

ShenZhen Ascend Semiconductor incorporated MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

ShenZhen Ascend Semiconductor Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. ShenZhen Ascend Semiconductor Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does ShenZhen Ascend Semiconductor Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume .

all risks of such use and will agree to hold Ascendsemi Incorporated and all the companies whose products are represented on ShenZhen Ascend Semiconductor Incorporated website, harmless against all damages.

ShenZhen Ascend Semiconductor Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use ShenZhen Ascend Semiconductor Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold ShenZhen Ascend Semiconductor Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

[www.ascendsemi.com](http://www.ascendsemi.com)