ISO9001: 2000 ISO14001: 2004

APPROVAL SPECIFICATIONS

Title. TACT SWITCH

Product Model. KAN0631-0651C

Customer's Part NO.

Customer's Model:

Customer's Approval Requested.

Please return this copy as a certification of your approval.

Checked by: Date:

Approved by: Date:

APPROVE	REVIEW	POLT		
孙自波	金成尧	连丽媛		

WENZHOU GANGYUAN ELECTRONICS CO., LTD.



GYUAN CO.,LTD

CUSTOMER	CUSTOMER'S P/N	GYE'S P/N	PRODUCT	REVISION
		KAN0631-0651C	TACT SWITCH	А

1、 概述

GENERAL

1.2 适用范围

APPLICATION

此规格书适用于机械式轻触开关的相关要求

This specification is applied to the requirements for TACTILE SWITCH (MECHANICAL CONTACT)

1.3 工作温度范围

Operating Temperature Range

- -20℃~70℃(在标准大气压、标准湿度条件下)
- -20°C ~70°C (Normal humidity, normal air pressure)

1.4 贮藏温度范围

- Storage Temperature Range —30℃~80℃(在标准大气压、标准湿度条件下)
- -30° C \sim 80°C (Normal humidity, normal air pressure)

1.5 测试条件

Test Conditions

在没有其它特定的条件下,应该在以下的条件下进行测试和测量:

Unless otherwise specified, tests and measurement shall be made in the following standard conditions:

常温......5℃~35℃

Normal temperature......5°C~35°C

标准湿度......相对湿度 25%~85%

Normal humidity.....relative humidity 25%~85%

标准大气压......86KPa~106Kpa

Normal air pressure......86Kpa~106Kpa

在制造过程中,测试和测量应该在以下的条件下进行:

If any doubt arise from the judgment, tests shall be conducted at the following conditions:

温度......**20℃±2℃**

Temperature......20°C±2°C

相对湿度......65%±5%

Relative humidity......65%±5%

环境气压......86KPa~106Kpa

Air pressure......86KPa~106Kpa

孙自波 12.09.13 金成尧 12.09.13 APPROVE BY CHECKED BY PRPARE BY 连丽媛 12.09.13



CUSTOMER	CUSTOMER'S P/N	GYE'S P/N	PRODUCT	REVISION
		KAN0631-0651C	TACT SWITCH	Α

详细说明

Detailed specification

2.1 外观:应无影响、降低产品性能的缺陷;

Appearance: There should be no defects that affect the serviceability of product.

2.2 结构尺寸和安装尺寸:应符合装配图要求;

Style and dimension: shall conform to the assemble drawings.

2.3 操作形式:有触觉反应的操作

(Details of contact arrangement are given in the assembly drawings.)

2.5 开关工作额定值: DC 12V, 50mA (有效值)

Ratings: 12V DC, 50mA (effective value)

3. 电气性能:

ELECTRICAL SPECIFICATION

项	目		1	试验条件			要求		
ITI	EM		TE	TEST CONDITIONS					
			在以 5V 10mA的] 的电路中,以一个等于	Hz 的交流电源 加于手柄中心					
1		接触电阻	Applying a static	load of 2 times ope	rating force to		<100 O		
1	Conta	act Resistance	the center of the stem,	, measurements sha	III be made by		≤100mΩ		
			5V DC 10mA or mo	re than 1KHZ AC	small-current				
			contact resistance met	er.					
2	I	绝缘电阻 Insulation Resistance	在端子之间施加 DC 100V /1min 的条件下,测量端子之间底座、盖板的电阻值 Measurement shall be made following application of 100V DC potential, across terminals, and across terminals and cover, for one minute.				≥100MΩ		
3	介质耐压 Dielectric voltage proof		在端子之间施加 250V AC(50HZ 或 60HZ)/1min 250V AC (50HZ or 60HZ) shall be applied across terminals, for one minute.				无击穿、无飞弧 There should be b breakdown and flashover		
APPROVI	E BY 孙自波 12.09.13		APPROVE BY		13 CHECKED BY 金成尧 12.09.13 PRPARE BY			Y	连丽媛 12.09.13



CUSTOME	ΕR	CUSTOMER'S	S P/N	GYE'S P/N	PRO	ODUCT		REVISION
				KAN0631-0651C	TAC	CT SWITC	СН	А
项目			试	: 验 条 件				要求
ITEM			TEST	CONDITIONS			RE	QUIREMENTS
4. 机械性能: MECHANICAL	SPEC	IFICATION						_
	g力 ating	开关垂直于操作 量开关导通所需 Placing the swit vertical and the center of the ste	开关垂直于操作方向放置,在开关驱动件顶端中心逐渐施力,测量开关导通所需的最大力度。 Placing the switch such that the direction of switch operation is vertical and then gradually increasing the load applied to the center of the stem, the maximum load required for the switch to come to a stop shall be measured.					
2 最大/ Full Ti		开关垂直于操作 开关驱动件顶端 Placing the swit vertical and ther the center of the to a stop shall b	中心,测量 tch such than applying st e stem; the t	ation is	(0.25±0.1mm		
APPROVE B	Y 3	外自波 12.09.13	CHECKE) BY 金成尧 12.	.09.13	PRPARE	E BY	连丽媛 12.09.13



		VOTUAN	ALLINOV.						
С	USTOMER	CUSTOMER'S P/N	GYE'S P/N	1	PRODUCT		REVISION		
			KAN0631-06	651C	TACT SWITCH	н	Α		
	项目		试 验 条 件 要求			要求			
	ITEM		TEST CONDITION	S		REC	QUIREMENTS		
3	回弹力 Return Force	开关垂直于操作方向后,测量顶端向自由 The sample switch i operation is vertical to the whole travel d	开关垂直于操作方向放置,在开关驱动件顶端中心下降至全行程后,测量顶端向自由位置转换的力度。 The sample switch is installed such that the direction of switch operation is vertical and upon depressing the stem in its center to the whole travel distance, the force of the stem to return to its free position shall be measured.						
4	停止强度 Stop Strengt	开关垂直于操作方向 荷持续 1min。 Placing the switch s vertical, and then a direction of stem ope	uch that the direction static load of 30N	peration is	There s damage	L械和电气损坏 shall be no sign of mechanically and electrically.			
5	手柄拔出 强度 Stem Strength	的行程范围。 Placing the switch s vertical, and then the	开关垂直于操作方向放置,反方向实施最大操作力,并测量手柄的行程范围。 Placing the switch such that the direction of switch operation is vertical, and then the maximum force to withstand a pull applied opposite to the direction of stem operation shall be measured.						
6	在以下设定条件下进行测量: Measurements shall be made following the test set forth below: (1) 焊接温度:245±5℃ Solder temperature: 245±5℃ (2) 浸入时间:2s±0.5s Immersion time: 2s±0.5s 对于其它步骤参考《GB 5095.6—86》试验 12a The other steps please refer to《GB 5095.6-86》TEST 12a						小涂层应均匀覆盖 for the edge, the should cover a n 90%		
APP	ROVE BY	孙自波 12.09.13 CH	ECKED BY 金成	尧 12.09.13	PRPARE	BY	连丽媛 12.09.13		



-		1101	UAN		/ \	O V/ \L	<u> </u>		<i>,</i> , , , , ,	<u> </u>	
С	USTOMER		CUSTOMER	'S P/N	GYE'	S P/N	PF	RODUCT		REVISION	
					KAN0	631-06510	т,	ACT SWITC	Н	А	
					试 验	条 件			要求		
	ITEM				TEST CON	IDITIONS			RE	QUIREMENTS	
	限电气性能: RONMENTAL	. SPEC	CIFICATION								
1	低温测试 Resistance low tempera	to ature	标准湿度的 Following t normal ten measurem (1) 温度 Tem	样品应按照以下实验条件进行测试,实验后样品应放在常温及示准湿度的环境中 1 小时后做性能测试: Following the test set forth below the sample shall be left in cormal temperature and humidity conditions for 1 h before neasurements are made: (1) 温度: -30±2℃ (2) 时间: 96h Time: 96h						⊞: ≤200mΩ resistance: Ω 4.1,4.2,4.3 4.1,4.2,4.3	
2	高温测试 Heat resista	ance	标准湿度的 forth below humidity co (1) 温质 ten (2) 时间	humidity conditions for 1 h before measurements are made: (1) 温度: 80±2℃ temperature:80±2℃ 「項目 3,4.1,4.2,4.3 ltem 3,4.1,4.2,4.3						t resistance: Ω 4.1,4.2,4.3	
3	温度周期性 Change temperat	of	样品应放在 试期间样品 After 5 cyc allowed to conditions	常温及相应保持 cles of stand for 1 h.	要求进行 5 次循环的温度周期性测试, 实验后及标准湿度的环境中 1 小时后做性能测试。测					⊞: ≤200mΩ t resistance: Ω 4.1,4.2,4.3 4.1,4.2,4.3	
APP	APPROVE BY 孙自波 12.09.13 CHE				ECKED BY	金成尧 1	2.09.13	PRPARE	E BY	连丽媛 12.09.13	



С	USTOMER	CUSTOMER'S		S P/N	PRODUCT		REVISION
			KANO)631-0651C	TACT SWI	тсн	А
	项目		试 验	条件			要求
	ITEM		TEST CON	NDITIONS			REQUIREMENTS
4	湿温测试 Moisture resistance	标准湿度的环 forth below the humidity cond (1) 温度: temper (2) 相对温		t 接触 Con ≤200 项目	电阻: ≤200mΩ tact resistance: 0mΩ 3,4.1,4.2,4.3 3,4.1,4.2,4.3		
5	硫化试验 Sulfuration resistance	标准湿度的环 forth below the humidity cond (1) H ₂ S与 H ₂ S ga (2) 时间: Time: 7		t I 接触 Con ≤200 项目	e电阻: ≤200mΩ tact resistance: DmΩ 3,4.1,4.2,4.3 3,4.1,4.2,4.3		
6	盐雾试验 Salt Mist	(1) 温度: 3 tempera (2) 盐溶液液 salt solu (3) 时间: 8 Time: 8h 实验后的盐沉	shall be checked a 5℃±2℃ ature: 35℃±2℃ 尽度: 5±1%(质量 ution:5±1%(solid h±1h n±1 hour	corre	件上没有腐蚀斑点 No remarkable osion shall be gnized in metal part.		
APP	APPROVE BY 孙自波 12.09.13 CHECKED BY 金成尧 12.09.13 PRPARE BY 连						连丽媛 12.09.13



	GA	NGY	UAN		APPR	OVAL	SPE		AII	JINO
С	USTOMER		CUSTOMER'	S P/N	GYE'	S P/N	Р	RODUCT		REVISION
					KAN0	631-0651C	Т	ACT SWITC	СН	А
	限机械性能: NDURANCE	SPEC	IFICATION							
	项目				试验	条件				要求
	ITEM TEST CONDIT					DITIONS			RE	QUIREMENTS
	工作寿命 Operation									
1	WE		根据下面的测试要求进行测试: Measurement shall be made following the test set forth below: (1) DC 12V, 50mA 带负载							
2	振动 Vibra	ition	Measureme (1)振云 Vib (2)振帧 Am (3)振云 Dir dire (4)测证	Vibration frequency range: 10 to 55 to 10Hz (2) 振幅(峰一峰): 1.5mm Amplitude: 1.5mm (3) 振动方向: 包括手柄行程方向在内的三个相互垂直的方向 Direction of vibration:Three mutually perpendicular direction including the direction of stem travel						4.1,4.2,4.3 4.1,4.2,4.3
7. 焊			I					<u> </u>		
	ERING CON	DITIO	NS:							
请按以下条件进行焊接: (1) 焊锡温度: ≤350℃ (2) 连续焊接时间: ≤3 s Please practice according to below conditions: (1) Soldering temperature: 350℃ Max. (2) Continuous soldering time: 3 s Max.										
APP	ROVE BY	孙自治	波 12.09.13	CHE	CKED BY	金成尧 12.	.09.13	PRPARE	ΞBY	连丽媛 12.09.13



	ı								
Cl	JSTOMER	CUSTOMER'S P/N	GY	E'S P/N	PRODUCT	REVISION			
			KAI	N0631-0651C	TACT SWITCH	А			
	自动浸焊	项目 Items			条件 Condition				
	Conditions for	助焊剂附着量 Flux built-up			不附着于零部件贴装面的程度 Mounting surface should not be coated with flax				
	Auto-dip	预热温度 Preheating temper	ature	印刷电路板焊接面的周围温度 100℃ max. Ambient temperature of the soldered surface of PC board. 100℃ max.					
7.2		预热温度时间 Preheating time		60s max.					
		焊接温度 Soldering tem	perature	ICVI	260°C max.				
	WER	操接浸渍时间与Continuous dipping time 焊接次数		5s max.		•			
				2次以下					
		Number of solde	ering	2times max.					
1	俾姥说 昍.								

焊接说明:

1、开关浸焊后,注意不要用溶剂清洗。

After switches were soldered, please be careful not to clean switches with solvent.

1.1 在使用烙铁的情况下,焊锡温度应在350℃以下、3秒以内。

In the case of using solding iron, solding conditions shall be 380℃ max and 3 sec.max.

1.2 浸焊后,注意不要在顶部施加负荷。

Right after switches were soidered; please be careful not to load to on the knobs of switches.

- 2、设计中应注意的事项(Design instructions)
- 2.1 印刷基板的安装孔尺寸参见产品图。

Follow recommended P.W.B. piercing plan in outside drawing page.

- 3、注意点(Note):
- 3.1 注意不要施加超负荷的压力或晃动开关。

Please be cautions not to give excessive static load or shock to swiches.

3.2 开关浸焊后,印刷基板注意不要叠放。

Please be careful not to pile up P.W.B.after switches were soldered.


3.3 保管时尤其应注意避开高湿高温和有腐蚀性气体的环境。如需要长时间保存,请不要打开包装箱。


Preservation under high temperature and high high humidity or corrosive gas should be avoided Especially. When you need to preserve for a long period ,do not open the carton.


APPROVE BY	孙自波 12.09.13	CHECKED BY	金成尧 12.09.13	PRPARE BY	连丽媛 12.09.13
	11		32/9452 1210110		101317/102



CUSTOMER	CUSTOMER'S P/N	GYE'S P/N	PRODUCT	REVISION
		KAN0631-0651C	TACT SWITCH	А







电路图

 $\bigcirc \bigcirc \bigcirc \bigcirc \bigcirc \bigcirc$

General tolerance: ±0.2mm

	NO.	NAME	MATERIAL	NATIONALITY	QTY.	FINISHING	
	1	TERMINAL	Brass	China	1	Silver plating	
	2	CASE	PA66	China	1	Black	
	3	CONTACT	Phosphor bronze	Korea	1	Contact side silver plating	
	4	BRACKET	SPCC-SD	China	1	CuSn plating	
	5	STEM	PA66	China	1	ВІ	ack
APPROVE BY		孙自波 12.09.13	CHECKED BY	金成尧 12.0	金成尧 12.09.13 P		连丽媛 12.09.