

## HR915340A

## Electrical Specification @25°C

RoHS Compliant (PB Free)

Isolation: 2250VDC 0.5mA 60sec (UTP Side to Chip Side)

OCL: 350uH Minimum @100KHz 100mV with 8mADC Insertion Loss: -1.0dB Maximum @300KHz ~ 100MHz

Return Loss: -20dB Minimum @1MHz  $\sim 10$ MHz / -16dB Minimum @10MHz  $\sim 30$ MHz -12dB Minimum @30MHz  $\sim 60$ MHz / -10dB Minimum @60MHz  $\sim 80$ MHz


Common Mode Rejection: -30dB Minimum @1MHz ~ 50MHz

−20dB Minimum @50MHz ~ 150MHz

Crosstalk: -40 dB Minimum @1MHz  $\sim 30 \text{MHz} / -35 \text{dB}$  Minimum @30MHz  $\sim 60 \text{MHz}$ 

-30dB Minimum @60MHz  $\sim 100$ MHz

#### **Schematics**



Notes: Connect CHS GND to PCB Ground

REV. 01 1 of 4





## HR915340A


- RoHS Compliant (PB Free)
- Meets or Exceeds IEEE802.3 standards including 350uH Min OCL with 8mADC
- High performance for EMI suppression, Crosstalk, Return Loss and Consistent Electrical
- Minimum 2250VDC isolation per IEEE802.3 requirement
- Minimize PCB space and Simplify PCB Layout
- Less magnetic components to be placed on PCB, higher reliability and yields
- UL Recognized Component: File # E330599

#### Mechanical Dimensions:









Standard LED	Wavelength	Forward V (Min/Max)	Forward A	Туре
Green	568nm	1.8V/2.8V	20mA	squareness
Yellow	585nm	1.8V/2.8V	20mA	squareness

Dimensions in mm

Unless otherwise specified, Tolerance: .xx  $\pm 0.25$ 


REV.: 01 2 of 4

E-Mail: sales@hanrun.com http://www.hanrun.com




# HR915340A

## PCB Layout:



Recommended PCB layout (Component Side View) All dimension tolerance are  $\pm 0.08$  unless otherwise specified

## Suggested Panel Cutout:



SUGGESTED PANEL OPENING

Dimensions in mm

Unless otherwise specified, Tolerance: .xx  $\pm 0.25$ 

REV.: 01 3 of 4

Address: No.16, Industrial Road Central, Industrial Zone, Xiaolan Town, Zhongshan City, Guangdong Province, China
Tel: (0760)86103511 86103508 Fax: (0760)86103686 Post code: 528416
E-Mail: sales@hanrun.com http://www.hanrun.com

# 1x1 Port Tab-UP RJ45 Connector with Integrated Magnetics and LED



## HR915340A

## Material Specification:

Housing: PBT GF Black UL94V-0

Shield: 50u" Nickel over 0.20mm Thickness Brass

Insert: PBT GF Black UL94V-0

Phosphor Bronze 0.35mm Thickness
Plating Area, 30u" gold over 50u" nickel
Solder Area, 100u" tin over 50u" nickel

#### Mechanical Performance:

Mating force: 5 lbs Maximum
Unmating force: 5 lbs Maximum
Operating life: 750 Cycles Minimum

## Operating and Storage Temperature:

Operating Temperature Range:  $0^{\circ}\text{C} \sim +70^{\circ}\text{C}$ Storage Temperature Range:  $-40^{\circ}\text{C} \sim +85^{\circ}\text{C}$ 

REV.: 01 4 of 4