



# JCS15N70C

## 主要参数 MAIN CHARACTERISTICS

$I_D$	15.0 A
$V_{DSS}$	700 V
$R_{dson-max}$ (@ $V_{gs}=10V$ )	0.55 $\Omega$
$Q_g-typ$	44.6 nC

### 用途

- 高频开关电源
- 电子镇流器
- UPS 电源

### APPLICATIONS

- High frequency switching mode power supply
- Electronic ballast
- UPS




### 产品特性

- 低栅极电荷
- 低  $C_{rss}$  (典型值 10.79pF)
- 开关速度快
- 产品全部经过雪崩测试
- 高抗  $dv/dt$  能力
- RoHS 产品

### FEATURES

- Low gate charge
- Low  $C_{rss}$  (typical 10.79pF)
- Fast switching
- 100% avalanche tested
- Improved  $dv/dt$  capability
- RoHS product

## 封装 Package



## 订货信息 ORDER MESSAGE

订货型号 Order codes	印记 Marking	封装 Package	无卤素 Halogen Free	包装 Packaging	器件重量 Device Weight
JCS15N70CC-O-C-N-B	JCS15N70C	TO-220C	否 NO	条管 Tube	2.15 g(typ)
JCS15N70FC-O-F-N-B	JCS15N70F	TO-220MF	否 NO	条管 Tube	2.20 g(typ)





## 绝对最大额定值 ABSOLUTE RATINGS (Tc=25℃)

项 目 Parameter	符 号 Symbol	数 值 Value		单 位 Unit
		JCS15N70CC	JCS15N70FC	
最高漏极-源极直流电压 Drain-Source Voltage	V <sub>DSS</sub>	700	700	V
连续漏极电流 Drain Current -continuous	I <sub>D</sub>	T=25℃	15.0	15.0*
		T=100℃	9.5	9.5*
最大脉冲漏极电流 (注1) Drain Current - pulse (note 1)	I <sub>DM</sub>	60	60*	A
最高栅源电压 Gate-Source Voltage	V <sub>GSS</sub>	±30		V
单脉冲雪崩能量 (注2) Single Pulsed Avalanche Energy (note 2)	E <sub>AS</sub>	910		mJ
雪崩电流 (注1) Avalanche Current (note 1)	I <sub>AR</sub>	15.0		A
重复雪崩能量 (注1) Repetitive Avalanche Energy (note 1)	E <sub>AR</sub>	56.8		mJ
二极管反向恢复最大电压变 化速率 (注3) Peak Diode Recovery dv/dt (note 3)	dv/dt	4.7		V/ns
耗散功率 Power Dissipation	P <sub>D</sub> T <sub>C</sub> =25℃ -Derate above 25℃	568	62.5	W
		4.5	0.5	W/℃
最高结温及存储温度 Operating and Storage Temperature Range	T <sub>J</sub> , T <sub>STG</sub>	-55~+150		℃
引线最高焊接温度 Maximum Lead Temperature for Soldering Purposes	T <sub>L</sub>	300		℃

\*漏极电流由最高结温限制

\*Drain current limited by maximum junction temperature





## 电特性 ELECTRICAL CHARACTERISTICS

项 目 Parameter	符 号 Symbol	测试条件 Tests conditions	最小 Min	典型 Typ	最大 Max	单 位 Units
<b>关态特性 Off –Characteristics</b>						
漏—源击穿电压 Drain-Source Voltage	$BV_{DSS}$	$I_D=250\mu A, V_{GS}=0V$	700	-	-	V
击穿电压温度特性 Breakdown Voltage Temperature Coefficient	$\Delta BV_{DSS}/\Delta T_J$	$I_D=250\mu A$ , referenced to $25^\circ C$	-	0.64	-	V/ $^\circ C$
零栅压下漏极漏电流 Zero Gate Voltage Drain Current	$I_{DSS}$	$V_{DS}=700V, V_{GS}=0V,$ $T_C=25^\circ C$	-	-	10	$\mu A$
		$V_{DS}=560V, T_C=125^\circ C$	-	-	100	$\mu A$
正向栅极体漏电流 Gate-body leakage current, forward	$I_{GSSF}$	$V_{DS}=0V, V_{GS}=30V$	-	-	100	nA
反向栅极体漏电流 Gate-body leakage current, reverse	$I_{GSSR}$	$V_{DS}=0V, V_{GS}=-30V$	-	-	-100	nA
<b>通态特性 On-Characteristics</b>						
阈值电压 Gate Threshold Voltage	$V_{GS(th)}$	$V_{DS} = V_{GS}, I_D=250\mu A$	3.0	-	5.0	V
静态导通电阻 Static Drain-Source On-Resistance	$R_{DS(ON)}$	$V_{GS}=10V, I_D=7.5A$	-	0.45	0.55	$\Omega$
正向跨导 Forward Transconductance	$g_{fs}$	$V_{DS}=40V, I_D=15A$ (note 4)	-	15.45	-	S
<b>动态特性 Dynamic Characteristics</b>						
输入电容 Input capacitance	$C_{iss}$	$V_{DS}=25V,$ $V_{GS}=0V,$ $f=1.0MHz$	-	2185	2840	pF
输出电容 Output capacitance	$C_{oss}$		-	235	304	pF
反向传输电容 Reverse transfer capacitance	$C_{rss}$		-	10.79	14.1	pF





## 电特性 ELECTRICAL CHARACTERISTICS

开关特性 Switching Characteristics						
延迟时间 Turn-On delay time	$t_{d(on)}$	VDD=350V, ID=15A, RG=25Ω (note 4, 5)	-	52.8	66	ns
上升时间 Turn-On rise time	$t_r$		-	112	140	ns
延迟时间 Turn-Off delay time	$t_{d(off)}$		-	94.4	118	ns
下降时间 Turn-Off Fall time	$t_f$		-	43.2	54	ns
栅极电荷总量 Total Gate Charge	$Q_g$	V <sub>DS</sub> =560V , I <sub>D</sub> =15A V <sub>GS</sub> =10V (note 4, 5)	-	44.6	51.3	nC
栅-源电荷 Gate-Source charge	$Q_{gs}$		-	12.7	-	nC
栅-漏电荷 Gate-Drain charge	$Q_{gd}$		-	22	-	nC
漏-源二极管特性及最大额定值 Drain-Source Diode Characteristics and Maximum Ratings						
正向最大连续电流 Maximum Continuous Drain -Source Diode Forward Current		I <sub>S</sub>	-	-	15	A
正向最大脉冲电流 Maximum Pulsed Drain-Source Diode Forward Current		I <sub>SM</sub>	-	-	60	A
正向压降 Drain-Source Diode Forward Voltage	V <sub>SD</sub>	V <sub>GS</sub> =0V, I <sub>S</sub> =15.0A	-	-	1.4	V
反向恢复时间 Reverse recovery time	$t_{rr}$	V <sub>GS</sub> =0V, I <sub>S</sub> =15.0A di/dt=100A/μs (note 4)	-	552	-	ns
反向恢复电荷 Reverse recovery charge	$Q_{rr}$		-	6.18	-	μC

## 热特性 THERMAL CHARACTERISTIC

项 目 Parameter	符 号 Symbol	最大 Max		单 位 Unit
		JCS15N70CC	JCS15N70FC	
结到管壳的热阻 Thermal Resistance, Junction to Case	Rth(j-c)	0.22	2.0	°C/W
结到环境的热阻 Thermal Resistance, Junction to Ambient	Rth(j-A)	62.5	62.5	°C/W

注释:

- 1: 脉冲宽度由最高结温限制
- 2: L=7.5mH, I<sub>AS</sub>=15.0A, V<sub>DD</sub>=50V, R<sub>G</sub>=25Ω, 起始结温 T<sub>J</sub>=25°C
- 3: I<sub>SD</sub>≤15.0A, di/dt≤300A/μs, V<sub>DD</sub>≤BV<sub>DSS</sub>, 起始结温 T<sub>J</sub>=25°C
- 4: 脉冲测试: 脉冲宽度≤300μs, 占空比≤2%
- 5: 基本与工作温度无关

Notes:


- 1: Pulse width by maximum junction temperature
- 2: L=7.5mH, I<sub>AS</sub>=15.0A, V<sub>DD</sub>=50V, R<sub>G</sub>=25Ω, Starting T<sub>J</sub>=25°C
- 3: I<sub>SD</sub>≤15.0A, di/dt≤300A/μs, V<sub>DD</sub>≤BV<sub>DSS</sub>, Starting T<sub>J</sub>=25°C
- 4: Pulse Test: Pulse Width ≤300μs, Duty Cycle≤2%
- 5: Essentially independent of operating temperature






特征曲线 ELECTRICAL CHARACTERISTICS (curves)


On-Region Characteristics




Transfer Characteristic




On-Resistance Variation vs. Drain Current and Gate Voltage




Body Diode Forward Voltage Variation vs. Source Current and Temperature



Capacitance Characteristics




Gate Charge Characteristics






### 特征曲线 ELECTRICAL CHARACTERISTICS (curves)


#### Breakdown Voltage Variation vs. Temperature




#### On-Resistance Variation vs. Temperature




#### Maximum Safe Operating Area For JCS15N70CC



#### Maximum Safe Operating Area For JCS15N70FC




#### Maximum Drain Current vs. Case Temperature






Transient Thermal Response Curve For JCS15N70CC




Transient Thermal Response Curve For JCS15N70FC





## TO-220C

单位 Unit: mm



符号 symbol	MIN	MAX
A	4.30	4.70
B	1.22	1.47
b	0.70	0.95
c	0.40	0.65
D	15.20	16.20
D2	9.00	9.40
E	9.70	10.10
e	2.39	2.69
F	1.25	1.40
L	12.60	13.60
L2	2.80	3.20
Q	2.60	3.00
Q1	2.20	2.60
P	3.50	3.80








## TO-220MF

单位 Unit: mm



SYMBOL	mm	
	MIN	MAX
A	4.5	4.9
B		1.47
b	0.7	0.9
c	0.45	0.60
D	15.67	16.07
D1	9.04	9.20
e	2.54TYPE	
E	9.96	10.36
F	2.34	2.74
L	12.58	13.38
L1	3.13	3.33
Q	3.2	3.4
Q1	2.56	2.96
ΦP	3.08	3.28



**注意事项**

1. 吉林华微电子股份有限公司的产品销售分为直销和销售代理，无论哪种方式，订货时请与公司核实。
2. 购买时请认清公司商标，如有疑问请与公司本部联系。
3. 在电路设计时请不要超过器件的绝对最大额定值，否则会影响整机的可靠性。
4. 本说明书如有版本变更不另外告知

**NOTE**

1. Jilin Sino-miceonics co., Ltd sales its product either through direct sales or sales agent , thus, for customers, when ordering , please check with our company.
2. We strongly recommend customers check carefully on the trademark when buying our product, if there is any question, please don't be hesitate to contact us.
3. Please do not exceed the absolute maximum ratings of the device when circuit designing.
4. Jilin Sino-microelectronics co., Ltd reserves the right to make changes in this specification sheet and is subject to change without prior notice.

**联系方式****吉林华微电子股份有限公司**

公司地址：吉林省吉林市深圳街 99 号

邮编：132013

总机：86-432-64678411

传真：86-432-64665812

网址：[www.hwdz.com.cn](http://www.hwdz.com.cn)

**市场营销部**

地址：吉林省吉林市深圳街 99 号

邮编：132013

电话：86-432-64675588

64675688

64678411

传真：86-432-64671533

**CONTACT****JILIN SINO-MICROELECTRONICS CO., LTD.**

ADD: No.99 Shenzhen Street, Jilin City, Jilin Province, China.

Post Code: 132013

Tel: 86-432-64678411

Fax: 86-432-64665812

Web Site: [www.hwdz.com.cn](http://www.hwdz.com.cn)

**MARKET DEPARTMENT**

ADD: No.99 Shenzhen Street, Jilin City, Jilin Province, China.

Post Code: 132013

Tel: 86-432-64675588

64675688

64678411

Fax: 86-432-64671533

