

TJ-4 AQ SPECIFICATION

FILE No. : E-Q-AT35-A REV. : A Page : 1 / 5

1. Style

This specification describes "TACTILE SWITCH", mainly used as signal switch of electric devices, with the general requirements of mechanical and electrical characteristic..

1.1 Operating Temperature Range : -20 °C ~+70°C

1.2 Storage Temperature Range : -30°C ~+80°C

1.3 The shelf life of product is within 6 months.

Current Range: 50mA, 12 V DC
 Type of Actuation: Tactile feedback

4. Test Sequence:

| | ITEM | DESCRIPTION | TEST CONDITIONS | REQUIREMENTS | | |
|----------------------|------|---------------------------------------|--------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------|--|--|
| APPEARANCE | 1 | Visual Examination | By visual examination check without any out pressure & testing. | There shall be no defects that affect the serviceability of the product. | | |
| ш | 2 | Contact Resistance | Applying a static load 1.5~2 times the operating force to the center made with a 1 kHz small current contact resistance meter. | 100mΩ Max. | | |
| ELECTRIC PERFORMANCE | 3 | Insulation Resistance | Measurements shall be made following application of 500 V DC potential across terminals and cover for 1 minute ±5 seconds. | 100MΩ Min. | | |
| | 4 | Dielectric Withstanding Voltage | 300 V AC(50Hz or 60Hz) shall be applied across terminals and cover for 1 minute | There shall be no breakdown or flashover. | | |
| | 5 | Bounce | 3 to 4 operations at a rate of 1 cycles per second Switch Synchroscope 5V DC 5ΚΩ | 10 m seconds Max. ON OFF 10ms 10ms | | |

| TIADDAO ODECIDATION | | | | FILE No. : E-Q-A135-A | | | | | D-A |
|------------------------|----|---------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------|------------------------|------|-----------------------|------|
| TJ-4 AQ SPECIFICATION | | | | | REV. : | | | Α | |
| | | | | Pa | ige | : | 2 | / | 5 |
| | | | | | | | | | |
| | | | Applied in the direction of operation. \[\frac{1}{2} \] | TJ-410-V | TJ-416-V | TJ-42 | 20-V | TJ-42 | 26-V |
| | 6 | Operating Force | operation. | 100g±50g (.98N± .49N) | 160g±50g (1.57N± .49N) | 200g± (1.96 .49l | 3N± | 260g: (2.55 .49 | δN± |
| | 7 | Stroke | Placing the switch such that the direction of switch operation is vertical and then gradually increasing the load applied to the stem, the stroke distance for the stem to come to a stop shall be measured. | 0.2±0.1mm | | | | | |
| ANCE | 8 | Stop Strength | Placing the switch such that the direction of switch operation is vertical, a static load of 3 kgf(29.4N) shall be applied in the direction of stem operation for a period of 15 seconds |)As shown in item 4∼6 | | | | | |
| MECHANICAL PERFORMANCE | 9 | Solder Heat Resistance | ■SMT Type ~ Series(4/4) (PCB is 1.2 mm in thickness) | ①Shall be free from pronounced backlash and falling-off or breakage terminals ②As shown in item 4 \ 5 ③Contact Resistance: 200mΩ Max ④ Insulation Resistance: 10MΩ Min | | | | | ınd |
| | 10 | Vibration | Shall be vibrated in accordance with Method 201A of MIL-STD-202F 1) Swing distance=1.5mm 2) Frequency: 10-55-10Hz in 1-min/cycle. 3) Direction: 3 vertical directions including the directions of operation 4) Test time: 2 hours each direction | 1)As shown in item 4~7 2)Contact Resistance: 200mΩ Max 3)Insulation Resistance: 10MΩ Min | | | | | |
| | 11 | Shock | Shall be shocked in accordance with Method 213B condition A of MIL-STD-202F 1) Acceleration; 50G 2) Action time:11±1m seconds 3) Testing Direction: 6 sides 4) Test Cycle: 3 times in each direction | Ditto | | | | | |


FILE No. : E-Q-AT35-A

| TJ-4 AQ SPECIFICATION | | | | FILE No. : E-Q-AT35-A REV. : A Page : 3 / 5 | | | | | |
|-----------------------|----|----------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--|--|--|--|
| | | | | | | | | | |
| DURABILITY | 12 | Operating Life | Measurements shall be made following the test forth below: 1)5 mA,5 VDC resistive load 2)Applying a static load the operating force to the center of the stem in the direction of operation 3)Cycle of Operation: 1,000,000cycles Min~100gf \(\) 160gf 500,000 cycles Min~200 gf \(\) 260gf | 1)As shown in item 4 \ 5 2)Operating force:±50% of initial force. 3)Contact Resistance: 10Ω Max 4)Insulation Resistance: 10ΜΩ Min 5)Bounce: 20 m seconds Max | | | | | |
| WEATHER-PROOF | 13 | Resistance Low Temperature | Following the test set forth below the sample shall be left in normal temperature and humidity conditions for 1 hour before the measurements are made: 1) Temperature:-30±2°C 2) Time: 96 hours | 1)As shown in item 4~7 2)Contact Resistance: 200mΩ Max 3)Insulation Resistance: 10MΩ Min | | | | | |
| | 14 | Heat Resistance | Following the test set forth below the sample shall be left in normal temperature and humidity conditions for 1 hour before the measurements are made: 1) Temperature:80±2°C 2) Time: 96 hours | Ditto | | | | | |
| | 17 | Humidity Resistance | Following the test set forth below the sample shall be left in normal temperature and humidity conditions for 1 hour before the measurements are made: 1) Temperature:60±2°C 2) Relative Humidity: 90~95% 3) Time: 96 hours | Ditto | | | | | |
| | | | | | | | | | |

FILE No. : E-Q-AT35-A REV. : A Page : 4 / 5

5. SOLDERING CONDITIONS:

Condition for Soldering TJ4 Series



■ The condition mentioned above is the temperature on the Cu foil of the PCB surface. There are cases where board's temperature greatly differs from switch's surface be used not to allow switch's surface temperature to exceed 260°C.

■ Manual Soldering

| Soldering Temperature | 350°C MAX. |
|---------------------------|---------------|
| Continuous Soldering Time | 5 second MAX. |

■ Precautions in Handling

- 1. Care should be exercised so that flux from the upper part of the printed circuit board does not adhere to the switch.
- 2. Except for washable type do not wash the switch.

■ Notes on storage conditions:

Do not store in the following environment or it may affect product's function and solderbility:

- 1. temperature of -10 (max) \sim +40 (min) $^{\circ}$ C & humidity at 85% (min)
- 2. environment with corrosive gas
- 3. storage over 6 months
- 4. place of direct sunlight

| TJ-4 AQ SPECIFICATION | FILE No. REV. Page | : | E-Q 5 | -AT3 A / | 55-A | | | |
|-----------------------------------------------------------------------------------------------------------------------------------------------|--------------------------|---|----------|----------------|------|--|--|--|
| Store with proper packaging conditions and to avoid loading heavy force We suggest to use the products within 3 months or at least 6 months. | | | | | | | | |
| After opening the package, the rest products must be stored in the appropriate moisture-proof & airtight environment. | | | | | | | | |
| | | | | | | | | |
| | | | | | | | | |
| | | | | | | | | |
| | | | | | | | | |
| | | | | | | | | |
| | | | | | | | | |
| | | | | | | | | |
| | | | | | | | | |
| | | | | | | | | |
| | | | | | | | | |