

November 2018

Multilayer Triplexer

For 1559-1606MHz / 2400-2500MHz / 4900-5950MHz

TPX205950MT-7036A1

2.0x1.25mm [EIA 0805]*

* Dimensions Code JIS[EIA]




Multilayer Triplexer

Conformity to RoHS Directive


For 1559-1606MHz / 2400-2500MHz / 4900-5950MHz

TPX205950MT-7036A1


SHAPES AND DIMENSIONS



■ RECOMMENDED LAND PATTERN



EVALUATION BOARD



 $\begin{tabular}{ll} \hline Copper bottom GND & 0.035mm \\ \hline Line width should be designed to match <math>50\Omega$ characteristic impedance, depending on PCB material and thickness. \\ \hline \end{tabular}

RoHS Directive Compliant Product: See the following for more details.https://product.tdk.com/info/en/environment/rohs/index.html

- All specifications are subject to change without notice.
- Before using these products, be sure to request the delivery specifications.



TPX205950MT-7036A1

ELECTRICAL CHARACTERISTICS

□LOW-BAND

Item	Frequency Range (MHz)	Min.	Тур.	Max.
Insertion Loss (dB)	1559 to 1606	_	0.58	0.70
	1559 to 1606	_	_	0.90 (-40 to +85°C)
Return Loss (dB)	1559 to 1606	10	22	_
Attenuation (dB)	2400 to 2500	19	23	
	4900 to 5950	28	32	_
Characteristic Impedance (Ω)			50 (Nominal)	

[·] Ta: +25±5°C

■MIDDLE-BAND

Item	Frequency Range (MHz)	Min.	Тур.	Max.
Insertion Loss (dB)	2400 to 2500	_	1.09	1.25
	2400 to 2500	_	_	1.45 (-40 to +85°C)
Return Loss (dB)	2400 to 2500	10	16	_
Attenuation (dB)	1560 to 1606	25	28	_
	4800 to 5000	25	29	_
	7200 to 7500	15	25	
Characteristic Impedance (Ω)			50 (Nominal)	

[·] Ta: +25±5°C

□HIGH-BAND

Item	Frequency Range (MHz)	Min.	Тур.	Мах.
	4900 to 5100	_	1.03	1.50
Insertion Lass (dD)	5150 to 5950	_	1.14	1.50
Insertion Loss (dB)	4900 to 5100	_	_	1.70 (-40 to +85°C)
	5150 to 5950	_	_	1.70 (-40 to +85°C)
D-t (-ID)	4900 to 5100	10	15	_
Return Loss (dB)	5150 to 5950	9	13	_
	1560 to 1606	25	44	_
	3400 to 3600	30	44	_
	3600 to 3800	30	42	_
Attenuation (dB)	6900 to 7200	10	15	
	7200 to 7800	13	15	_
	10300 to 11700	21	24	
	15300 to 16200	15	25	_
Characteristic Impedance (Ω)			50 (Nominal)	

[•] Ta: +25±5°C

[•] All specifications are subject to change without notice.

[•] Before using these products, be sure to request the delivery specifications.



TPX205950MT-7036A1

ELECTRICAL CHARACTERISTICS

□ COMMON

Item		Frequency Range (MHz)	Min.	Тур.	Max.
Low	Low to Middle	1560 to 1606	25	31	_
	Low to ivildule	2400 to 2500	19	27	_
loolotion (dD)	Middle to High	2400 to 2500	30	35	
-	Middle to High	4900 to 5950	20	27	
	Low to High	1560 to 1606	25	43	
		4900 to 5950	28	35	
Power Handling (W) —			_	0.5	
Characteristic Impedance (Ω)			50 (Nominal)	50 (Nominal)	

[·] Ta: +25±5°C

TEMPERATURE RANGE

Operating temperature	Storage temperature		
(°C)	(°C)		
-40 to +85	-40 to +85		

[•] All specifications are subject to change without notice.

[•] Before using these products, be sure to request the delivery specifications.


公TDK

TPX205950MT-7036A1

FREQUENCY CHARACTERISTICS


LOW-BAND

Insertion Loss




■MIDDLE-BAND


Insertion Loss




Return Loss




Return Loss



Attenuation



Attenuation



[•] All specifications are subject to change without notice.

[•] Before using these products, be sure to request the delivery specifications.


公TDK

TPX205950MT-7036A1


■ FREQUENCY CHARACTERISTICS

HIGH-BAND


Insertion Loss



Return Loss



Attenuation



- All specifications are subject to change without notice.
- Before using these products, be sure to request the delivery specifications.




TPX205950MT-7036A1


■ FREQUENCY CHARACTERISTICS

□COMMON


Return Loss




Isolation (Low-Mid)



Isolation (Low-High)



Isolation (Mid-High)




[•] All specifications are subject to change without notice.

[•] Before using these products, be sure to request the delivery specifications.



TPX205950MT-7036A1

■ RECOMMENDED REFLOW PROFILE



Preheating			Soldering Critical zon	e (T3 to T4)	Peak	
Temp.		Time	Temp.	Time	Temp.	Time
T1	T2	t1	T3	t2	T4	t3*
150°C	200°C	60 to 120sec	217°C	60 to 120sec	240 to 260°C	30sec max.

 $^{^{\}ast}\,\text{t3}$: Time within 5°C of actual peak temperature

The maximum number of reflow is 3.

[•] All specifications are subject to change without notice.

[•] Before using these products, be sure to request the delivery specifications.



REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using these products.

⚠ REMINDERS

The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition.

The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property.

Please understand that we are not responsible for any damage or liability caused by use of the products in any of the applications below or for any other use exceeding the range or conditions set forth in this catalog.

- (1) Aerospace/Aviation equipment
- (2) Transportation equipment (cars, electric trains, ships, etc.)
- (3) Medical equipment
- (4) Power-generation control equipment
- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When using this product in general-purpose applications, you are kindly requested to take into consideration securing protection circuit/ equipment or providing backup circuits, etc., to ensure higher safety.

All specifications are subject to change without notice.

[•] Before using these products, be sure to request the delivery specifications.