Effective January 2021 Supersedes December 2019

S505SC 5 mm x 20 mm Time-delay, axial lead ceramic tube fuses





Product features

- Time-delay, high breaking capacity
- Designed to IEC 60127-2
- Nickel-plated brass end cap construction
- 5 mm x 20 mm physical size

Applications

- Primary circuit protection:
- Power supplies
- LED lighting
- LED/LCD televisions
- · Appliances and white goods
- Printers

Agency information

 cURus Recognition file number: E19180, Guide JDYX2/JDYX8

BUSSMANN

- SEMKO: File 1219335, 1310139
- VDE: File 40024252, 40037710 (1 A 8 A)
- BSI: File KM55676
- IMQ: File CA03.00529
- PSE/JET: JET1641-31003-1010, JET1641-31003-2002, JET7042-31003-2001
- CCC self declaration: 2020970207000210
- KC-Mark: File SU05011-12003, SU05011-12004, SU05011-12005A; SU05030-13003A, SU05030-13004, SU05030-13005
- TUV: J50233218

Ordering

 The ordering code is the part number replacing the " with a "-" plus adding the packaging prefix (i.e. S505SC-1.25-R; BK-S505SC1-25-R)

Packaging prefixes

- BK- (20 parts in a carrier, 5 carriers in a box)
- TR2- (1500 parts per reel, tape width 52 mm)
- TR3- (1500 parts per reel, tape width 54 mm)



Electrical characteristics

I <u>.</u>	1.51 _n min minute	2.11 max minute	2.751 min ms	max s	4l min ms	max s	10l min ms	max ms
1 A-3.15 A	60	30	750	80	95	5	10	150
4 A-6.3 A	60	30	750	80	150	5	10	150
8 A-10 A	30	30	750	80	150	5	10	150

Product specifications

Part number⁵	Current rating (A)	Voltage rating (Vac)	Interrupting rating at rated voltage (50 Hz) (A)	Typical DC cold resistance (Ω) ²	Typical pre-arc- ing l ² t (A ² s) ³	Typical voltage drop (mV)⁴	IMQ	VDE	SEMKO	cURus	PSE/ JET	ссс	кс	BSI	τυν
S505SC-1-R	1.0	250	1500	0.169	1.38	180	Х	х	х	Х	х	х	х	х	Х
S505SC-1.25-R	1.25	250	1500	0.108	2.14	151	х	х	х	Х	х	х	х	х	х
S505SC-1.6-R	1.6	250	1500	0.070	7.35	130	х	х	х	Х	х	Х	х	х	Х
S505SC-2-R	2.0	250	1500	0.055	9.83	123.5	х	х	х	Х	х	Х	х	х	х
S505SC-2.5-R	2.5	250	1500	0.040	19.9	119	х	х	х	Х	х	х	х	х	х
S505SC-3.15-R	3.15	250	1500	0.031	40.4	110	х	х	х	Х	х	х	х	х	х
S505SC-4-R	4.0	250	1500	0.018	41.0	89.8	х	х	х	Х	х	Х	х	х	х
S505SC-5-R	5.0	250	1500	0.013	71.2	88	х	х	х	х	х	х	х	х	Х
S505SC-6.3-R	6.3	250	1500	0.010	152	72.5	х	х	х	Х	х	х	х	х	х
S505SC-8-R	8.0	250	1500	0.007	237	82.5	х	х	х	Х	х	х	Х	х	х
S505SC-10-R	10	250	1500	0.005	353	70	х		х	Х	х	х	х	х	х

1 Interrupting ratings 1 A to 10 A were measured at 70% to 80% PF on AC.

2 Typical DC cold resistance measured at <10% of rated current .

3. Typical I²t value is measured at 10 times the rated current under DC.

4. Typical voltage drop is measured at +20 $^{\circ}\mathrm{C}$ ambient temperature at rated current .


5. Part number definition: S505SC-xxx-R

S505 = Product code


SC = Single cap xxx = Ampere rating

-R = RoHS compliant


Dimensions-mm




Time vs. current curve



l²t vs. time curve




Temperature derating curve



General specifications

Operating temperature: -55 °C to +125 °C (with derating)

Wave solder profile



Reference EN 61760-1:2006

Profile feat	ure	Standard SnPb solder	Lead (Pb) free solder				
Preheat	• Temperature min. (T _{smin})	100 °C	100 °C				
	• Temperature typ. (T _{Styp})	120 °C	120 °C				
	• Temperature max. (T _{smax})	130 °C	130 °C				
	• Time (T _{smin} to T _{smax}) (t _s)	70 seconds	70 seconds				
$\overline{\Delta}$ preheat to max Temperature		150 °C max.	150 °C max.				
Peak temperature (Tp)*		235 °C – 260 °C	250 °C − 260 °C				
Time at peak temperature (t _p)		10 seconds max 5 seconds max each wave	10 seconds max 5 seconds max each wave				
Ramp-down ra	ate	~ 2 K/s min ~3.5 K/s typ ~5 K/s max	~ 2 K/s min ~3.5 K/s typ ~5 K/s max				
Time 25 °C to 25 °C		4 minutes	4 minutes				

Manual solder

Powerina Business Worldwide

+350 °C (4-5 seconds by soldering iron), generally manual/hand soldering is not recommended.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton Electronics Division 1000 Eaton Boulevard Cleveland, OH 44122 United States Eaton.com/electronics

© 2021 Eaton All Rights Reserved Printed in USA Publication No. 10132 January 2021

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

