

July 2015

Multilayer Diplexer

For 806-941MHz / 1574.42-1576.42MHz

DPX161576DT-8011B1

1.6x0.8mm [EIA 0603]*

* Dimensions Code JIS[EIA]


Multilayer Diplexer

Conformity to RoHS Directive


For 806-941MHz / 1574.42-1576.42MHz

DPX161576DT-8011B1


SHAPES AND DIMENSIONS



RECOMMENDED LAND PATTERN



EVALUATION BOARD



Line width should be designed to match 50Ω characteristic impedance, depending on PCB material and thickness.

O RoHS Directive Compliant Product: See the following for more details related to RoHS Directive compliant products. http://product.tdk.com/en/environment/rohs/

All specifications are subject to change without notice.

[•] Before using these products, be sure to request the delivery specifications.

DPX161576DT-8011B1

ELECTRICAL CHARACTERISTICS

LOW-BAND

Item	Frequency Range (MHz)	Min.	Тур.	Max.
Insertion Loss (dB)	806 to 941	_	0.40	0.60
	806 to 941	_		0.70 (-30 to +85°C)
Return Loss (dB)	806 to 941	14	16.8	_
Attenuation (dB)	1575	16	21.7	_
	1612 to 1648	18	25.2	_
	1792 to 1856	14	18.9	_
	2000 to 3000	5	10.1	_
Characteristic Impedance (Ω)			50 (Nominal)	

• Ta: +25±5°C

□HIGH-BAND

Item	Frequency Range (MHz)	Min.	Тур.	Max.
Insertion Loss (dB)	1574.42 to 1576.42	—	0.66	0.70
Insertion Loss (dB)	1574.42 to 1576.42	—	—	0.80 (-30 to +85°C)
Return Loss (dB)	1574.42 to 1576.42	14	22.8	—
Attenuation (dB)	806 to 928	20	30.5	_
Characteristic Impedance (Ω)			50 (Nominal)	

• Ta: +25±5°C

Item	Frequency Range (MHz)	Min.	Тур.	Max.
Isolation (dB)	806 to 928	20	30.8	_
	1575	16	22.3	—
	1612 to 1648	18	26.0	_
	1792 to 1856	14	21.5	_
Return Loss (dB)	806 to 941	14	17.6	—
	1574.42 to 1576.42	14	16.7	—
Characteristic Impedance (Ω)			50 (Nominal)	

• Ta: +25±5°C

TEMPERATURE RANGE

Operating temperature		
(° C)		
-30 to +85		


• All specifications are subject to change without notice.

• Before using these products, be sure to request the delivery specifications.


DPX161576DT-8011B1

FREQUENCY CHARACTERISTICS







Return Loss



Attenuation









Return Loss

HIGH-BAND



Attenuation




• All specifications are subject to change without notice.


• Before using these products, be sure to request the delivery specifications.

DPX161576DT-8011B1

FREQUENCY CHARACTERISTICS








• All specifications are subject to change without notice.

• Before using these products, be sure to request the delivery specifications.

⊗TDK

RECOMMENDED REFLOW PROFILE



Soldering Preheating Critical zone (T3 to T4) Peak Temp. Time Temp. Time Temp. Time T1 T2 **T**4 t3* t1 ТЗ t2 150°C 200°C 60 to 120sec 217°C 60 to 120sec 240 to 260°C 30sec max.

 * t3 : Time within 5°C of actual peak temperature

The maximum number of reflow is 3.

All specifications are subject to change without notice.Before using these products, be sure to request the delivery specifications.

REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using these products.

▲ REMINDERS

The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition.

The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property.

Please understand that we are not responsible for any damage or liability caused by use of the products in any of the applications below or for any other use exceeding the range or conditions set forth in this catalog.

- (1) Aerospace/Aviation equipment
- (2) Transportation equipment (cars, electric trains, ships, etc.)
- (3) Medical equipment
- (4) Power-generation control equipment
- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When using this product in general-purpose applications, you are kindly requested to take into consideration securing protection circuit/ equipment or providing backup circuits, etc., to ensure higher safety.

• All specifications are subject to change without notice.

[•] Before using these products, be sure to request the delivery specifications.