AMDLA4012Q MOLDED INDUCTOR

FEATURES

- AEC-Q200 Qualified
- Shielded construction
- Soft saturation
- Low DCR per cubic mm
- Designed for switching frequencies between 100KHz-5MHz

ELECTRICAL SPECIFICATIONS @ 25°C

PART NUMBER*	INDUCTANCE		IRMS	ISAT	DC RESISTANCE (mΩ)		ТҮРЕ
	(uH)	(%)	(A)	(A)	TYP	MAX	
AMDLA4012Q-R33MT	0.33	20	10	14	12	14.5	Lead Frame
AMDLA4012Q-R47MT	0.47	20	8.8	13	16.8	20	Lead Frame
AMDLA4012Q-1R0MT	1.0	20	5.2	7.8	36.5	43	Lead Frame
AMDLA4012Q-1R5MT	1.5	20	4.2	6.2	54.5	62	Lead Frame
AMDLA4012Q-2R2MT	2.2	20	3.5	5.5	72	80	Lead Frame
AMDLA4012Q-3R3MT	3.3	20	2.8	4.5	97	111	Lead Frame
AMDLA4012Q-4R7MT	4.7	20	2.2	3.2	119	143	Lead Frame

* Please refer to Part Identification section

Test Conditions

Inductance: 1 MHz, 1 V, 0 Adc Humidity Range: 85 \pm 2% RH Temperature Rise Current: Current measured at Δ T of 40°C Saturation Current: Current measured at Δ L of 30%

PART BUILDER



Series

*Refer to Electrical Specification table

1. Tolerance: M = 20%

Inductance* Tol.¹

2. Packaging: B = Bulk

T = Tape and Reel (4,000pcs/reel)

Packaging²

GENERAL SPECIFICATIONS

Operating Temperature: -55°C to +125°C with (40°C rise) Irms current. **Maximum Part Temperature:** +125°C


Components Storage Temperature: -55°C to +125°C Tape and Reel Packaging

Temperature: -20°C to +65°C MSL: Level 1

MATERIALS

Core:Metal AlloyWire:CopperTerminal:Tin PlatingInk:Black

PRODUCT DIMENSIONS










Check Inventory 🕥

Request Samples 🕥



RECOMMENDED REFLOW PROFILE



ZONE	DESCRIPTION	TEMPERATURE	TIMES
1	Preheat	T _{smin} [∼] T _{smax} 150°C [∼] 180°C	60 ~ 120 sec.
2	Reflow	Τ _∟ 230℃	30 ~ 40 sec.
3	Peak Heat	Т _Р 250°С+0/-5°С	10 sec. MAX




AMDLA4012Q MOLDED INDUCTOR




PACKAGING

Tape and Reel:	4,000
Units per Carton:	32,000
T&R per Carton:	8
Weight per Carton:	13.5 kg
Weight per Unit:	0.34 g
Carton Dimensions:	360 x 360 x 400 mm



ТҮРЕ	А	В	С	D
13" x 12 mm	12.4 +2/-0	100.0 ± 0.5	13.0 +0.5/-0.2	330.0



1.50

This product is commercial off-the-shelf (COTS) and not specifically designed for automotive, military, aviation, aerospace, implantable, life-dependent medical or safety applications. This product is not recommended for use in any application requiring high reliability in which component failure could result in loss of life and/or property damage without prior written approval from Abracon. Specifications are subject to change without notice. Contact Abracon for more information.

 $4.85 \pm 0.10 \qquad 4.45 \pm 0.10 \qquad 1.40 \pm 0.10 \qquad 8.00 \pm 0.10 \qquad 12.00 \pm 0.30 \qquad 5.50 \pm 0.10 \qquad 0.30 \pm 0.05$



Headquarters: 5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858