


A758, Polymer Aluminum, 390 uF, 20%, 2.5 VDC, -55/+105°C, Lead Spacing = 2.5mm



**Dimensions**

<b>D</b>	6.3mm +/-0.5mm
<b>L</b>	8mm +/-1mm
<b>S</b>	2.5mm +/-0.5mm
<b>LL Negative</b>	15mm MIN
<b>LL Positive</b>	19mm MIN
<b>F</b>	0.5mm +/-0.05mm

**Packaging Specifications**

<b>Packaging:</b>	Bulk, Bag
<b>Packaging Quantity:</b>	1000

**General Information**

<b>Series:</b>	A758
<b>Dielectric:</b>	Polymer Aluminum
<b>Description:</b>	Single Ended, Polymer Aluminum
<b>RoHS:</b>	Yes
<b>Lead:</b>	Wire Leads
<b>AEC-Q200:</b>	No
<b>Halogen Free:</b>	Yes

**Specifications**

<b>Capacitance:</b>	390 uF
<b>Capacitance Tolerance:</b>	20%
<b>Voltage DC:</b>	2.5 VDC, 2.9 VDC (Surge)
<b>Temperature Range:</b>	-55/+105°C
<b>Rated Temperature:</b>	105°C
<b>Life:</b>	5000 Hrs (+/-20% Initial Capacitance, 1.5x DF MAX, Leakage Within Limit)
<b>Dissipation Factor:</b>	10% 120Hz 20C
<b>Resistance:</b>	18 mOhms (100kHz 20C)
<b>Ripple Current:</b>	3100 mAmps (100kHz 105C)
<b>Leakage Current:</b>	146.25 uA (2min 20°C)