Intrinsically safe integral cable accelerometer

786F-IS



Sensitivity, ±5%, 25°C	100 mV/g
Acceleration range, VDC > 22 V	80 g peak
Amplitude nonlinearity	1%
Frequency response: ±10% ±3 dB	1 - 8,000 Hz 0.5 - 13,000 Hz
Resonance frequency	30 kHz
Transverse sensitivity, max	5% of axial
Temperature response: -25°C +120°C	–10% +10%
Power requirement: Voltage source Current regulating diode	18 - 30 VDC 2 - 10 mA
Electrical noise, equiv. g: Broadband 2.5 Hz to 25 kHz Spectral 10 Hz 100 Hz 1,000 Hz	700 μg 10 μg/√Hz 5 μg/√Hz 5 μg/√Hz
Output impedance, max	100 Ω
Bias output voltage	12 VDC
Grounding	case isolated, internally shielded
Temperature range	–50° to +120°C
Vibration limit	500 g peak
Shock limit	5,000 g peak
Electromagnetic sensitivity, equiv. g, max	τ 70 μg/gauss
Sealing	hermetic
Base strain sensitivity, max	0.0002 g/µstrain
Hydrostatic pressure	100 psi
Sensing element design	PZT, shear
Weight	90 grams (excluding cable)
Case material	316L stainless steel
Mounting	1/4-28 UNF tapped hole
Integral cabling	J9T2A, 16 ft., blunt cut

Accessories supplied: SF6 mounting stud (metric mounting available); calibration data (level 2)

Certifications



Class I, Div 1 Groups A, B, C, D Class II, Div 1 Groups E, F, G Class III

Class I Zone 0 AEx/Ex ia IIC T4 Ta = -50°C to 120°C



II 1 G Ex ia IIC T4 Ga Ta = -50°C to 120°C






Must be installed per document 12879. For application in explosive atmospheres caused by gases, vapours or mists and where the use of apparatus of category 1G is required, electrostatic charges on the cable and non-metallic parts of the enclosure shall be avoided. The ambient temperature range for these applications is -40° C to $+80^{\circ}$ C.





Key features

- · Class I, Div 1/Zone 1 certified intrinsically safe
- · 100 psi pressure rating
- · Manufactured in ISO 9001 facility



Connections	
Function	Cable conductor
power/signal	white
common	black
case	shield

Note: Due to continuous process improvement, specifications are subject to change without notice. This document is cleared for public release.