DL DIELECTRIC<sup>®</sup> Mulaboratories

a Knowles Precision Devices brand

## 10. 25 GHz Surface Mount Band pass Filter



www.knowlescapacitors.com

**B099NC4S** 

#### DESCRIPTION

One of DLI's surface mountable catalog bandpass filters designed for the 5G band. This filter utilizes DLI's low loss temperature stable materials which offer small size and minimal performance variation over temperature. The catalog BPF's are offered in a variety of frequency bands, which offers a drop in solution with highly repeatable performance.


#### **FEATURES**

- Small Size
- Fully Shielded Component
- Solder Surface Mount Package
- Moisture Sensitivity Level: MSL1
- Frequency Stable over Temperature
- Operating & Storage Temp: -55°C to +125°C
- Characteristic Impedance: 50Ω

### SPECIFICATIONS\*

Parameter	Frequency Range (GHz)	Min	Тур.	Max
Insertion Loss (dB)	9.0 - 11.25	2.0	2.25	2.25
Return Loss (dB)			10	10
Low Side Rejection (dB)	DC - 7.5		40	40
High Side Rejection (dB)	13.0 - 23.0		40	40
Input Power (W)				TBD
Size (L x W x H)	0.400x 0.150 x 0.090 in 10.16 x 3.81 x 2.286 mm			

\*Electrical specifications based on typical probed performance at room temperature. Insertion loss shall vary ±0.5dB over temperature.



2777 Route 20 East, Cazenovia, NY 13035| Ph.: (315)655-8710 | KCCSales@knowles.com

## **Typical Measured RF Performance**




10. 25 GHz Surface Mount Band pass Filter

# **B099NC4S**

# Physical Dimensions

COMPEX • DLI • JOHANSON MFG NOVACAP • SYFER • VOLTRONICS www.knowlescapacitors.com

Units = inches (in)



2777 Route 20 East, Cazenovia, NY 13035| Ph.: (315)655-8710 | KCCSales@knowles.com