Saturating Choke



See below:

Approvals and Compliances

Description

- Saturating choke
- THT-terminals
- Based on laminated iron core
- Fully potted resign

Applications

- Phase angle control circuits with thyristors, triacs or transistors
- The choke acts at its optimum when it is mounted directly at the interference originator (thyristor, triac)

Weblinks

pdf data sheet, html datasheet, General Product Information, Approvals, Distributor-Stock-Check, Detailed request for product

Technical Data

Rated voltage	up to 440 VAC
Rated Current	0.8 - 10A @ Ta 45 °C
Power Operating Frequency	50/60 Hz
Terminal Type	THT, Flexible wire
Weight	14 - 86g
Material: Housing	UL 94V-0
Sealing Compound	UL 94V-0

Isolation Voltage	2 kV eff., winding to ambient	
Climatic Category	25/100/21 acc. to IEC 60068-1	
Allowable Operation Temp.	-25°C to 100°C	

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals

SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

Application standards

Application standards where the product can be used

Organization	Design	Standard	Description
<u>IEC</u>	Designed for applications acc.		IEC 62368-1 includes the basic requirements for safety of audio, video, information technology and office equipment.

Compliances


The product complies with following Guide Lines


requirements laid down in the harmonisation of Community legislation its affixing in accordance with EU Regulation 765/2008. ROHS SCHURTER AG Directive RoHS 2011/65/EU, Amendment (EU) 2015/863 China RoHS SCHURTER AG The law SJ / T 11363-2006 (China RoHS) has been in force since 1 Ma 2007. It is similar to the EU directive RoHS. REACH SCHURTER AG On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration,	Identification	Details	Initiator	Description
China RoHS SCHURTER AG The law SJ / T 11363-2006 (China RoHS) has been in force since 1 Ma 2007. It is similar to the EU directive RoHS. REACH REACH SCHURTER AG On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated a	C€	CE declaration of conformity	SCHURTER AG	The CE marking declares that the product complies with the applicable requirements laid down in the harmonisation of Community legislation on its affixing in accordance with EU Regulation 765/2008.
2007. It is similar to the EU directive RoHS. REACH SCHURTER AG On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated a	ROHS	RoHS	SCHURTER AG	Directive RoHS 2011/65/EU, Amendment (EU) 2015/863
Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated a	©	China RoHS	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.
	REACH	REACH	SCHURTER AG	Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as


Dimension [mm]


Case 00

Case 08













Case 17

Case 21











Diagrams



Interference suppression with resistive load, 2-phase

- 1) Line
- 2) Load




Interference suppression with resisitive load, 2-stage

DFSG: Radio interference suppression saturation choke


DFK: Radio interference suppression choke magnetically condensated

- 1) Line
- 2) Load



Interference suppression with resistive load, < 10A, e.g. dimmers circuit (DFSG)


- 1) Line
- 2) Load
- 3) only to protection class I



Interference suppression with inductive load

- 1) Line
- 2) Load

Derating Curves



Allowed current versus ambient temperature

All Variants

I _n [A]	R_{cu} [m Ω]	Weight [g]	Housings	Packing unit [pcs.]	Order Number
0.8	1300	14 g	00	90	DFSG-20-0001
1.5	450	14 g	00	90	DFSG-20-0002
2	260	29 g	08	25	DFSG-25-0001
3	100	29 g	08	25	DFSG-25-0002
3	165	55 g	17	30	DFSG-30-0001
6	60	55 g	17	30	DFSG-30-0002
5	70	86 g	21	30	DFSG-33-0001
10	30	86 g	21	30	DFSG-33-0002

Most Popular.

Availability for all products can be searched real-time:https://www.schurter.com/en/Stock-Check/ Stock-Check-SCHURTER