

## 1.227 GHz Surface Mount Bandpass Filter



**B012MD5S** 

www.knowlescapacitors.com

#### DESCRIPTION

**SPECIFICATIONS\*** 


One of DLI's surface mountable catalog
bandpass filters designed for the 5G band. This
filter utilizes DLI's low loss temperature stable
materials which offer small size and minimal
performance variation over temperature. The
catalog BPF's are offered in a variety of
frequency bands, which offers a drop in solution
with highly repeatable performance.

### **FEATURES**

- Small Size •
- Shielded Component .
- Solder Surface Mount Package .
- Moisture Sensitivity Level: MSL1 •
- Frequency Stable over Temperature •
- Operating & Storage Temp: -55°C to +125°C
- Characteristic Impedance: 50Ω

Parameter	Frequency Range (GHz)	Min	Тур.	Max
Insertion Loss (dB)	· 1.220 - 1.234		3.5	4.2
Return Loss (dB)		9.5	10	
Low Side Rejection (dB)	DC - 0.925	40	45	
High Side Rejection (dB)	1.45 - 2.5	40	50	
Input Power (W)				TBD
Size (L x W x H)	0.460 x 0.460 x 0.113 in 11.68 x 11.68 x 2.87 mm			

\*Electrical specifications based on typical probed performance at room temperature. Insertion loss shall vary ±0.5dB over temperature.



2777 Route 20 East, Cazenovia, NY 13035| Ph.: (315)655-8710 | KCCSales@knowles.com

## **Typical Measured Performance**



1.227 GHz Surface Mount Bandpass Filter




.030

.018


.015

## **B012MD5S**

# **Physical Dimensions**



# **Recommended PCB Layout**



- $50\Omega$  trace dimensions are application specific.
- Ensure adequate grounding beneath the part.



2777 Route 20 East, Cazenovia, NY 13035| Ph.: (315)655-8710 | KCCSales@knowles.com