

### 2.8 GHz Surface Mount Bandpass Filter



**B028RF2S** 

DESCRIPTION

# SPECIFICATIONS\*


One of DLI's surface mountable catalog	
bandpass filters designed for the 5G band. This	
filter utilizes DLI's low loss temperature stable	
materials which offer small size and minimal	
performance variation over temperature. The	
catalog BPF's are offered in a variety of	
frequency bands, which offers a drop in solution	
with highly repeatable performance.	

#### FEATURES

- Small Size
- Fully Shielded Component
- Solder Surface Mount Package
- Moisture Sensitivity Level: MSL1
- Frequency Stable over Temperature
- Operating & Storage Temp: -55°C to +125°C
- Characteristic Impedance: 50Ω

Parameter	Frequency Range (GHz)	Min	Тур.	Max	
Insertion Loss (dB)	2.0 - 4.0		2.0	3.0	
Return Loss (dB)		10	11.5		
Low Side Rejection (dB)	DC - 1.25	40	45		
High Side Rejection (dB)	4.85 - 6.0	40	45		
Input Power (W)				TBD	
Size (L x W x H)	0.460 x 0.460x 0.113 in 11.68 x 11.68 x 2.87 mm				

\*Electrical specifications based on typical probed performance at room temperature. Insertion loss shall vary ±0.5dB over temperature.



2777 Route 20 East, Cazenovia, NY 13035| Ph.: (315)655-8710 | KCCSales@knowles.com

### **Typical Measured Performance**




2.8 GHz Surface Mount Bandpass Filter




### **B028RF2S**

## **Physical Dimensions**



# **Recommended PCB Layout**



- 50Ω trace dimensions are application specific.
- Ensure adequate grounding beneath the part.



2777 Route 20 East, Cazenovia, NY 13035| Ph.: (315)655-8710 | KCCSales@knowles.com