

Parameter	Rating	Units
Blocking Voltage	400	V <sub>P</sub>
Load Current	250	mA <sub>rms</sub> / mA <sub>DC</sub>
On-Resistance (max)	8	Ω


#### **Features**

- · Low On-Resistance, High Current Handling
- · Low Drive Power Requirements
- 3750V<sub>rms</sub> Input/Output Isolation
- High Reliability
- VDE Compatible
- FCC Compatible
- Arc-Free With No Snubbing Circuits
- No EMI/RFI Generation
- Flammability Rating UL 94 V-0
- Small 6-Pin Package
- Surface Mount Tape & Reel Version Available

## **Applications**

- Telecommunications
  - Telecomm Switching
  - Hook Switch
- Instrumentation
- Multiplexers
- Data Acquisition
- Electronic Switching
- I/O Subsystems
- · Meters (Watt-Hour, Water, Gas)
- · Medical Equipment—Patient/Equipment Isolation
- Security
- Aerospace
- Industrial Controls
- Automotive

## **Pin Configuration**









# **Description**

The PLA140 is a single-pole normally open (1-Form-A) Solid State Relay that uses optically coupled MOSFET technology to provide 3750V<sub>rms</sub> of input-to-output isolation.

MOSFET output switches, which use IXYS Integrated Circuits' patented OptoMOS architecture, are controlled by a highly efficient infrared LED.

The PLA140's combination of low on-resistance and high load current handling makes it suitable for a variety of industrial applications.

Because Solid State Relays like the PLA140 have no moving parts, they offer faster, bounce-free switching in a more compact surface mount or though hole package than traditional electromechanical relays.


## **Approvals**

- UL Certified Component: File E76270
- CSA Certified Component: Certificate 1175739
- EN/IEC 60950-1 Certified Component: Certificate available on our website

# **Ordering Information**

Part Number	Description
PLA140	6-Pin DIP (50/Tube)
PLA140S	6-Pin Surface Mount (50/Tube)
PLA140STR	6-Pin Surface Mount (1,000/Reel)

#### Switching Characteristics of Normally Open Devices





# Absolute Maximum Ratings @ 25°C

Parameter	Ratings	Units
Blocking Voltage	400	$V_P$
Reverse Input Voltage	5	V
Input Control Current	50	mA
Peak (10ms)	1	Α
Input Power Dissipation <sup>1</sup>	150	mW
Total Power Dissipation <sup>2</sup>	800	mW
Isolation Voltage, Input to Output	3750	V <sub>rms</sub>
Operational Temperature	-40 to +85	°C
Storage Temperature	-40 to +125	°C

<sup>1</sup> Derate linearly 1.33 mW / °C

Absolute Maximum Ratings are stress ratings. Stresses in excess of these ratings can cause permanent damage to the device. Functional operation of the device at conditions beyond those indicated in the operational sections of this data sheet is not implied.

Typical values are characteristic of the device at +25°C, and are the result of engineering evaluations. They are provided for information purposes only, and are not part of the manufacturing testing requirements.


## Electrical Characteristics @ 25°C


Parameter	Conditions	Symbol	Min	Тур	Max	Units
Output Characteristics	'					
Load Current (Continuous)						
AC/DC Configuration	I Em A		-	-	250	mA <sub>rms</sub> / mA <sub>DC</sub>
DC Configuration	I <sub>F</sub> =5mA	IL I	-	-	350	mA <sub>DC</sub>
Peak Load Current	I <sub>F</sub> =5mA , t=10ms	I <sub>LPK</sub>	-	-	±500	mA <sub>P</sub>
On-Resistance						
AC/DC Configuration	I <sub>F</sub> =5mA , I <sub>L</sub> =250mA	D.	-	5.5	8	Ω
DC Configuration	I <sub>F</sub> =5mA , I <sub>L</sub> =350mA	R <sub>ON</sub>	-	1.5	3	22
Off-State Leakage Current	$V_L = 400 V_P$	I <sub>LEAK</sub>	-	-	1	μΑ
Switching Speeds						
Turn-On	I Em / \/ 10\/	t <sub>on</sub>	-	0.4	3	100.0
Turn-Off	I <sub>F</sub> =5mA, V <sub>L</sub> =10V	t <sub>off</sub>	-	0.19	1	ms
Output Capacitance	I <sub>F</sub> =0mA , V <sub>L</sub> =50V, f=1MHz	C <sub>OUT</sub>	-	18	-	pF
Input Characteristics				1		1
Input Control Current to Activate	I <sub>L</sub> =250mA	I <sub>F</sub>	-	0.46	5	mA
Input Control Current to Deactivate	-	I <sub>F</sub>	0.2	0.44	-	mA
Input Voltage Drop	I <sub>F</sub> =5mA	$V_{F}$	0.9	1.2	1.5	V
Reverse Input Current	V <sub>R</sub> =5V	I <sub>R</sub>	-	-	10	μΑ
Common Characteristics				1	1	1
Input to Output Capacitance	V <sub>IO</sub> =0V, f=1MHz	C <sub>IO</sub>	-	3	-	pF


<sup>&</sup>lt;sup>2</sup> Derate linearly 6.67 mW / °C





#### **PERFORMANCE DATA\***



































\*Unless otherwise noted, data presented in these graphs is typical of device operation at 25°C. For guaranteed parameters not indicated in the written specifications, please contact our application department.





#### **PERFORMANCE DATA\***

























# **Manufacturing Information**

### **Moisture Sensitivity**

All plastic encapsulated semiconductor packages are susceptible to moisture ingression. IXYS Integrated Circuits classifies its plastic encapsulated devices for moisture sensitivity according to the latest version of the joint industry standard, IPC/JEDEC J-STD-020, in force at the time of product evaluation. We test all of our products to the maximum conditions set forth in the standard, and guarantee proper operation of our devices when handled according to the limitations and information in that standard as well as to any limitations set forth in the information or standards referenced below.

Failure to adhere to the warnings or limitations as established by the listed specifications could result in reduced product performance, reduction of operable life, and/or reduction of overall reliability.

This product carries a Moisture Sensitivity Level (MSL) classification as shown below, and should be handled according to the requirements of the latest version of the joint industry standard **IPC/JEDEC J-STD-033**.

Device	Moisture Sensitivity Level (MSL) Classification
PLA140 / PLA140S	MSL 1

#### **ESD Sensitivity**



This product is ESD Sensitive, and should be handled according to the industry standard JESD-625.

### **Soldering Profile**

Provided in the table below is the Classification Temperature ( $T_C$ ) of this product and the maximum dwell time the body temperature of this device may be ( $T_C$  - 5)°C or greater. The classification temperature sets the Maximum Body Temperature allowed for this device during lead-free reflow processes. For through-hole devices, and any other processes, the guidelines of **J-STD-020** must be observed.

Device	Classification Temperature (T <sub>c</sub> )	Dwell Time (t <sub>p</sub> )	Max Reflow Cycles
PLA140	250°C	30 seconds	1
PLA140S	250°C	30 seconds	3

### **Board Wash**

IXYS Integrated Circuits recommends the use of no-clean flux formulations. Board washing to reduce or remove flux residue following the solder reflow process is acceptable provided proper precautions are taken to prevent damage to the device. These precautions include, but are not limited to: using a low pressure wash and providing a follow up bake cycle sufficient to remove any moisture trapped within the device due to the washing process. Due to the variability of the wash parameters used to clean the board, determination of the bake temperature and duration necessary to remove the moisture trapped within the package is the responsibility of the user (assembler). Cleaning or drying methods that employ ultrasonic energy may damage the device and should not be used. Additionally, the device must not be exposed to flux or solvents that are Chlorine- or Fluorine-based.











#### **MECHANICAL DIMENSIONS**

#### **PLA140**





#### **PCB Hole Pattern**



Dimensions mm (inches)

### **PLA140S**





# 2.54 (0.10) 0 0 — 8.90 (0.3503) (0.0649) —

0.65

(0.0255)


**PCB Land Pattern** 

<u>Dimensions</u> mm

(inches)



## PLA140STR Tape & Reel



#### For additional information please visit our website at: www.ixysic.com

IXYS Integrated Circuits makes no representations or warranties with respect to the accuracy or completeness of the contents of this publication and reserves the right to make changes to specifications and product descriptions at any time without notice. Neither circuit patent licenses nor indemnity are expressed or implied. Except as set forth in IXYS Integrated Circuits' Standard Terms and Conditions of Sale, IXYS Integrated Circuits assumes no liability whatsoever, and disclaims any express or implied warranty, relating to its products including, but not limited to, the implied warranty of merchantability, fitness for a particular purpose, or infringement of any intellectual property right.

The products described in this document are not designed, intended, authorized or warranted for use as components in systems intended for surgical implant into the body, or in other applications intended to support or sustain life, or where malfunction of IXYS Integrated Circuits' product may result in direct physical harm, injury, or death to a person or severe property or environmental damage. IXYS Integrated Circuits reserves the right to discontinue or make changes to its products at any time without notice.