




REV	LOCATIONS	DESCRIPTION	DATE	REVISER	APPD
1	△	Size changes	26/APR/21	KATE	JOHNNY

Electrical  
 Temperature Range—Operating: -25°C~+85°C  
 Material  
 Housing: PA66( UL 94V-2)  
 Applicable Terminal: FT20011  
 Mates With(Housing): FHG20012 Series



Circuits (n)	Part No.	Dimensions(in/mm)		
		A	B	C
2	FHG20011-S02M2W1B	.079(2.00)	.181(4.60)	.260(6.60)
3	FHG20011-S03M2W1B	.157(4.00)	.260(6.60)	.339(8.60)
4	FHG20011-S04M2W1B	.236(6.00)	.339(8.60)	.417(10.60)
5	FHG20011-S05M2W1B	.315(8.00)	.417(10.60)	.496(12.60)
6	FHG20011-S06M2W1B	.394(10.00)	.496(12.60)	.575(14.60)
7	FHG20011-S07M2W1B	.472(12.00)	.575(14.60)	.654(16.60)
8	FHG20011-S08M2W1B	.551(14.00)	.654(16.60)	.732(18.60)

### Ordering Information

FHG 200 11 — S XX M 2 W1 B  
 1 2 3 4 5 6 7 8 9

† Category FHG-Housing 2 Series Number 200-Pitch2.00mm 3 Distinction No. 11 4 Row Option S-Single Row

5 Circuits XX 6 Type M-Male 7 Material-Resin 2-PA66 8 Color-Resin K6-Black 9 Packaging B-PE Bag

 THIRD ANGLE PROJECTION DESIGN UNITS Inch (metric) SCALE 5:1 SIZE A4	GENERAL TOLERANCES (UNLESS SPECIFIED)		APPROVE BY FRANK	DATE 25/JUN/13	PART NO. FHG20011-SXXM2W1B	ITEM NO. FHG20011	 Leader Of Industry
	X±.012(0.30)	X'±5'	CHECKED BY JACOB	DATE 25/JUN/13	TITLE Wire to Board Pitch 2.0mm(Housing)		
	X.X±.008(0.20)	.X'±2'	DRAWN BY CHERRY	DATE 25/JUN/13	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO TXGA INDUSTRIAL ELECTRONICS(S.Z)CO.,LTD AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		
	X.XX±.006(0.15)	.XX'±1'					
	X.XXX±.004(0.10)	.XXX'±0.5'					