



REV	LOCATIONS	DESCRIPTION	DATE	REVISER	APPD

**Notes**

1. Material: PBT UL94V-0
2. Temperature Range-Operating: -25C° ~ +85C°
3. Applicable Terminal: FT25403



Circuits (n)	Part No.	Dimensions(in/mm)	
		A	B
1	FHG25403-S01M2K6B	-	.100(2.54)
2	FHG25403-S02M2K6B	.100(2.54)	.200(5.08)
3	FHG25403-S03M2K6B	.200(5.08)	.300(7.62)
4	FHG25403-S04M2K6B	.300(7.62)	.400(10.16)
5	FHG25403-S05M2K6B	.400(10.16)	.500(12.70)
6	FHG25403-S06M2K6B	.500(12.70)	.600(15.24)
7	FHG25403-S07M2K6B	.600(15.24)	.700(17.78)
8	FHG25403-S08M2K6B	.700(17.78)	.800(20.32)
9	FHG25403-S09M2K6B	.800(20.32)	.900(22.86)
10	FHG25403-S10M2K6B	.900(22.86)	1.000(25.40)
11	FHG25403-S11M2K6B	1.000(25.40)	1.100(27.94)
12	FHG25403-S12M2K6B	1.100(27.94)	1.200(30.48)
13	FHG25403-S13M2K6B	1.200(30.48)	1.300(33.02)
14	FHG25403-S14M2K6B	1.300(33.02)	1.400(35.56)
15	FHG25403-S15M2K6B	1.400(35.56)	1.500(38.10)
16	FHG25403-S16M2K6B	1.500(38.10)	1.600(40.64)



**Ordering Information**

FHG 254 03 - S XX M 2 K6 B  
 1 2 3 4 5 6 7 8 9

1   Category FHG-Housing	2   Series Number 254-Pitch2.54mm	3   Distinction No. 03	4   Row Option S-Single row	5   Circuits XX
6   Entry Type M-Male	7   Material-Resin 2-PBT	8   Color-Resin K6-Black	9   Packaging B-PE Bag	

 THIRD ANGLE PROJECTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		APPROVE BY FRANK	DATE 25/JUN/13	PART NO. FHG25403-SXXM2K6B	ITEM NO. FHG25403	 Leader Of Industry	
	DESIGN UNITS Inch (metric)	X.X±.012(0.30)	X.±5'	CHECKED BY JACOB	DATE 25/JUN/13	TITLE Wire to Board Pitch 2.54mm(Housing)		REV 0
SCALE 5:1	SIZE A4	X.XX±.006(0.15)	.XX'±1'	DRAWN BY CHERRY	DATE 25/JUN/13	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO TXGA INDUSTRIAL ELECTRONICS(S.Z.)CO.,LTD AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		