

APPROVAL SHEET

MODEL NO.:	nSMD035-13.2V	

CUSTOMER:

CUSTOMER'S APPROVAL:

AUTHORIZED SIGNATURE/STAMP:

DATE

13F.,No.120-10,Sec.3,Zhongshan Rd.,Zhonghe Dist.,New Taipei City 23544,Taiwan
Tel: 886-2-8221-2567
Fax:882-2-2225-7268
E-mail:service@chipfast.com.tw
31 Chang-Xin-Zon Road,Gao-Ling Industrial Zone,Chiu-chang Town
Huey Yang Distric, Huey Zhou City, Guang Dong516221, CHINA
Tel: 86-752-3562001
Fax:86-752-3558696
E-mail:service@atpptc.com

|--|--|

SEA & LAND ELECTRONIC CORP.



Features

- Surface Mount Devices
- Lead free device
- Size 3.2*1.6 mm/0.12*0.06 inch
- Surface Mount packaging for automated assembly

Almost anywhere there is a low voltage

Applications

- power supply, up to 60V and a load to be protected, including: Computer mother board, Modem. USB hub
- PDAs & Charger, Analog & digital line card

.

■ Digital cameras, Disk drivers, CD-ROMs,

Alpha-Top (Sea&Land Alliance)

nSMD035-13.2V

Model	Marking	V _{max}	I _{max}	I _{hold}	l _{trip}	P _d	Maxiı Time T		Resis	stance	Agency.	Approval
Model	Marking			@25°C	@25°C	Max.	Current	Time	Ri min	R1max	UL	тиу
		(Vdc)	(A)	(A)	(A)	(W)	(A)	(Sec)	(Ω)	(Ω)	0L	104
nSMD035-13.2V	αB	13.2	100	0.35	0.75	0.6	8.00	0.10	0.250	1.300		
hold = Hold Current.	Maximum cı	irrent device	e will not trip	in 25°C still a	air.							
trip = Trip Current. N	linimum curr	ent at which	the device	will always tri	ip in 25°C stil	l air.						
Vmax = Maximum operating voltage device can withstand without damage at rated current (Imax).												
Imax = Maximum fault current device can withstand without damage at rated voltage (Vmax).												
Pd = Power dissipat	ion when de	vice is in the	e tripped stat	e in 25°C stil	ll air environr	nent at rate	d voltage.					
Rimin/max = Minimum	/Maximum d	levice resist	ance prior to	tripping at 2	5°C.							
R1 _{max} = Maximum dev	/ice resistan	ce is measu	red one hou	r post reflow.								
CAUTION : Operation I	havond the s	necified ratio	nae may ree	ult in damage	o and nossibl	lo arcina ar	d flamo					

Environmental Specifications

Test	Conditions	Resistance change
Passive aging	+85°C, 1000 hrs.	±5% typical
Humidity aging	+85°C, 85% R.H. , 168 hours	±5% typical
Thermal shock	+85°C to -40°C, 20 times	±33% typical
Resistance to solvent	MIL-STD-202, Method 215	No change
Vibration	MIL-STD-202, Method 201	No change
Ambient operating conditions :	- 40 °C to 85 °C	
Maximum surface temperature of the de	evice in the tripped state is 125 °C	

Agency Approvals :

UL pending

Regulation/Standard:



2002/95/EC EN14582

Ihold Versus Temperature


Medel	Maximum ambient operating temperature (T _{mao}) vs. hold current (I _{hold})								
Model	-40°C	-20°C	0°C	25°C	40°C	50°C	60°C	70°C	85°C
nSMD035-13.2V	0.50	0.45	0.40	0.35	0.30	0.27	0.24	0.21	0.15

nSMD035-13.2V

Alpha-Top (Sea&Land Alliance)


Construction And Di	mension (Unit:n	nm)						
Model		4	В		С		D	E
Model	Min.	Max.	Min.	Max.	Min.	Max.	Min.	Min.
nSMD035-13.2V	3.00	3.50	1.50	1.80	0.40	0.90	0.15	0.10

Dimensions & Marking



 α = Trademark B = Part identification

Recommended Pad Layout (mm)




Termination Pad Characteristics

Terminal pad materials : Terminal pad solderability : Rework


Tin-plated Nickel-Copper Meets EIA specification RS186-9E and ANSI/J-STD-002 Category 3.

Use standard industry practices, the removal device must be replaced with a fresh one.

Thermal Derating Curve



Typical Time-To-Trip At 25°C



WARNING:

Use PPTC beyond the maximum ratings or improper use may result in device damage and possible electrical arcing and flame.


- DPTC are intended for protection against occasional over current or were magnetain possible conditions and should not be used when repeated fault conditions or prolonged trip events are anticipated.
 Device performance can be impacted negatively if devices are handled in a manner inconsistent with recommended electronic, thermal, and mechanical procedures for electronic components.

Use PPTC with a large inductance in circuit will generate a circuit voltage (L di/dt) above the rated voltage of the PPTC.

Avoid impact PPTC device its thermal expansion like placed under pressure or installed in limited space. Contamination of the PPTC material with certain silicon based oils or some aggressive solvents can adversely impact the performance of the devices. PPTC SMD can be cleaned by standard methods. Requests that customers comply with our recommended solder pad layouts and recommended reflow profile. Improper board layouts or reflow profile could negatively impact solderability performance of our devices.

nSMD035-13.2V


Alpha-Top (Sea&Land Alliance)




Tape And Reel Specifications (mm)

W P0 P1	$ \begin{array}{r} 8.15 \pm 0.3 \\ 4.0 \pm 0.10 \\ 4.0 \pm 0.10 \\ 2.0 \pm 0.05 \\ \end{array} $
	4.0 ± 0.10
P1	
	2.0 ± 0.05
P2	
<u>A0</u>	1.95 ± 0.10
B0	3.45 ± 0.10
B1max.	4.35
D0	1.5 + 0.1, -0
F	3.5 ± 0.05
E1	1.75 ± 0.10
E2min.	6.25
Tmax.	0.6
T1max.	0.1
<u>K0</u>	1.04 ± 0.1
Leader min.	390
Trailer min.	160
Reel Dimensions	
A max.	178
N min.	60
W1	9 ± 0.5
W2	12.6 ± 0.5

EIA Tape Component Dimensions



EIA Reel Dimensions



- Storage And Handling Storage conditions : 40°C max, 70% R.H.
- Devices may not meet specified performance if storage conditions are exceeded.

Order Information			Packaging
nSMD	035	-13.2V	Tape & Reel Quantity
Product name	Hold	Max	
Size 3216 mm / 1206 inch	Current	Voltage	5,000 pcs/reel
SMD : surface mount device	0.35A		

Tape & reel packaging per EIA481-1

Labeling Information

Sea & Land Electronic Corp.
HF Pb RoHS
Model:
Part no.:
Spec.:
Lot no.:
Q'ty:
含儲: 密封! 溫度: 18~33℃/濕度: 30~60% A